

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1304883

Luminaire Tested: P3DUS02R55B2750DE010 E3CBUS1MW_2700K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1304883
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-92)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3DUS02R55B2750DE010 E3CBUS1MW_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R55 optic, 2700K CCT AND, 90CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 289.0 lumens
Efficiency: N/A
Efficacy: 99.6 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 2.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1304883

CATALOG NUMBER: P3DUS02R55B2750DE010 E3CBUS1MW_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1304883

CATALOG NUMBER: P3DUS02R55B2750DE010 E3CBUS1MW_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	98	98
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	98	98	97	95	95	93
2	109	105	102	99	107	103	100	97	100	98	95	97	95	93	95	93	91	90	88	87
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	87	85	83	82
4	100	94	89	85	99	93	88	85	91	87	84	89	86	83	87	84	82	81	79	78
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76	74	73
6	92	84	79	76	91	84	79	75	82	78	75	81	77	74	80	76	74	73	71	70
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69	67	65
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65	63	62
9	81	73	68	64	80	72	67	64	72	67	64	71	67	64	70	66	64	62	60	59
10	78	70	64	61	77	69	64	61	68	64	61	68	64	61	67	63	61	59	57	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	96023
5°	91657
10°	91648
15°	88763
20°	80320
25°	62181
30°	31144
35°	9369
40°	2004
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 0 cd/sqm

TEST NUMBER: P1304883

CATALOG NUMBER: P3DUS02R55B2750DE010 E3CBUS1MW_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.8	13.8
10°-20°	108.5	37.5
20°-30°	111.7	38.6
30°-40°	28.1	9.7
40°-50°	1.0	0.3
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	259.9	89.9
0°-40°	288.0	99.7
0°-60°	289.0	100.0
0°-90°	289.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	289.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	438	
5°	416	40
15°	391	108
25°	257	112
35°	35	28
45°	0	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1304883

CATALOG NUMBER: P3DUS02R55B2750DE010 E3CBUS1MW_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	437.9
2.5°	429.1
5°	416.4
7.5°	413.8
10°	411.6
12.5°	403.7
15°	391.0
17.5°	371.3
20°	344.2
22.5°	307.4
25°	257.0
27.5°	193.1
30°	123.0
32.5°	71.4
35°	35.0
37.5°	16.6
40°	7.0
42.5°	1.8
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)