

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1304900

Luminaire Tested: P3DUS02R70B2750DE010 E3CBUS1MW_3500K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1304900
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-95)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3DUS02R70B2750DE010 E3CBUS1MW_3500K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R70 optic, 3500K CCT AND, 80CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 256.0 lumens
Efficiency: N/A
Efficacy: 88.3 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.99
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 2.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1304900

CATALOG NUMBER: P3DUS02R70B2750DE010 E3CBUS1MW_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1304900

CATALOG NUMBER: P3DUS02R70B2750DE010 E3CBUS1MW_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	107	105	105	103	101	101	100	98	98	96	95	94			
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87			
3	103	96	91	88	101	95	90	87	92	89	85	90	87	84	88	85	83	81			
4	98	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71			
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66			
7	83	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	62	59	66	62	59	57			
9	75	66	60	56	74	65	60	56	64	59	56	63	59	55	63	58	55	54			
10	72	62	56	52	71	62	56	52	61	56	52	60	55	52	59	55	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	62254
5°	59278
10°	56712
15°	54098
20°	50031
25°	45341
30°	39145
35°	35228
40°	13683
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 0 cd/sqm

TEST NUMBER: P1304900

CATALOG NUMBER: P3DUS02R70B2750DE010 E3CBUS1MW_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.2	9.9
10°-20°	66.6	26.0
20°-30°	85.2	33.3
30°-40°	73.5	28.7
40°-50°	5.5	2.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	177.0	69.1
0°-40°	250.5	97.9
0°-60°	256.0	100.0
0°-90°	256.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	256.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	284	
5°	269	25
15°	238	67
25°	187	85
35°	132	74
45°	0	5
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1304900

CATALOG NUMBER: P3DUS02R70B2750DE010 E3CBUS1MW_3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	283.9
2.5°	279.5
5°	269.3
7.5°	260.4
10°	254.7
12.5°	247.6
15°	238.3
17.5°	227.2
20°	214.4
22.5°	200.2
25°	187.4
27.5°	171.0
30°	154.6
32.5°	147.9
35°	131.6
37.5°	95.7
40°	47.8
42.5°	6.2
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)