

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1304919

Luminaire Tested: P3DUS05R30B2750DE010 E3CBUS1MW_3000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1304919
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-88)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3DUS05R30B2750DE010 E3CBUS1MW_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R30 optic, 3000K CCT AND, 90CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 544.0 lumens
Efficiency: N/A
Efficacy: 92.2 lumens/watt
Spacing Criteria (0/90/45): 0.5 / 0.5 / 0.45
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1304919

CATALOG NUMBER: P3DUS05R30B2750DE010 E3CBUS1MW_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1304919

CATALOG NUMBER: P3DUS05R30B2750DE010 E3CBUS1MW_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	110	113	111	109	108	107	106	105	103	103	102	100	99	99	97		
2	112	108	105	103	110	107	104	102	104	101	100	101	99	98	98	97	96	94		
3	108	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92		
4	105	100	97	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89		
5	102	97	93	90	101	96	93	90	95	91	89	93	90	88	92	89	88	87		
6	100	94	90	87	99	93	90	87	92	89	86	91	88	86	90	87	85	84		
7	97	91	87	84	96	91	87	84	90	86	84	89	86	83	88	85	83	82		
8	95	89	85	82	94	88	84	82	87	84	82	86	83	81	86	83	81	80		
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78		
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	487965
5°	474113
10°	401284
15°	241704
20°	87041
25°	24461
30°	6457
35°	2490
40°	973
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 0 cd/sqm

TEST NUMBER: P1304919

CATALOG NUMBER: P3DUS05R30B2750DE010 E3CBUS1MW_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	194.9	35.8
10°-20°	283.3	52.1
20°-30°	58.5	10.8
30°-40°	6.8	1.3
40°-50°	0.5	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	536.7	98.7
0°-40°	543.5	99.9
0°-60°	544.0	100.0
0°-90°	544.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	544.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2225	
5°	2154	195
15°	1065	283
25°	101	59
35°	9	7
45°	0	0
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1304919

CATALOG NUMBER: P3DUS05R30B2750DE010 E3CBUS1MW_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2225.3
2.5°	2207.5
5°	2153.9
7.5°	2035.8
10°	1802.2
12.5°	1466.5
15°	1064.7
17.5°	681.4
20°	373.0
22.5°	186.9
25°	101.1
27.5°	55.2
30°	25.5
32.5°	15.3
35°	9.3
37.5°	5.9
40°	3.4
42.5°	0.8
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)