

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1306658

Luminaire Tested: P3SQAS09R109027DE010 E3SQCB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1306658
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3SQAS09R109027DE010 E3SQCB1MMS
Description: 3in Adjustable LED luminaire with, R10 optic, 2700K CCT AND, 90CRI , E3SQCB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 711.0 lumens
Efficiency: N/A
Efficacy: 56.9 lumens/watt
Spacing Criteria (0/90/45): 0.18 / 0.18 / 0.18
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1306658

CATALOG NUMBER: P3SQAS09R109027DE010 E3SQCB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1306658

CATALOG NUMBER: P3SQAS09R109027DE010 E3SQCB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	116	114	113	111	114	112	111	110	108	107	106		105	104	103		101
2	113	110	108	106	111	109	107	105	106	104	103		103	102	101		100
3	111	107	104	102	109	106	103	101	104	102	100		101	100	98		99
4	109	105	102	99	107	104	101	99	102	99	98		100	98	97		98
5	107	102	99	97	105	101	99	97	100	98	96		99	97	95		97
6	105	100	97	95	104	100	97	95	98	96	94		97	95	94		96
7	103	99	96	93	102	98	95	93	97	95	93		96	94	92		95
8	102	97	94	92	101	97	94	92	96	93	92		95	93	91		94
9	100	96	93	91	100	95	93	91	95	92	90		94	92	90		93
10	99	94	92	90	98	94	91	90	94	91	89		93	91	89		92

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2528401
5°	1306181
10°	256706
15°	80822
20°	35299
25°	15620
30°	8412
35°	4436
40°	1574
45°	560
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 47.5°

Luminance: 586 cd/sqm

TEST NUMBER: P1306658

CATALOG NUMBER: P3SQAS09R109027DE010 E3SQCB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	508.2	71.5
10°-20°	144.4	20.3
20°-30°	42.1	5.9
30°-40°	13.8	1.9
40°-50°	2.4	0.3
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	694.8	97.7
0°-40°	708.6	99.7
0°-60°	711.0	100.0
0°-90°	711.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	711.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	14681	
5°	7555	508
15°	453	144
25°	82	42
35°	21	14
45°	2	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1306658

CATALOG NUMBER: P3SQAS09R109027DE010 E3SQCB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	14681.0
1°	14258.3
2°	13152.1
3°	11416.5
4°	9518.8
5°	7555.4
6°	5697.7
7°	4126.5
8°	2902.9
9°	2040.9
10°	1467.9
11°	1087.4
12°	836.1
13°	671.7
14°	547.2
15°	453.3
17.5°	300.6
20°	192.6
22.5°	122.1
25°	82.2
27.5°	58.7
30°	42.3
32.5°	30.5
35°	21.1
37.5°	14.1
40°	7.0
42.5°	4.7
45°	2.3
47.5°	2.3
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1306658

CATALOG NUMBER: P3SQAS09R109027DE010 E3SQCB1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)