

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1304947

Luminaire Tested: P3DUS05R55B2750DE010 E3CBUS1MW_5000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1304947
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-92)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3DUS05R55B2750DE010 E3CBUS1MW_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R55 optic, 5000K CCT AND, 80CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 609.0 lumens
Efficiency: N/A
Efficacy: 103.2 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1304947
CATALOG NUMBER: P3DUS05R55B2750DE010 E3CBUS1MW_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1304947

CATALOG NUMBER: P3DUS05R55B2750DE010 E3CBUS1MW_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	98	98	97	95	95	95	95
2	109	105	102	99	107	103	100	97	100	98	95	97	95	93	95	93	91	90	90	90	90
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	87	85	85	85	85
4	100	94	89	85	99	93	88	85	91	87	84	89	86	83	87	84	82	81	81	81	81
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76	76	76	76
6	92	84	79	76	91	84	79	75	82	78	75	81	77	74	80	76	74	73	73	73	73
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69	69	69	69
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65	65	65	65
9	81	73	68	64	80	72	67	64	72	67	64	71	67	64	70	66	64	62	62	62	62
10	78	70	64	61	77	69	64	61	68	64	61	68	64	61	67	63	61	59	59	59	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	202352
5°	193154
10°	193138
15°	187061
20°	169251
25°	131064
30°	65656
35°	19756
40°	4237
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 0 cd/sqm



TEST NUMBER: P1304947

CATALOG NUMBER: P3DUS05R55B2750DE010 E3CBUS1MW_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.8	13.8
10°-20°	228.6	37.5
20°-30°	235.3	38.6
30°-40°	59.3	9.7
40°-50°	2.0	0.3
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	547.7	89.9
0°-40°	607.0	99.7
0°-60°	609.0	100.0
0°-90°	609.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	609.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	923	
5°	878	84
15°	824	229
25°	542	235
35°	74	59
45°	0	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1304947
CATALOG NUMBER: P3DUS05R55B2750DE010 E3CBUS1MW_5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	922.8
2.5°	904.3
5°	877.5
7.5°	872.0
10°	867.4
12.5°	850.8
15°	824.0
17.5°	782.5
20°	725.3
22.5°	647.8
25°	541.7
27.5°	406.9
30°	259.3
32.5°	150.4
35°	73.8
37.5°	35.1
40°	14.8
42.5°	3.7
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)