

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1304966

Luminaire Tested: P3DUS09R15B2750DE010 E3CBUS1MW_4000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1304966
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-85)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3DUS09R15B2750DE010 E3CBUS1MW_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R15 optic, 4000K CCT AND, 80CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 759.0 lumens
Efficiency: N/A
Efficacy: 57.9 lumens/watt
Spacing Criteria (0/90/45): 0.29 / 0.29 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1304966

CATALOG NUMBER: P3DUS09R15B2750DE010 E3CBUS1MW_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1304966

CATALOG NUMBER: P3DUS09R15B2750DE010 E3CBUS1MW_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	116	114	112	111		113	112	110	109		108	107	106		104	103	103		101	100	100
2	113	110	107	105		111	108	106	104		105	103	102		102	101	100		100	99	98
3	110	106	103	101		109	105	102	100		103	101	99		101	99	97		98	97	96
4	108	103	100	98		106	102	100	97		101	98	96		99	97	95		97	96	94
5	106	101	98	95		104	100	97	95		99	96	94		97	95	93		96	94	93
6	104	99	95	93		102	98	95	93		97	94	92		96	93	92		95	93	91
7	102	97	93	91		101	96	93	91		95	92	90		94	92	90		93	91	90
8	100	95	92	89		99	94	91	89		94	91	89		93	90	89		92	90	88
9	98	93	90	88		97	93	90	88		92	89	88		91	89	87		91	89	87
10	97	92	89	87		96	91	88	86		91	88	86		90	88	86		90	87	86

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1622151
5°	1282211
10°	591327
15°	171261
20°	55025
25°	20662
30°	7748
35°	2382
40°	716
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 52.5°

Luminance: 468 cd/sqm

TEST NUMBER: P1304966

CATALOG NUMBER: P3DUS09R15B2750DE010 E3CBUS1MW_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	452.3	59.6
10°-20°	254.6	33.5
20°-30°	44.7	5.9
30°-40°	6.7	0.9
40°-50°	0.5	0.1
50°-60°	0.3	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	751.5	99.0
0°-40°	758.2	99.9
0°-60°	759.0	100.0
0°-90°	759.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	759.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7398	
5°	5825	452
15°	754	255
25°	85	45
35°	9	7
45°	0	0
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1304966

CATALOG NUMBER: P3DUS09R15B2750DE010 E3CBUS1MW_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	7397.6
2.5°	6986.0
5°	5825.1
7.5°	4253.8
10°	2655.7
12.5°	1436.2
15°	754.4
17.5°	418.0
20°	235.8
22.5°	137.6
25°	85.4
27.5°	52.2
30°	30.6
32.5°	14.0
35°	8.9
37.5°	5.1
40°	2.5
42.5°	1.3
45°	0.0
47.5°	0.0
50°	0.0
52.5°	1.3
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)