

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1304982

Luminaire Tested: P3DUS09R30B2750DE010 E3CBUS1MW_5000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1304982
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-88)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3DUS09R30B2750DE010 E3CBUS1MW_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R30 optic, 5000K CCT AND, 80CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 871.0 lumens
Efficiency: N/A
Efficacy: 66.5 lumens/watt
Spacing Criteria (0/90/45): 0.5 / 0.5 / 0.45
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1304982

CATALOG NUMBER: P3DUS09R30B2750DE010 E3CBUS1MW_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1304982

CATALOG NUMBER: P3DUS09R30B2750DE010 E3CBUS1MW_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	113	111	110	113	111	109	108	107	106	105		103	103	102		100	99	99	97
2	112	108	105	103	110	107	104	102	104	101	100		101	99	98		98	97	96	94
3	108	104	101	98	107	103	100	97	100	98	96		98	96	94		96	94	93	92
4	105	100	97	94	104	99	96	93	97	94	92		95	93	91		94	92	90	89
5	102	97	93	90	101	96	93	90	95	91	89		93	90	88		92	89	88	87
6	100	94	90	87	99	93	90	87	92	89	86		91	88	86		90	87	85	84
7	97	91	87	84	96	91	87	84	90	86	84		89	86	83		88	85	83	82
8	95	89	85	82	94	88	84	82	87	84	82		86	83	81		86	83	81	80
9	92	86	82	80	92	86	82	80	85	82	79		84	81	79		84	81	79	78
10	90	84	80	78	90	84	80	78	83	80	77		82	79	77		82	79	77	76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	781297
5°	759122
10°	642495
15°	386972
20°	139359
25°	39172
30°	10331
35°	4015
40°	1546
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 0 cd/sqm

TEST NUMBER: P1304982

CATALOG NUMBER: P3DUS09R30B2750DE010 E3CBUS1MW_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	312.1	35.8
10°-20°	453.6	52.1
20°-30°	93.7	10.8
30°-40°	10.9	1.3
40°-50°	0.7	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	859.3	98.7
0°-40°	870.3	99.9
0°-60°	871.0	100.0
0°-90°	871.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	871.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3563	
5°	3449	312
15°	1705	454
25°	162	94
35°	15	11
45°	0	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1304982

CATALOG NUMBER: P3DUS09R30B2750DE010 E3CBUS1MW_5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	3563.0
2.5°	3534.4
5°	3448.7
7.5°	3259.6
10°	2885.5
12.5°	2348.1
15°	1704.6
17.5°	1091.1
20°	597.2
22.5°	299.3
25°	161.9
27.5°	88.4
30°	40.8
32.5°	24.5
35°	15.0
37.5°	9.5
40°	5.4
42.5°	1.4
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)