

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1304999

Luminaire Tested: P3DUS09R50B2750DE010 E3CBUS1MW_3000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1304999
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-91)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3DUS09R50B2750DE010 E3CBUS1MW_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R50 optic, 3000K CCT AND, 90CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 837.0 lumens
Efficiency: N/A
Efficacy: 63.9 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 0.71 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1304999

CATALOG NUMBER: P3DUS09R50B2750DE010 E3CBUS1MW_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1304999

CATALOG NUMBER: P3DUS09R50B2750DE010 E3CBUS1MW_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			
2	110	105	102	99	108	104	101	98	101	98	96	98	96	94	95	93	92	90			
3	105	100	95	92	103	98	94	91	96	93	90	93	91	89	91	89	87	86			
4	101	95	90	86	99	93	89	86	91	88	85	89	86	84	88	85	83	82			
5	97	90	85	81	95	89	84	81	87	83	80	86	82	79	84	81	79	78			
6	93	85	80	77	92	85	80	76	83	79	76	82	78	75	81	78	75	74			
7	89	81	76	73	88	81	76	73	80	75	72	79	75	72	77	74	72	70			
8	86	78	73	69	85	77	72	69	76	72	69	75	71	69	74	71	68	67			
9	83	74	69	66	82	74	69	66	73	69	66	72	68	65	71	68	65	64			
10	79	71	66	63	79	71	66	63	70	66	63	69	65	63	69	65	62	61			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	337451
5°	329363
10°	311150
15°	273464
20°	205701
25°	152089
30°	92267
35°	30490
40°	5382
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 0 cd/sqm

TEST NUMBER: P1304999

CATALOG NUMBER: P3DUS09R50B2750DE010 E3CBUS1MW_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.7	16.7
10°-20°	327.6	39.1
20°-30°	280.9	33.6
30°-40°	86.6	10.3
40°-50°	2.2	0.3
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	748.2	89.4
0°-40°	834.8	99.7
0°-60°	837.0	100.0
0°-90°	837.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	837.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1539	
5°	1496	140
15°	1205	328
25°	629	281
35°	114	87
45°	0	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1304999

CATALOG NUMBER: P3DUS09R50B2750DE010 E3CBUS1MW_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1538.9
2.5°	1527.6
5°	1496.3
7.5°	1452.5
10°	1397.4
12.5°	1309.8
15°	1204.6
17.5°	1070.6
20°	881.5
22.5°	721.2
25°	628.6
27.5°	510.9
30°	364.4
32.5°	221.6
35°	113.9
37.5°	51.3
40°	18.8
42.5°	2.5
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)