

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1305000

Luminaire Tested: P3DUS09R50B2750DE010 E3CBUS1MW_3500K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1305000
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-91)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3DUS09R50B2750DE010 E3CBUS1MW_3500K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R50 optic, 3500K CCT AND, 80CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 859.0 lumens
Efficiency: N/A
Efficacy: 65.6 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 0.71 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1305000

CATALOG NUMBER: P3DUS09R50B2750DE010 E3CBUS1MW_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1305000

CATALOG NUMBER: P3DUS09R50B2750DE010 E3CBUS1MW_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20				20				20
RC	80				70				50				30				10				0				0				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	97	95	90	86	82	77	74	70	67
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	90	86	82	77	74	70	67	64	61	58	55
2	110	105	102	99	108	104	101	98	101	98	96	98	96	94	95	93	92	90	86	82	77	74	70	67	64	61	58	55	52
3	105	100	95	92	103	98	94	91	96	93	90	93	91	89	91	89	87	86	82	77	74	70	67	64	61	58	55	52	49
4	101	95	90	86	99	93	89	86	91	88	85	89	86	84	88	85	83	82	77	74	70	67	64	61	58	55	52	49	46
5	97	90	85	81	95	89	84	81	87	83	80	86	82	79	84	81	79	77	74	70	67	64	61	58	55	52	49	46	43
6	93	85	80	77	92	85	80	76	83	79	76	82	78	75	81	78	75	74	70	67	64	61	58	55	52	49	46	43	40
7	89	81	76	73	88	81	76	73	80	75	72	79	75	72	77	74	72	70	67	64	61	58	55	52	49	46	43	40	37
8	86	78	73	69	85	77	72	69	76	72	69	75	71	69	74	71	68	67	64	61	58	55	52	49	46	43	40	37	34
9	83	74	69	66	82	74	69	66	73	69	66	72	68	65	71	68	65	64	61	58	55	52	49	46	43	40	37	34	31
10	79	71	66	63	79	71	66	63	70	66	63	69	65	63	69	65	62	61	58	55	52	49	46	43	40	37	34	31	28

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	346332
5°	338036
10°	319322
15°	280637
20°	211115
25°	156082
30°	94698
35°	31293
40°	5525
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 0 cd/sqm

TEST NUMBER: P1305000

CATALOG NUMBER: P3DUS09R50B2750DE010 E3CBUS1MW_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	143.4	16.7
10°-20°	336.2	39.1
20°-30°	288.3	33.6
30°-40°	88.9	10.4
40°-50°	2.2	0.3
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	767.9	89.4
0°-40°	856.8	99.7
0°-60°	859.0	100.0
0°-90°	859.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	859.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1579	
5°	1536	143
15°	1236	336
25°	645	288
35°	117	89
45°	0	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1305000

CATALOG NUMBER: P3DUS09R50B2750DE010 E3CBUS1MW_3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1579.4
2.5°	1567.8
5°	1535.7
7.5°	1490.7
10°	1434.1
12.5°	1344.2
15°	1236.2
17.5°	1098.7
20°	904.7
22.5°	740.2
25°	645.1
27.5°	524.3
30°	374.0
32.5°	227.5
35°	116.9
37.5°	52.7
40°	19.3
42.5°	2.6
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)