

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1305017

Luminaire Tested: P3DUS09R65B2750DE010 E3CBUS1MW_5000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1305017
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-94)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3DUS09R65B2750DE010 E3CBUS1MW_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R65 optic, 5000K CCT AND, 80CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 793.0 lumens
Efficiency: N/A
Efficacy: 60.5 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.84
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1305017

CATALOG NUMBER: P3DUS09R65B2750DE010 E3CBUS1MW_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1305017

CATALOG NUMBER: P3DUS09R65B2750DE010 E3CBUS1MW_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96		94
2	109	104	101	97	107	103	99	96	99	97	94		96	94	92		94	92	90		89
3	104	98	93	90	102	96	92	89	94	90	87		92	89	86		89	87	85		83
4	99	92	87	83	97	91	86	83	89	85	82		87	83	81		85	82	80		78
5	94	87	81	77	93	86	81	77	84	80	76		82	79	76		81	78	75		74
6	90	82	76	72	89	81	76	72	80	75	72		78	74	71		77	73	71		69
7	86	77	72	68	85	77	71	68	75	71	67		74	70	67		73	69	67		65
8	82	73	68	64	81	73	67	64	72	67	63		71	66	63		70	66	63		62
9	79	69	64	60	77	69	64	60	68	63	60		67	63	60		66	62	60		58
10	75	66	61	57	74	66	60	57	65	60	57		64	60	57		63	59	56		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	232394
5°	219502
10°	212955
15°	204156
20°	185399
25°	161284
30°	111612
35°	64835
40°	17146
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 0 cd/sqm

TEST NUMBER: P1305017

CATALOG NUMBER: P3DUS09R65B2750DE010 E3CBUS1MW_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.1	11.9
10°-20°	249.8	31.5
20°-30°	293.3	37.0
30°-40°	148.6	18.7
40°-50°	7.2	0.9
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	637.2	80.4
0°-40°	785.8	99.1
0°-60°	793.0	100.0
0°-90°	793.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	793.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1060	
5°	997	94
15°	899	250
25°	667	293
35°	242	149
45°	0	7
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1305017

CATALOG NUMBER: P3DUS09R65B2750DE010 E3CBUS1MW_5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1059.8
2.5°	1036.7
5°	997.2
7.5°	972.7
10°	956.4
12.5°	934.6
15°	899.3
17.5°	848.9
20°	794.5
22.5°	738.7
25°	666.6
27.5°	553.7
30°	440.8
32.5°	342.8
35°	242.2
37.5°	141.5
40°	59.9
42.5°	9.5
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)