

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1305018

Luminaire Tested: P3DUS09R70B2750DE010 E3CBUS1MW_2700K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1305018
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-95)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3DUS09R70B2750DE010 E3CBUS1MW_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R70 optic, 2700K CCT AND, 90CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 735.0 lumens
Efficiency: N/A
Efficacy: 56.1 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.99
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1305018

CATALOG NUMBER: P3DUS09R70B2750DE010 E3CBUS1MW_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1305018

CATALOG NUMBER: P3DUS09R70B2750DE010 E3CBUS1MW_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	114	111	108	106	111	109	107	105	105	103	101		101	100	98		98	96	95		94
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93	91	89		87
3	103	96	91	88	101	95	90	87	92	89	85		90	87	84		88	85	83		81
4	98	90	85	80	96	89	84	80	87	82	79		85	81	78		83	80	77		76
5	93	84	79	74	91	83	78	74	82	77	73		80	76	73		78	75	72		71
6	88	79	73	69	86	78	73	69	77	72	68		75	71	68		74	70	67		66
7	83	74	68	64	82	74	68	64	72	67	64		71	67	63		70	66	63		61
8	79	70	64	60	78	69	64	60	68	63	59		67	62	59		66	62	59		57
9	75	66	60	56	74	65	60	56	64	59	56		63	59	55		63	58	55		54
10	72	62	56	52	71	62	56	52	61	56	52		60	55	52		59	55	52		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	178758
5°	170195
10°	162812
15°	155324
20°	143629
25°	130145
30°	112372
35°	101107
40°	39302
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 0 cd/sqm

TEST NUMBER: P1305018

CATALOG NUMBER: P3DUS09R70B2750DE010 E3CBUS1MW_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.5	9.9
10°-20°	191.1	26.0
20°-30°	244.5	33.3
30°-40°	211.1	28.7
40°-50°	15.7	2.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	508.2	69.1
0°-40°	719.3	97.9
0°-60°	735.0	100.0
0°-90°	735.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	735.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	815	
5°	773	72
15°	684	191
25°	538	245
35°	378	211
45°	0	16
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1305018

CATALOG NUMBER: P3DUS09R70B2750DE010 E3CBUS1MW_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	815.2
2.5°	802.5
5°	773.2
7.5°	747.8
10°	731.2
12.5°	710.9
15°	684.2
17.5°	652.4
20°	615.5
22.5°	574.8
25°	537.9
27.5°	490.9
30°	443.8
32.5°	424.8
35°	377.7
37.5°	274.7
40°	137.3
42.5°	17.8
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)