

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1305019

Luminaire Tested: P3DUS09R70B2750DE010 E3CBUS1MW_3000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1305019
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-95)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3DUS09R70B2750DE010 E3CBUS1MW_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R70 optic, 3000K CCT AND, 90CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 724.0 lumens
Efficiency: N/A
Efficacy: 55.3 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.99
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1305019

CATALOG NUMBER: P3DUS09R70B2750DE010 E3CBUS1MW_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1305019

CATALOG NUMBER: P3DUS09R70B2750DE010 E3CBUS1MW_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	108	106		111	109	107	105		105	103	101		101	100	98		98	96	95
2	108	103	99	96		106	102	98	95		98	95	93		95	93	91		93	91	89
3	103	96	91	88		101	95	90	87		92	89	85		90	87	84		88	85	83
4	98	90	85	80		96	89	84	80		87	82	79		85	81	78		83	80	77
5	93	84	79	74		91	83	78	74		82	77	73		80	76	73		78	75	72
6	88	79	73	69		86	78	73	69		77	72	68		75	71	68		74	70	67
7	83	74	68	64		82	74	68	64		72	67	64		71	67	63		70	66	63
8	79	70	64	60		78	69	64	60		68	63	59		67	62	59		66	62	59
9	75	66	60	56		74	65	60	56		64	59	56		63	59	55		63	58	55
10	72	62	56	52		71	62	56	52		61	56	52		60	55	52		59	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	176082
5°	167642
10°	160384
15°	152986
20°	141482
25°	128209
30°	110701
35°	99582
40°	38730
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 0 cd/sqm

TEST NUMBER: P1305019

CATALOG NUMBER: P3DUS09R70B2750DE010 E3CBUS1MW_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.4	9.9
10°-20°	188.3	26.0
20°-30°	240.9	33.3
30°-40°	207.9	28.7
40°-50°	15.5	2.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	500.6	69.1
0°-40°	708.5	97.9
0°-60°	724.0	100.0
0°-90°	724.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	724.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	803	
5°	762	71
15°	674	188
25°	530	241
35°	372	208
45°	0	15
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1305019

CATALOG NUMBER: P3DUS09R70B2750DE010 E3CBUS1MW_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	803.0
2.5°	790.4
5°	761.6
7.5°	736.6
10°	720.3
12.5°	700.3
15°	673.9
17.5°	642.6
20°	606.3
22.5°	566.2
25°	529.9
27.5°	483.5
30°	437.2
32.5°	418.4
35°	372.0
37.5°	270.6
40°	135.3
42.5°	17.5
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)