

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1305024

Luminaire Tested: P3DUS13R15B2750DE010 E3CBUS1MW_3000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1305024
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-85)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3DUS13R15B2750DE010 E3CBUS1MW_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R15 optic, 3000K CCT AND, 90CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 978.0 lumens
Efficiency: N/A
Efficacy: 51.2 lumens/watt
Spacing Criteria (0/90/45): 0.29 / 0.29 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1305024

CATALOG NUMBER: P3DUS13R15B2750DE010 E3CBUS1MW_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1305024

CATALOG NUMBER: P3DUS13R15B2750DE010 E3CBUS1MW_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20				20				20
RC	80				70				50				30				10				0				0				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	102	102	102	102	102	102	102	102	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	100	100	100	100	100	100	100	100	100	100	100	98
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	99	98	98	98	98	98	98	98	98	98	98	98	98	96
3	110	106	103	101	109	105	102	100	103	101	99	101	99	97	98	97	96	96	96	96	96	96	96	96	96	96	96	96	95
4	108	103	100	98	106	102	100	97	101	98	96	99	97	95	97	96	94	94	94	94	94	94	94	94	94	94	94	94	93
5	106	101	98	95	104	100	97	95	99	96	94	97	95	93	96	94	93	93	93	93	93	93	93	93	93	93	93	93	92
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	91	91	91	91	91	91	91	91	91	91	91	90
7	102	97	93	91	101	96	93	91	95	92	90	94	92	90	93	91	90	90	90	90	90	90	90	90	90	90	90	90	89
8	100	95	92	89	99	94	91	89	94	91	89	93	90	89	92	90	88	88	88	88	88	88	88	88	88	88	88	88	88
9	98	93	90	88	97	93	90	88	92	89	88	91	89	87	91	89	87	87	87	87	87	87	87	87	87	87	87	87	86
10	97	92	89	87	96	91	88	86	91	88	86	90	88	86	90	87	86	86	86	86	86	86	86	86	86	86	86	86	85

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2090205
5°	1652164
10°	761954
15°	220682
20°	70893
25°	26614
30°	9976
35°	3078
40°	945
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 52.5°

Luminance: 576 cd/sqm

TEST NUMBER: P1305024

CATALOG NUMBER: P3DUS13R15B2750DE010 E3CBUS1MW_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	582.8	59.6
10°-20°	328.0	33.5
20°-30°	57.5	5.9
30°-40°	8.7	0.9
40°-50°	0.6	0.1
50°-60°	0.3	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	968.4	99.0
0°-40°	977.0	99.9
0°-60°	978.0	100.0
0°-90°	978.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	978.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9532	
5°	7506	583
15°	972	328
25°	110	58
35°	12	9
45°	0	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1305024

CATALOG NUMBER: P3DUS13R15B2750DE010 E3CBUS1MW_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	9532.1
2.5°	9001.7
5°	7505.8
7.5°	5481.2
10°	3422.0
12.5°	1850.6
15°	972.1
17.5°	538.6
20°	303.8
22.5°	177.3
25°	110.0
27.5°	67.3
30°	39.4
32.5°	18.1
35°	11.5
37.5°	6.6
40°	3.3
42.5°	1.6
45°	0.0
47.5°	0.0
50°	0.0
52.5°	1.6
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)