

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1305046

Luminaire Tested: P3DUS13R35B2750DE010 E3CBUS1MW_4000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1305046
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-89)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3DUS13R35B2750DE010 E3CBUS1MW_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R35 optic, 4000K CCT AND, 80CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1073.0 lumens
Efficiency: N/A
Efficacy: 56.2 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 0.55 / 0.5
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1305046

CATALOG NUMBER: P3DUS13R35B2750DE010 E3CBUS1MW_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1305046

CATALOG NUMBER: P3DUS13R35B2750DE010 E3CBUS1MW_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	109	113	111	109	108	107	105	104	103	102	101	100	99	98	97		
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	93		
3	108	103	99	97	106	102	98	96	99	97	94	97	95	93	95	93	92	90		
4	104	99	95	92	103	98	94	92	96	93	90	94	92	89	92	90	89	87		
5	101	95	91	88	100	94	91	88	93	90	87	91	89	86	90	88	86	85		
6	98	92	88	85	97	91	87	85	90	87	84	89	86	83	88	85	83	82		
7	95	89	85	82	94	88	84	82	87	84	81	86	83	81	85	83	80	79		
8	93	86	82	79	92	86	82	79	85	81	79	84	81	78	83	80	78	77		
9	90	83	79	77	89	83	79	76	82	79	76	82	78	76	81	78	76	75		
10	88	81	77	74	87	81	77	74	80	76	74	79	76	74	79	76	74	73		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	786034
5°	762600
10°	680014
15°	480389
20°	231720
25°	75101
30°	21117
35°	8486
40°	2376
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 0 cd/sqm

TEST NUMBER: P1305046

CATALOG NUMBER: P3DUS13R35B2750DE010 E3CBUS1MW_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	318.2	29.7
10°-20°	559.3	52.1
20°-30°	171.9	16.0
30°-40°	22.3	2.1
40°-50°	1.4	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1049.3	97.8
0°-40°	1071.6	99.9
0°-60°	1073.0	100.0
0°-90°	1073.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1073.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3585	
5°	3464	318
15°	2116	559
25°	310	172
35°	32	22
45°	0	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1305046

CATALOG NUMBER: P3DUS13R35B2750DE010 E3CBUS1MW_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	3584.6
2.5°	3556.3
5°	3464.5
7.5°	3312.6
10°	3054.0
12.5°	2650.1
15°	2116.1
17.5°	1535.3
20°	993.0
22.5°	575.7
25°	310.4
27.5°	163.5
30°	83.4
32.5°	50.1
35°	31.7
37.5°	20.0
40°	8.3
42.5°	3.3
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)