

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1305060

Luminaire Tested: P3DUS13R50B2750DE010 E3CBUS1MW_3500K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1305060
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-91)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3DUS13R50B2750DE010 E3CBUS1MW_3500K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R50 optic, 3500K CCT AND, 80CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1126.0 lumens
Efficiency: N/A
Efficacy: 59.0 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 0.71 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1305060

CATALOG NUMBER: P3DUS13R50B2750DE010 E3CBUS1MW_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1305060

CATALOG NUMBER: P3DUS13R50B2750DE010 E3CBUS1MW_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95
2	110	105	102	99	108	104	101	98	101	98	96	98	96	94	95	93	92	90	90	90
3	105	100	95	92	103	98	94	91	96	93	90	93	91	89	91	89	87	86	86	86
4	101	95	90	86	99	93	89	86	91	88	85	89	86	84	88	85	83	82	82	82
5	97	90	85	81	95	89	84	81	87	83	80	86	82	79	84	81	79	77	77	77
6	93	85	80	77	92	85	80	76	83	79	76	82	78	75	81	78	75	74	74	74
7	89	81	76	73	88	81	76	73	80	75	72	79	75	72	77	74	72	70	70	70
8	86	78	73	69	85	77	72	69	76	72	69	75	71	69	74	71	68	67	67	67
9	83	74	69	66	82	74	69	66	73	69	66	72	68	65	71	68	65	64	64	64
10	79	71	66	63	79	71	66	63	70	66	63	69	65	63	69	65	62	61	61	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	453977
5°	443098
10°	418585
15°	367880
20°	276734
25°	204592
30°	124120
35°	41037
40°	7242
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 0 cd/sqm

TEST NUMBER: P1305060

CATALOG NUMBER: P3DUS13R50B2750DE010 E3CBUS1MW_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.9	16.7
10°-20°	440.7	39.1
20°-30°	377.9	33.6
30°-40°	116.6	10.4
40°-50°	2.9	0.3
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1006.5	89.4
0°-40°	1123.1	99.7
0°-60°	1126.0	100.0
0°-90°	1126.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1126.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2070	
5°	2013	188
15°	1620	441
25°	846	378
35°	153	117
45°	0	3
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1305060

CATALOG NUMBER: P3DUS13R50B2750DE010 E3CBUS1MW_3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2070.3
2.5°	2055.1
5°	2013.0
7.5°	1954.0
10°	1879.9
12.5°	1762.0
15°	1620.5
17.5°	1440.3
20°	1185.9
22.5°	970.3
25°	845.6
27.5°	687.3
30°	490.2
32.5°	298.2
35°	153.3
37.5°	69.1
40°	25.3
42.5°	3.4
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)