

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1305067

Luminaire Tested: P3DUS13R55B2750DE010 E3CBUS1MW_5000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1305067
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-92)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3DUS13R55B2750DE010 E3CBUS1MW_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R55 optic, 5000K CCT AND, 80CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1176.0 lumens
Efficiency: N/A
Efficacy: 61.6 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1305067

CATALOG NUMBER: P3DUS13R55B2750DE010 E3CBUS1MW_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1305067

CATALOG NUMBER: P3DUS13R55B2750DE010 E3CBUS1MW_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	98	98
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	98	98	97	95	95	93
2	109	105	102	99	107	103	100	97	100	98	95	97	95	93	95	93	91	90	91	88
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	87	85	87	84
4	100	94	89	85	99	93	88	85	91	87	84	89	86	83	87	84	82	81	83	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76	80	76
6	92	84	79	76	91	84	79	75	82	78	75	81	77	74	80	76	74	73	76	73
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69	73	70
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65	70	66
9	81	73	68	64	80	72	67	64	72	67	64	71	67	64	70	66	64	62	67	63
10	78	70	64	61	77	69	64	61	68	64	61	68	64	61	67	63	61	59	67	63

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	390736
5°	373012
10°	372961
15°	361228
20°	326835
25°	253079
30°	126779
35°	38173
40°	8158
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 0 cd/sqm

TEST NUMBER: P1305067

CATALOG NUMBER: P3DUS13R55B2750DE010 E3CBUS1MW_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.8	13.8
10°-20°	441.4	37.5
20°-30°	454.4	38.6
30°-40°	114.5	9.7
40°-50°	3.9	0.3
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1057.6	89.9
0°-40°	1172.1	99.7
0°-60°	1176.0	100.0
0°-90°	1176.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1176.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1782	
5°	1695	162
15°	1591	441
25°	1046	454
35°	143	115
45°	0	4
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1305067

CATALOG NUMBER: P3DUS13R55B2750DE010 E3CBUS1MW_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1781.9
2.5°	1746.2
5°	1694.6
7.5°	1683.9
10°	1675.0
12.5°	1642.9
15°	1591.2
17.5°	1511.0
20°	1400.6
22.5°	1250.9
25°	1046.0
27.5°	785.8
30°	500.7
32.5°	290.4
35°	142.6
37.5°	67.7
40°	28.5
42.5°	7.1
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)