

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1305071

Luminaire Tested: P3DUS13R60B2750DE010 E3CBUS1MW_4000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1305071
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-93)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3DUS13R60B2750DE010 E3CBUS1MW_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R60 optic, 4000K CCT AND, 80CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1054.0 lumens
Efficiency: N/A
Efficacy: 55.2 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.84
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1305071

CATALOG NUMBER: P3DUS13R60B2750DE010 E3CBUS1MW_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1305071

CATALOG NUMBER: P3DUS13R60B2750DE010 E3CBUS1MW_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94		
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	89		
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83		
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78		
5	94	86	81	77	93	86	80	77	84	79	76	82	78	75	81	77	75	73		
6	90	82	76	72	89	81	76	72	79	75	71	78	74	71	77	73	70	69		
7	86	77	71	68	85	76	71	67	75	70	67	74	70	67	73	69	66	65		
8	82	73	67	63	81	72	67	63	71	67	63	70	66	63	69	66	63	61		
9	78	69	64	60	77	69	63	60	68	63	60	67	63	59	66	62	59	58		
10	75	66	60	57	74	65	60	56	64	60	56	64	59	56	63	59	56	55		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	296862
5°	288069
10°	290665
15°	280433
20°	237227
25°	192640
30°	142427
35°	98752
40°	35352
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 0 cd/sqm

TEST NUMBER: P1305071

CATALOG NUMBER: P3DUS13R60B2750DE010 E3CBUS1MW_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.0	11.9
10°-20°	337.7	32.0
20°-30°	359.7	34.1
30°-40°	218.5	20.7
40°-50°	13.0	1.2
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	822.5	78.0
0°-40°	1041.0	98.8
0°-60°	1054.0	100.0
0°-90°	1054.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1054.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1354	
5°	1309	125
15°	1235	338
25°	796	360
35°	369	219
45°	0	13
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1305071

CATALOG NUMBER: P3DUS13R60B2750DE010 E3CBUS1MW_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1353.8
2.5°	1333.8
5°	1308.7
7.5°	1302.0
10°	1305.4
12.5°	1290.4
15°	1235.3
17.5°	1138.4
20°	1016.6
22.5°	899.7
25°	796.2
27.5°	676.1
30°	562.5
32.5°	474.1
35°	368.9
37.5°	240.4
40°	123.5
42.5°	10.0
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)