

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1306706

Luminaire Tested: P3SQAS09R259027DE010 E3SQCD1MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1306706
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3SQAS09R259027DE010 E3SQCD1MMS
Description: 3in Adjustable LED luminaire with, R25 optic, 2700K CCT AND, 90CRI , E3SQCD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 891.0 lumens
Efficiency: N/A
Efficacy: 80.3 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.45 / 0.41
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1306706

CATALOG NUMBER: P3SQAS09R259027DE010 E3SQCD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1306706

CATALOG NUMBER: P3SQAS09R259027DE010 E3SQCD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	110	113	111	110	108	107	106	105		103	103	102		100
2	112	108	105	103	110	107	104	102	104	102	100		101	99	98		98
3	108	104	101	98	107	103	100	97	100	98	96		98	96	94		96
4	105	100	97	94	104	99	96	93	97	95	92		96	93	91		94
5	103	97	93	90	101	96	93	90	95	92	89		93	91	89		92
6	100	94	90	87	99	93	90	87	92	89	87		91	88	86		90
7	97	91	87	85	96	91	87	84	90	86	84		89	86	84		88
8	95	89	85	82	94	88	85	82	87	84	82		87	84	82		86
9	93	86	83	80	92	86	82	80	85	82	80		85	82	80		84
10	91	84	81	78	90	84	80	78	83	80	78		83	80	78		82

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	737199	737199	737199
5°	679749	681287	682705
10°	527786	529692	532560
15°	260814	271797	271904
20°	87826	93709	89585
25°	36371	40400	37416
30°	14279	17938	14418
35°	3742	7338	3890
40°	1394	2923	1394
45°	170	828	170
50°	0	188	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 828 cd/sqm

TEST NUMBER: P1306706

CATALOG NUMBER: P3SQAS09R259027DE010 E3SQCD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	346.8	38.9
10°-20°	419.5	47.1
20°-30°	102.4	11.5
30°-40°	19.9	2.2
40°-50°	2.3	0.3
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	868.8	97.5
0°-40°	888.7	99.7
0°-60°	891.0	100.0
0°-90°	891.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	891.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4280	4280	4280	4280	4280	
5°	3932	3937	3941	3958	3949	346
15°	1463	1498	1524	1539	1525	412
25°	191	202	213	204	197	97
35°	18	25	35	25	18	16
45°	1	2	3	2	1	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	

TEST NUMBER: P1306706

CATALOG NUMBER: P3SQAS09R259027DE010 E3SQCD1MMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4280.5	4280.5	4280.5	4280.5	4280.5
1°	4264.1	4266.8	4267.5	4271.6	4263.4
2°	4225.1	4225.8	4227.9	4236.1	4228.6
3°	4153.4	4158.2	4158.8	4169.8	4171.8
4°	4055.6	4058.3	4063.8	4082.3	4065.9
5°	3931.9	3937.4	3940.8	3957.9	3949.0
6°	3778.8	3780.1	3787.7	3807.5	3795.2
7°	3622.9	3622.2	3622.9	3638.6	3635.2
8°	3434.9	3431.5	3442.5	3461.6	3474.6
9°	3238.7	3243.5	3250.4	3268.8	3253.8
10°	3018.0	3030.9	3028.9	3030.3	3045.3
11°	2763.7	2767.8	2768.5	2782.8	2780.8
12°	2464.9	2464.9	2487.5	2510.7	2503.2
13°	2163.5	2184.7	2169.6	2174.4	2204.5
14°	1812.1	1828.5	1849.1	1868.2	1853.2
15°	1462.8	1497.7	1524.4	1539.4	1525.0
17.5°	838.1	849.7	872.2	875.0	866.1
20°	479.2	493.5	511.3	505.8	488.8
22.5°	301.5	305.6	323.3	314.4	310.3
25°	191.4	201.7	212.6	203.7	196.9
27.5°	118.9	125.8	137.4	127.8	120.3
30°	71.8	77.9	90.2	77.2	72.5
32.5°	37.6	46.5	56.7	47.2	37.6
35°	17.8	25.3	34.9	25.3	18.5
37.5°	10.9	13.7	21.2	13.7	10.9
40°	6.2	8.9	13.0	8.9	6.2
42.5°	2.7	4.8	6.2	4.8	3.4
45°	0.7	2.1	3.4	2.1	0.7
47.5°	0.0	0.0	2.1	0.7	0.0
50°	0.0	0.0	0.7	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1306706

CATALOG NUMBER: P3SQAS09R259027DE010 E3SQCD1MMS

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)