

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1308872

Luminaire Tested: P3SQAS05R609035DE010 E3SQCD1MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1308872
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3SQAS05R609035DE010 E3SQCD1MMS
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 90CRI , E3SQCD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 646.0 lumens
Efficiency: N/A
Efficacy: 89.7 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.93 / 0.9
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1308872

CATALOG NUMBER: P3SQAS05R609035DE010 E3SQCD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1308872

CATALOG NUMBER: P3SQAS05R609035DE010 E3SQCD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98
2	108	104	100	97	106	102	98	95	99	96	93		96	93	91		93
3	103	97	92	88	101	96	91	88	93	89	86		91	88	85		88
4	98	91	86	81	96	90	85	81	88	83	80		86	82	79		84
5	93	85	80	76	92	84	79	75	83	78	75		81	77	74		79
6	89	80	74	70	87	79	74	70	78	73	70		77	72	69		75
7	85	76	70	66	83	75	69	65	74	69	65		72	68	65		71
8	81	71	66	62	79	71	65	61	70	65	61		69	64	61		68
9	77	67	62	58	76	67	61	58	66	61	57		65	61	57		64
10	73	64	58	54	72	63	58	54	63	58	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	125550	125550	125550
5°	118890	119530	119702
10°	123430	123238	123972
15°	125468	125290	126199
20°	111028	111028	111230
25°	95146	92315	93094
30°	76126	73362	74475
35°	47221	48188	47116
40°	20728	22819	21313
45°	244	7404	633
50°	0	831	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 7404 cd/sqm

TEST NUMBER: P1308872

CATALOG NUMBER: P3SQAS05R609035DE010 E3SQCD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.6	10.3
10°-20°	193.0	29.9
20°-30°	224.0	34.7
30°-40°	141.1	21.8
40°-50°	21.2	3.3
50°-60°	0.1	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	483.6	74.9
0°-40°	624.7	96.7
0°-60°	646.0	100.0
0°-90°	646.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	646.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	729	729	729	729	729	
5°	688	690	691	693	692	66
15°	704	701	703	707	708	193
25°	501	495	486	488	490	228
35°	225	225	229	225	224	140
45°	1	10	30	13	3	14
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	

TEST NUMBER: P1308872

CATALOG NUMBER: P3SQAS05R609035DE010 E3SQCD1MMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	729.0	729.0	729.0	729.0	729.0
1°	723.3	725.4	725.4	725.9	725.4
2°	713.5	716.6	716.6	718.1	717.1
3°	703.7	706.3	706.8	708.9	708.4
4°	692.9	697.0	698.6	699.6	699.1
5°	687.7	690.3	691.4	692.9	692.4
6°	685.7	687.7	688.8	690.3	690.3
7°	687.2	688.8	690.3	691.4	690.3
8°	691.9	693.4	693.4	695.5	693.9
9°	698.6	699.1	699.1	701.7	700.1
10°	705.8	704.7	704.7	708.4	708.9
11°	712.0	710.9	710.4	714.0	715.1
12°	715.6	713.5	713.5	718.1	718.7
13°	716.1	713.5	713.5	718.1	719.7
14°	712.0	708.9	709.4	714.5	716.1
15°	703.7	701.1	702.7	707.3	707.8
17.5°	664.6	663.0	664.1	667.1	667.7
20°	605.8	604.8	605.8	605.8	606.9
22.5°	547.6	545.0	539.9	543.0	543.5
25°	500.7	495.1	485.8	487.9	489.9
27.5°	449.2	442.0	432.2	434.8	435.3
30°	382.8	379.2	368.9	371.4	374.5
32.5°	295.7	305.5	299.3	298.8	299.3
35°	224.6	225.1	229.2	224.6	224.1
37.5°	157.1	157.6	160.7	155.6	156.1
40°	92.2	98.9	101.5	99.4	94.8
42.5°	28.8	51.0	57.7	50.0	31.9
45°	1.0	9.8	30.4	12.9	2.6
47.5°	0.0	0.5	14.4	1.0	0.0
50°	0.0	0.0	3.1	0.0	0.0
52.5°	0.0	0.0	0.5	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1308872

CATALOG NUMBER: P3SQAS05R609035DE010 E3SQCD1MMS

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)