

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1310664

Luminaire Tested: P3SQAS24R209040D010 E3SQPH1MW

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1310664  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3SQAS24R209040D010 E3SQPH1MW  
Description: 3in Adjustable LED luminaire with, R20 optic, 4000K CCT AND, 90CRI , E3SQPH1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2333.0 lumens  
Efficiency: N/A  
Efficacy: 81.0 lumens/watt  
Spacing Criteria (0/90/45): 0.35 / 0.36 / 0.33  
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1310664

CATALOG NUMBER: P3SQAS24R209040D010 E3SQPH1MW

### Luminous Intensity Polar Plot



TEST NUMBER: P1310664

CATALOG NUMBER: P3SQAS24R209040D010 E3SQPH1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 116 | 114 | 112 | 111 | 113 | 112 | 110 | 109 | 108 | 107 | 106 |  | 104 | 103 | 102 |  | 101 |
| 2   | 113 | 109 | 107 | 105 | 111 | 108 | 106 | 104 | 105 | 103 | 101 |  | 102 | 101 | 99  |  | 99  |
| 3   | 110 | 106 | 103 | 100 | 108 | 105 | 102 | 100 | 102 | 100 | 98  |  | 100 | 98  | 97  |  | 98  |
| 4   | 107 | 103 | 99  | 97  | 106 | 102 | 99  | 96  | 100 | 97  | 95  |  | 98  | 96  | 94  |  | 96  |
| 5   | 105 | 100 | 97  | 94  | 104 | 99  | 96  | 94  | 98  | 95  | 93  |  | 96  | 94  | 92  |  | 95  |
| 6   | 103 | 98  | 94  | 92  | 102 | 97  | 94  | 91  | 96  | 93  | 91  |  | 95  | 92  | 90  |  | 93  |
| 7   | 101 | 95  | 92  | 90  | 100 | 95  | 92  | 89  | 94  | 91  | 89  |  | 93  | 90  | 89  |  | 92  |
| 8   | 99  | 93  | 90  | 88  | 98  | 93  | 90  | 88  | 92  | 89  | 87  |  | 91  | 89  | 87  |  | 91  |
| 9   | 97  | 92  | 88  | 86  | 96  | 91  | 88  | 86  | 91  | 88  | 86  |  | 90  | 87  | 86  |  | 89  |
| 10  | 95  | 90  | 87  | 85  | 95  | 90  | 87  | 85  | 89  | 86  | 84  |  | 88  | 86  | 84  |  | 88  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°      | 45°     | 90°     |
|-----|---------|---------|---------|
| 0°  | 2991490 | 2991490 | 2991490 |
| 5°  | 2584287 | 2608369 | 2618068 |
| 10° | 1555710 | 1570243 | 1648396 |
| 15° | 538103  | 525498  | 567380  |
| 20° | 141324  | 132948  | 133333  |
| 25° | 30803   | 37131   | 42262   |
| 30° | 13225   | 13225   | 13642   |
| 35° | 7422    | 6560    | 7001    |
| 40° | 3260    | 3732    | 4204    |
| 45° | 1023    | 1510    | 1510    |
| 50° | 563     | 563     | 563     |
| 55° | 0       | 0       | 0       |
| 60° | 0       | 0       | 0       |
| 65° | 0       | 0       | 0       |
| 70° | 0       | 0       | 0       |
| 75° | 0       | 0       | 0       |
| 80° | 0       | 0       | 0       |
| 85° | 0       | 0       | 0       |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 1510 cd/sqm

TEST NUMBER: P1310664

CATALOG NUMBER: P3SQAS24R209040D010 E3SQPH1MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 1242.4 | 53.3      |
| 10°-20°   | 945.9  | 40.5      |
| 20°-30°   | 117.0  | 5.0       |
| 30°-40°   | 22.1   | 0.9       |
| 40°-50°   | 5.3    | 0.2       |
| 50°-60°   | 0.3    | 0.0       |
| 60°-70°   | 0.0    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 2305.2 | 98.8      |
| 0°-40°    | 2327.3 | 99.8      |
| 0°-60°    | 2333.0 | 100.0     |
| 0°-90°    | 2333.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2333.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°    | 22.5° | 45°   | 67.5° | 90°   | Flux |
|-----|-------|-------|-------|-------|-------|------|
| 0°  | 17370 | 17370 | 17370 | 17370 | 17370 |      |
| 5°  | 14948 | 14938 | 15088 | 15077 | 15144 | 1233 |
| 15° | 3018  | 2910  | 2947  | 3124  | 3182  | 945  |
| 25° | 162   | 185   | 195   | 204   | 222   | 112  |
| 35° | 35    | 35    | 31    | 33    | 33    | 23   |
| 45° | 4     | 6     | 6     | 6     | 6     | 4    |
| 55° | 0     | 0     | 0     | 0     | 0     | 1    |
| 65° | 0     | 0     | 0     | 0     | 0     | 0    |
| 75° | 0     | 0     | 0     | 0     | 0     | 0    |
| 85° | 0     | 0     | 0     | 0     | 0     | 0    |
| 90° | 0     | 0     | 0     | 0     | 0     |      |

TEST NUMBER: P1310664

CATALOG NUMBER: P3SQAS24R209040D010 E3SQPH1MW

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      | 22.5°   | 45°     | 67.5°   | 90°     |
|-------|---------|---------|---------|---------|---------|
| 0°    | 17369.9 | 17369.9 | 17369.9 | 17369.9 | 17369.9 |
| 1°    | 17288.8 | 17268.0 | 17284.7 | 17249.3 | 17322.1 |
| 2°    | 17012.4 | 16991.6 | 16991.6 | 16970.8 | 16981.2 |
| 3°    | 16496.9 | 16530.2 | 16509.4 | 16465.7 | 16521.8 |
| 4°    | 15794.4 | 15831.8 | 15865.0 | 15867.1 | 15875.4 |
| 5°    | 14948.4 | 14938.0 | 15087.7 | 15077.3 | 15143.8 |
| 6°    | 13984.0 | 13971.6 | 14036.0 | 14144.1 | 14277.1 |
| 7°    | 12924.0 | 12772.3 | 12944.8 | 13163.0 | 13341.8 |
| 8°    | 11552.2 | 11591.7 | 11710.2 | 11967.9 | 12111.3 |
| 9°    | 10388.3 | 10157.5 | 10409.0 | 10716.7 | 10872.5 |
| 10°   | 8895.9  | 8708.8  | 8979.0  | 9303.3  | 9425.9  |
| 12.5° | 5599.4  | 5437.3  | 5524.6  | 5865.5  | 5919.5  |
| 15°   | 3018.0  | 2909.9  | 2947.3  | 3124.0  | 3182.2  |
| 17.5° | 1540.2  | 1442.5  | 1421.7  | 1533.9  | 1546.4  |
| 20°   | 771.1   | 748.3   | 725.4   | 735.8   | 727.5   |
| 22.5° | 357.5   | 388.7   | 384.5   | 363.7   | 388.7   |
| 25°   | 162.1   | 185.0   | 195.4   | 203.7   | 222.4   |
| 27.5° | 99.8    | 95.6    | 110.2   | 118.5   | 120.6   |
| 30°   | 66.5    | 64.4    | 66.5    | 68.6    | 68.6    |
| 32.5° | 47.8    | 45.7    | 43.6    | 43.6    | 45.7    |
| 35°   | 35.3    | 35.3    | 31.2    | 33.3    | 33.3    |
| 37.5° | 24.9    | 24.9    | 22.9    | 24.9    | 24.9    |
| 40°   | 14.5    | 16.6    | 16.6    | 16.6    | 18.7    |
| 42.5° | 8.3     | 10.4    | 10.4    | 10.4    | 10.4    |
| 45°   | 4.2     | 6.2     | 6.2     | 6.2     | 6.2     |
| 47.5° | 2.1     | 2.1     | 2.1     | 4.2     | 4.2     |
| 50°   | 2.1     | 2.1     | 2.1     | 2.1     | 2.1     |
| 52.5° | 2.1     | 0.0     | 0.0     | 0.0     | 2.1     |
| 55°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 57.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 60°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 62.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 65°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 67.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 70°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 72.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 75°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 77.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 80°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 82.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 85°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 87.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |

(END OF REPORT)