

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1311072

Luminaire Tested: P3SQAS05R609050DE010 E3SQCA301MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1311072
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-55)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3SQAS05R609050DE010 E3SQCA301MMS
Description: 3in Adjustable LED luminaire with, R60 optic, 5000K CCT AND, 90CRI , E3SQCA301MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 499.9 lumens
Efficiency: N/A
Efficacy: 69.4 lumens/watt
Spacing Criteria (0/90/45): 1.74 / 0.65 / 1.25
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1311072

CATALOG NUMBER: P3SQAS05R609050DE010 E3SQCA301MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1311072

CATALOG NUMBER: P3SQAS05R609050DE010 E3SQCA301MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96	94	93	91
2	105	100	95	91	103	98	93	90	94	91	88		91	88	86		89	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82	78	76	74
4	92	83	76	71	90	82	75	71	79	74	70		77	73	69		75	71	68	66
5	86	76	69	64	84	75	68	63	73	67	63		71	66	62		69	65	61	60
6	80	69	62	57	79	69	62	57	67	61	56		65	60	56		64	59	56	54
7	75	64	57	52	74	63	56	51	62	56	51		60	55	51		59	54	50	49
8	70	59	52	47	69	58	51	47	57	51	46		56	50	46		55	50	46	44
9	66	55	47	43	65	54	47	43	53	47	42		52	46	42		51	46	42	40
10	62	51	44	39	61	50	43	39	49	43	39		48	43	39		48	42	39	37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	52976	52976	52976	52976	52976
5°	76361	71918	52901	27246	17513
10°	92371	80410	49106	3253	1906
15°	118390	87348	40705	2140	1765
20°	131024	100123	27290	1210	202
25°	136268	109227	13416	95	0
30°	146524	108521	3699	0	0
35°	148811	93454	0	0	0
40°	161219	87140	0	0	0
45°	161042	76916	0	0	0
50°	117916	18621	0	0	0
55°	23000	0	0	0	0
60°	0	0	0	0	0
65°	0	204	204	0	0
70°	0	252	252	0	0
75°	0	333	333	0	0
80°	0	496	496	496	0
85°	0	988	988	988	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 5°

Vertical Angle: 45°

Luminance: 161310 cd/sqm

TEST NUMBER: P1311072

CATALOG NUMBER: P3SQAS05R609050DE010 E3SQCA301MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	26.4	5.3
10°-20°	75.2	15.1
20°-30°	119.9	24.0
30°-40°	138.6	27.7
40°-50°	110.1	22.0
50°-60°	29.0	5.8
60°-70°	0.2	0.0
70°-80°	0.3	0.1
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	221.5	44.3
0°-40°	360.1	72.0
0°-60°	499.2	99.8
0°-90°	499.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	499.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	308	308	308	308	308	
5°	442	416	306	158	101	45
15°	664	490	228	12	10	185
25°	717	575	71	0	0	334
35°	708	444	0	0	0	450
45°	661	316	0	0	0	471
55°	77	0	0	0	0	116
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P1311072

CATALOG NUMBER: P3SQAS05R609050DE010 E3SQCA301MMS

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	307.6	307.6	307.6	307.6	307.6	307.6	307.6	307.6	307.6	307.6	307.6
2.5°	387.0	390.8	389.2	387.6	383.7	382.1	382.1	377.7	370.6	369.5	364.6
5°	441.7	442.8	442.8	441.7	439.0	434.6	433.5	429.2	422.6	416.0	409.4
7.5°	489.4	488.8	485.5	483.3	478.4	472.4	466.9	460.9	451.0	442.3	433.0
10°	528.2	529.9	527.1	521.7	515.1	506.9	498.1	487.7	472.9	459.8	447.8
12.5°	583.0	582.4	575.3	566.0	550.1	534.8	521.1	509.6	491.6	475.7	460.9
15°	664.0	662.9	656.3	648.1	625.1	602.1	578.6	546.3	516.2	489.9	469.1
17.5°	700.7	702.8	697.4	693.0	679.9	664.5	643.7	611.4	564.9	517.3	473.5
20°	714.9	717.6	713.8	713.2	707.2	700.1	683.1	648.1	602.7	546.3	492.1
22.5°	714.3	716.5	714.9	722.0	729.1	725.3	704.5	669.5	622.9	568.7	507.4
25°	717.1	715.4	709.4	719.8	730.2	726.9	716.5	686.4	635.5	574.8	512.9
27.5°	729.7	717.6	705.6	718.7	723.6	724.7	718.7	683.1	633.3	568.2	502.0
30°	736.8	723.6	713.8	724.7	724.7	730.8	718.2	677.7	614.7	545.7	472.9
32.5°	723.6	720.9	729.7	740.6	743.4	743.4	715.4	659.6	583.5	499.8	426.4
35°	707.8	714.3	739.5	744.4	744.4	732.4	698.5	627.9	537.0	444.5	391.9
37.5°	706.1	716.5	744.4	738.4	728.6	706.1	656.9	572.6	470.8	413.3	366.2
40°	717.1	726.9	743.4	721.5	697.9	662.9	603.8	500.3	430.8	387.6	335.0
42.5°	710.5	719.8	720.4	688.1	654.7	607.1	528.8	441.7	401.8	354.7	299.4
45°	661.2	662.3	660.1	625.7	591.2	541.9	458.7	412.7	370.0	315.8	220.0
47.5°	499.8	497.6	505.8	495.9	497.6	468.0	416.6	378.8	327.9	221.7	66.8
50°	440.1	437.4	429.2	420.4	411.6	397.4	373.3	332.8	236.5	69.5	2.2
52.5°	235.9	249.1	274.8	314.2	329.0	327.9	309.8	246.3	74.4	0.5	0.0
55°	76.6	75.5	84.3	99.6	136.8	157.6	164.2	83.8	1.6	0.0	0.0
57.5°	0.0	0.0	0.0	1.6	5.5	14.2	18.6	1.1	0.0	0.5	0.0
60°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.5	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.5	0.5
65°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.5	0.5	0.5
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.5	0.5	0.5	0.5
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.5	0.5	0.5	0.5
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.5	0.5	0.5
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.5	0.5	0.5	0.5	0.5
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.5	0.5	0.5	0.5	0.5
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.5	0.5	0.5	0.5	0.5
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.5	0.5	0.5	0.5
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.5	0.5	0.5	0.5
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.5	0.5	0.5	0.5	0.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1311072

CATALOG NUMBER: P3SQAS05R609050DE010 E3SQCA301MMS

CANDELA DISTRIBUTION (continued):

	55°	60°	67.5°	90°	112.5°	135°	157.5°	180°
0°	307.6	307.6	307.6	307.6	307.6	307.6	307.6	307.6
2.5°	358.0	350.3	341.6	310.4	273.7	238.1	212.4	205.8
5°	399.0	385.9	367.3	306.0	226.1	157.6	112.8	101.3
7.5°	420.4	408.9	389.2	297.2	175.2	77.7	29.0	19.7
10°	433.5	419.8	398.0	280.8	114.4	18.6	10.4	10.9
12.5°	442.8	427.0	402.3	257.3	58.0	9.3	13.1	13.7
15°	446.7	429.7	401.8	228.3	20.8	12.0	11.5	9.9
17.5°	444.5	423.1	394.7	186.7	7.1	11.5	6.0	4.9
20°	441.7	417.7	383.2	148.9	6.0	6.6	2.2	1.1
22.5°	450.5	408.4	367.3	106.7	6.0	2.2	0.0	0.0
25°	451.6	404.5	347.0	70.6	2.7	0.5	0.0	0.0
27.5°	440.6	382.1	315.8	41.6	0.0	0.0	0.0	0.0
30°	405.6	354.2	282.5	18.6	0.0	0.0	0.0	0.0
32.5°	371.1	323.0	245.2	4.4	0.0	0.0	0.0	0.0
35°	343.8	290.7	204.2	0.0	0.0	0.0	0.0	0.0
37.5°	309.8	252.3	152.2	0.0	0.0	0.0	0.0	0.0
40°	274.2	203.6	76.1	0.0	0.0	0.0	0.0	0.0
42.5°	214.0	96.9	7.7	0.0	0.0	0.0	0.0	0.0
45°	82.1	8.8	0.0	0.0	0.0	0.0	0.0	0.0
47.5°	4.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60°	0.5	0.5	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	0.5	0.5	0.5	0.5	0.0	0.0	0.0	0.0
65°	0.5	0.5	0.5	0.5	0.0	0.0	0.0	0.0
67.5°	0.5	0.5	0.5	0.5	0.5	0.0	0.0	0.0
70°	0.5	0.5	0.5	0.5	0.5	0.0	0.0	0.0
72.5°	0.5	0.5	0.5	0.5	0.5	0.0	0.0	0.0
75°	0.5	0.5	0.5	0.5	0.5	0.0	0.0	0.0
77.5°	0.5	0.5	0.5	0.5	0.5	0.0	0.0	0.0
80°	0.5	0.5	0.5	0.5	0.5	0.5	0.0	0.0
82.5°	0.5	0.5	0.5	0.5	0.5	0.0	0.0	0.0
85°	0.5	0.5	0.5	0.5	0.5	0.5	0.0	0.0
87.5°	0.5	0.5	0.5	0.5	0.5	0.5	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)