

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1311417

Luminaire Tested: P3SQAS17R129050DE010 E3SQCD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1311417
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-24)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3SQAS17R129050DE010 E3SQCD1MMS
Description: 3in Adjustable LED luminaire with, R12 optic, 5000K CCT AND, 90CRI , E3SQCD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1464.0 lumens
Efficiency: N/A
Efficacy: 63.9 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.22
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 22.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1311417

CATALOG NUMBER: P3SQAS17R129050DE010 E3SQCD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1311417

CATALOG NUMBER: P3SQAS17R129050DE010 E3SQCD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	116	114	113	111	114	112	111	109	108	107	106		104	104	103		101	101	100	98
2	113	110	108	106	111	108	106	104	105	104	102		103	101	100		100	99	98	97
3	110	107	104	102	109	105	103	101	103	101	99		101	99	98		99	98	96	95
4	108	104	101	98	107	103	100	98	101	99	97		99	97	96		98	96	95	94
5	106	102	98	96	105	101	98	96	99	97	95		98	96	94		97	95	93	92
6	104	99	96	94	103	99	96	94	98	95	93		96	94	93		95	93	92	91
7	102	98	94	92	101	97	94	92	96	93	92		95	93	91		94	92	91	90
8	101	96	93	91	100	95	93	90	95	92	90		94	92	90		93	91	90	89
9	99	94	91	89	98	94	91	89	93	91	89		93	90	89		92	90	88	88
10	98	93	90	88	97	93	90	88	92	90	88		91	89	88		91	89	87	87

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3714532
5°	2400065
10°	677186
15°	191474
20°	80055
25°	35459
30°	18097
35°	9566
40°	4092
45°	1120
50°	1232
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 50°

Luminance: 1232 cd/sqm

TEST NUMBER: P1311417

CATALOG NUMBER: P3SQAS17R129050DE010 E3SQCD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	978.1	66.8
10°-20°	354.9	24.2
20°-30°	95.0	6.5
30°-40°	29.9	2.0
40°-50°	5.6	0.4
50°-60°	0.5	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1428.0	97.5
0°-40°	1457.9	99.6
0°-60°	1464.0	100.0
0°-90°	1464.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1464.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	21568	
5°	13883	978
15°	1074	355
25°	187	95
35°	46	30
45°	5	6
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1311417

CATALOG NUMBER: P3SQAS17R129050DE010 E3SQCD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	21568.2
1°	21204.2
2°	20180.4
3°	18428.5
4°	16253.5
5°	13882.8
6°	11412.0
7°	9200.6
8°	7080.2
9°	5269.2
10°	3872.3
11°	2853.0
12°	2147.7
13°	1665.4
14°	1319.6
15°	1073.9
17.5°	682.5
20°	436.8
22.5°	282.1
25°	186.6
27.5°	127.4
30°	91.0
32.5°	63.7
35°	45.5
37.5°	31.9
40°	18.2
42.5°	9.1
45°	4.6
47.5°	4.6
50°	4.6
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1311417

CATALOG NUMBER: P3SQAS17R129050DE010 E3SQCD1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)