

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1314888

Luminaire Tested: P3SQAS02R359740DE010 E3SQPHLD1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1314888
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3SQAS02R359740DE010 E3SQPHLD1MW
Description: 3in Adjustable LED luminaire with, R35 optic, 4000K CCT AND, 97CRI , E3SQPHLD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 183.0 lumens
Efficiency: N/A
Efficacy: 50.8 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.92
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1314888

CATALOG NUMBER: P3SQAS02R359740DE010 E3SQPHLD1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1314888

CATALOG NUMBER: P3SQAS02R359740DE010 E3SQPHLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	107	103	100	108	105	101	99	100	98	95		97	95	93		93	91	90	88
2	103	96	90	85	100	94	89	84	90	86	82		87	84	81		84	81	79	77
3	95	86	79	74	93	85	78	73	82	76	72		79	75	71		77	73	70	68
4	88	78	71	65	86	77	70	64	75	68	64		72	67	63		70	66	62	60
5	82	71	64	58	80	70	63	58	68	62	57		66	61	56		65	60	56	54
6	77	65	58	52	75	64	57	52	63	56	51		61	55	51		60	55	51	49
7	72	60	53	47	71	60	52	47	58	52	47		57	51	46		55	50	46	44
8	68	56	48	43	66	55	48	43	54	47	43		53	47	43		52	46	42	41
9	64	52	45	40	63	51	44	40	50	44	39		49	44	39		48	43	39	37
10	60	49	41	37	59	48	41	37	47	41	37		46	41	36		45	40	36	35

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	23595	23595	23595
5°	23149	23114	23149
10°	21772	21720	21772
15°	19702	19702	19755
20°	17448	17448	17448
25°	15164	15126	15126
30°	13145	13065	13105
35°	11311	11269	11311
40°	9825	9780	9825
45°	8622	8573	8573
50°	7663	7582	7582
55°	6726	6726	6726
60°	6097	6028	6097
65°	5501	5501	5501
70°	4884	4884	4884
75°	4392	4259	4392
80°	3769	3769	3769
85°	2371	2371	2371

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8622 cd/sqm

TEST NUMBER: P1314888

CATALOG NUMBER: P3SQAS02R359740DE010 E3SQPHLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	12.5	6.8
10°-20°	30.8	16.8
20°-30°	36.6	20.0
30°-40°	33.7	18.4
40°-50°	27.3	14.9
50°-60°	20.2	11.0
60°-70°	13.4	7.3
70°-80°	6.9	3.8
80°-90°	1.6	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	79.9	43.7
0°-40°	113.6	62.1
0°-60°	161.1	88.0
0°-90°	183.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	183.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	137	137	137	137	137	
5°	134	134	134	134	134	12
15°	110	110	110	110	111	31
25°	80	80	80	80	80	37
35°	54	54	54	54	54	34
45°	35	35	35	35	35	27
55°	22	22	22	22	22	20
65°	14	14	14	14	14	13
75°	7	7	6	7	7	7
85°	1	1	1	1	1	2
90°	0	0	0	0	0	

TEST NUMBER: P1314888

CATALOG NUMBER: P3SQAS02R359740DE010 E3SQPHLD1MW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	137.0	137.0	137.0	137.0	137.0
1°	137.0	136.7	136.7	136.7	137.0
2°	136.5	136.5	136.5	136.5	136.5
3°	136.0	135.8	135.8	135.8	135.8
4°	135.1	134.9	134.9	134.9	134.9
5°	133.9	133.7	133.7	133.7	133.9
6°	132.5	132.3	132.0	132.0	132.3
7°	131.1	130.6	130.6	130.6	130.6
8°	129.0	128.7	128.7	128.7	128.7
9°	126.8	126.4	126.6	126.6	126.6
10°	124.5	124.2	124.2	124.2	124.5
11°	122.1	121.9	121.9	121.6	121.9
12°	119.3	119.3	119.3	119.3	119.3
13°	116.7	116.4	116.4	116.4	116.7
14°	113.8	113.6	113.6	113.6	113.6
15°	110.5	110.5	110.5	110.5	110.8
17.5°	103.0	102.7	103.0	103.0	103.2
20°	95.2	94.9	95.2	95.2	95.2
22.5°	87.4	87.4	87.1	87.4	87.6
25°	79.8	79.6	79.6	79.8	79.6
27.5°	72.7	72.5	72.5	72.5	72.5
30°	66.1	65.7	65.7	65.9	65.9
32.5°	59.3	59.3	59.5	59.3	59.3
35°	53.8	53.6	53.6	53.8	53.8
37.5°	48.4	48.2	48.2	48.4	48.4
40°	43.7	43.7	43.5	43.7	43.7
42.5°	39.2	39.2	39.2	39.2	39.2
45°	35.4	35.2	35.2	35.2	35.2
47.5°	31.6	31.6	31.6	31.4	31.6
50°	28.6	28.3	28.3	28.3	28.3
52.5°	25.3	25.3	25.3	25.3	25.3
55°	22.4	22.4	22.4	22.4	22.4
57.5°	20.1	19.8	19.8	19.8	19.8
60°	17.7	17.7	17.5	17.7	17.7
62.5°	15.4	15.4	15.4	15.4	15.4
65°	13.5	13.5	13.5	13.5	13.5
67.5°	11.6	11.6	11.6	11.6	11.6
70°	9.7	9.7	9.7	9.7	9.7
72.5°	8.3	8.0	8.0	8.0	8.0
75°	6.6	6.6	6.4	6.6	6.6
77.5°	5.0	5.0	5.0	5.0	5.0
80°	3.8	3.8	3.8	3.5	3.8
82.5°	2.4	2.4	2.4	2.4	2.4
85°	1.2	1.2	1.2	1.2	1.2
87.5°	0.2	0.2	0.2	0.5	0.5



TEST NUMBER: P1314888

CATALOG NUMBER: P3SQAS02R359740DE010 E3SQPHLD1MW

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)