

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1312905

Luminaire Tested: P3SQAS02R259730DE010 E3SQPH1MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1312905
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3SQAS02R259730DE010 E3SQPH1MMS
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 97CRI , E3SQPH1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 245.0 lumens
Efficiency: N/A
Efficacy: 68.1 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.4
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1312905

CATALOG NUMBER: P3SQAS02R259730DE010 E3SQPH1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1312905

CATALOG NUMBER: P3SQAS02R259730DE010 E3SQPH1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	112	110	113	111	110	108	107	106	105		104	103	102		100
2	112	109	106	104	110	107	105	103	104	102	101		101	100	98		99
3	109	105	102	99	107	104	101	98	101	99	97		99	97	95		97
4	106	101	98	95	105	100	97	95	99	96	94		97	94	93		95
5	104	98	95	92	102	98	94	92	96	93	91		95	92	90		93
6	101	96	92	89	100	95	92	89	94	91	89		93	90	88		91
7	99	93	89	87	98	93	89	87	92	89	86		91	88	86		90
8	97	91	87	85	96	90	87	85	90	86	84		89	86	84		88
9	95	89	85	83	94	88	85	83	88	85	82		87	84	82		86
10	93	87	83	81	92	86	83	81	86	83	81		85	82	80		85

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	228626	228626	228626
5°	207180	209082	210102
10°	155748	156867	157584
15°	77114	74814	79806
20°	21773	22140	22378
25°	3782	7145	4485
30°	1472	1511	1571
35°	463	505	505
40°	157	202	157
45°	97	49	97
50°	54	0	54
55°	60	0	60
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 97 cd/sqm

TEST NUMBER: P1312905

CATALOG NUMBER: P3SQAS02R259730DE010 E3SQPH1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.5	43.0
10°-20°	118.9	48.5
20°-30°	18.4	7.5
30°-40°	1.9	0.8
40°-50°	0.2	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	242.8	99.1
0°-40°	244.7	99.9
0°-60°	245.0	100.0
0°-90°	245.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	245.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1328	1328	1328	1328	1328	
5°	1198	1201	1209	1214	1215	104
15°	432	430	420	438	448	118
25°	20	30	38	29	24	17
35°	2	2	2	3	2	2
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0

TEST NUMBER: P1312905

CATALOG NUMBER: P3SQAS02R259730DE010 E3SQPH1MMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1327.5	1327.5	1327.5	1327.5	1327.5
1°	1322.1	1323.8	1321.9	1324.0	1323.8
2°	1308.3	1310.1	1307.7	1309.0	1309.0
3°	1280.1	1283.8	1286.0	1287.6	1288.9
4°	1243.0	1247.1	1250.4	1254.4	1254.4
5°	1198.4	1200.6	1209.4	1214.2	1215.3
6°	1145.3	1154.1	1160.6	1170.3	1164.4
7°	1092.3	1099.5	1108.6	1110.2	1114.3
8°	1032.0	1039.6	1048.1	1046.6	1043.1
9°	958.6	969.7	979.8	976.5	980.9
10°	890.6	897.4	897.0	893.7	901.1
11°	811.8	813.3	804.8	818.1	810.0
12°	718.3	719.6	708.7	721.8	730.1
13°	628.7	625.6	610.6	627.8	638.3
14°	525.6	526.7	507.5	540.9	538.3
15°	432.5	429.5	419.6	438.4	447.6
17.5°	230.5	232.4	230.0	239.4	245.3
20°	118.8	122.1	120.8	124.7	122.1
22.5°	61.6	66.2	67.5	64.4	56.1
25°	19.9	29.5	37.6	28.6	23.6
27.5°	12.0	11.8	18.4	12.7	12.9
30°	7.4	7.2	7.6	7.6	7.9
32.5°	4.2	4.4	4.2	4.6	4.4
35°	2.2	2.4	2.4	2.6	2.4
37.5°	1.3	1.5	1.5	1.5	1.3
40°	0.7	0.9	0.9	0.7	0.7
42.5°	0.4	0.4	0.4	0.4	0.4
45°	0.4	0.2	0.2	0.2	0.4
47.5°	0.2	0.2	0.0	0.2	0.2
50°	0.2	0.2	0.0	0.2	0.2
52.5°	0.2	0.0	0.0	0.0	0.2
55°	0.2	0.0	0.0	0.0	0.2
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1312905

CATALOG NUMBER: P3SQAS02R259730DE010 E3SQPH1MMS

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)