

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1315030

Luminaire Tested: P3SQAS05R309740DE010 E3SQCD1MB

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1315030
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-24)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3SQAS05R309740DE010 E3SQCD1MB
Description: 3in Adjustable LED luminaire with, R30 optic, 4000K CCT AND, 97CRI , E3SQCD1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 624.0 lumens
Efficiency: N/A
Efficacy: 86.7 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.46
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1315030
CATALOG NUMBER: P3SQAS05R309740DE010 E3SQCD1MB

Luminous Intensity Polar Plot



0% Up
100% Dn

— 0°-180° - - 45°-225° - · - · 90°-270°



TEST NUMBER: P1315030
 CATALOG NUMBER: P3SQAS05R309740DE010 E3SQCD1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	115	113	111	110	113	111	109	108	107	106	105	103	102	101	100	99	99	99	99	99	97
2	112	108	105	103	109	106	104	102	103	101	99	100	99	97	98	96	95	95	94	94	94
3	108	104	100	97	106	102	99	97	100	97	95	98	95	94	95	94	92	92	92	92	91
4	105	100	96	93	103	99	95	92	97	94	91	95	92	90	93	91	89	89	89	89	88
5	102	96	92	89	101	95	92	89	94	91	88	92	90	87	91	89	87	87	87	87	86
6	99	93	89	86	98	92	89	86	91	88	85	90	87	85	89	86	84	84	84	84	83
7	96	90	86	83	95	90	86	83	89	85	83	87	85	82	87	84	82	82	82	82	81
8	94	88	84	81	93	87	83	81	86	83	80	85	82	80	84	82	80	80	80	80	79
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	78	78	78	77
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	80	78	76	76	76	76	75

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	416486	416486	416486
5°	406338	406840	409104
10°	347031	345422	343393
15°	214154	211658	212424
20°	80934	81393	81301
25°	24893	27307	26015
30°	10043	12747	10421
35°	2964	5403	3070
40°	1192	2181	1192
45°	244	706	244
50°	0	134	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 706 cd/sqm



TEST NUMBER: P1315030
 CATALOG NUMBER: P3SQAS05R309740DE010 E3SQCD1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	213.3	34.2
10°-20°	315.8	50.6
20°-30°	78.3	12.6
30°-40°	14.7	2.4
40°-50°	1.9	0.3
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	607.4	97.3
0°-40°	622.1	99.7
0°-60°	624.0	100.0
0°-90°	624.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	624.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2418	2418	2418	2418	2418	
5°	2350	2349	2353	2357	2366	213
15°	1201	1190	1187	1196	1191	317
25°	131	140	144	143	137	75
35°	14	18	26	19	15	12
45°	1	2	3	2	1	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1315030

CATALOG NUMBER: P3SQAS05R309740DE010 E3SQCD1MB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2418.3	2418.3	2418.3	2418.3	2418.3
1°	2419.3	2417.3	2417.3	2414.4	2419.7
2°	2410.5	2408.6	2412.0	2409.6	2416.4
3°	2397.4	2395.0	2399.9	2401.3	2404.7
4°	2378.0	2376.1	2381.4	2384.3	2393.5
5°	2350.4	2349.4	2353.3	2357.1	2366.4
6°	2312.5	2311.0	2313.5	2318.3	2324.1
7°	2257.7	2254.7	2256.7	2257.7	2259.1
8°	2188.3	2183.9	2181.5	2186.8	2189.7
9°	2099.0	2094.1	2088.8	2086.8	2093.6
10°	1984.4	1977.1	1975.2	1970.4	1963.6
11°	1851.5	1845.6	1844.2	1835.4	1831.6
12°	1699.1	1696.2	1699.6	1694.2	1692.3
13°	1553.0	1534.5	1532.1	1521.9	1516.6
14°	1380.2	1363.2	1362.7	1357.4	1364.7
15°	1201.1	1189.5	1187.1	1196.3	1191.4
17.5°	765.8	773.6	771.6	766.8	758.5
20°	441.6	436.3	444.1	446.0	443.6
22.5°	235.4	237.3	238.8	244.6	248.5
25°	131.0	139.8	143.7	143.2	136.9
27.5°	81.5	86.9	94.1	89.3	84.0
30°	50.5	54.8	64.1	55.3	52.4
32.5°	27.2	34.5	41.3	34.5	28.1
35°	14.1	18.4	25.7	18.9	14.6
37.5°	9.2	10.7	16.5	10.7	9.2
40°	5.3	6.8	9.7	6.8	5.3
42.5°	2.4	3.9	5.3	3.9	2.4
45°	1.0	1.5	2.9	1.9	1.0
47.5°	0.0	0.5	1.5	0.5	0.0
50°	0.0	0.0	0.5	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1315030
CATALOG NUMBER: P3SQAS05R309740DE010 E3SQCD1MB

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)