

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1313812

Luminaire Tested: P3SQAS02R089735DE010 E3SQPH1MMS

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1313812  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2408-211-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3SQAS02R089735DE010 E3SQPH1MMS  
Description: 3in Adjustable LED luminaire with, R08 optic, 3500K CCT AND, 97CRI , E3SQPH1MMS TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 230.0 lumens  
Efficiency: N/A  
Efficacy: 46.9 lumens/watt  
Spacing Criteria (0/90/45): 0.16 / 0.16 / 0.16  
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 4.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1313812

CATALOG NUMBER: P3SQAS02R089735DE010 E3SQPH1MMS

### Luminous Intensity Polar Plot



TEST NUMBER: P1313812

CATALOG NUMBER: P3SQAS02R089735DE010 E3SQPH1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |     | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 |
| 1   | 116 | 114 | 113 | 111 | 114 | 112 | 111 | 110 | 108 | 107 | 106 | 105 | 104 | 103 | 101 | 101 | 100 | 99  | 99  | 99  |
| 2   | 113 | 111 | 108 | 106 | 111 | 109 | 107 | 105 | 106 | 104 | 103 | 103 | 102 | 101 | 101 | 100 | 99  | 97  | 97  | 97  |
| 3   | 111 | 108 | 105 | 103 | 109 | 106 | 104 | 102 | 104 | 102 | 100 | 102 | 100 | 99  | 100 | 98  | 97  | 96  | 96  | 96  |
| 4   | 109 | 105 | 102 | 100 | 108 | 104 | 101 | 99  | 102 | 100 | 98  | 100 | 99  | 97  | 99  | 97  | 96  | 95  | 95  | 95  |
| 5   | 107 | 103 | 100 | 98  | 106 | 102 | 99  | 97  | 101 | 98  | 97  | 99  | 97  | 96  | 98  | 96  | 95  | 94  | 94  | 94  |
| 6   | 105 | 101 | 98  | 96  | 104 | 100 | 98  | 96  | 99  | 97  | 95  | 98  | 96  | 95  | 97  | 95  | 94  | 93  | 93  | 93  |
| 7   | 104 | 100 | 97  | 95  | 103 | 99  | 96  | 94  | 98  | 96  | 94  | 97  | 95  | 94  | 96  | 94  | 93  | 92  | 92  | 92  |
| 8   | 103 | 98  | 95  | 93  | 102 | 98  | 95  | 93  | 97  | 95  | 93  | 96  | 94  | 93  | 95  | 94  | 92  | 92  | 92  | 92  |
| 9   | 101 | 97  | 94  | 92  | 101 | 97  | 94  | 92  | 96  | 94  | 92  | 95  | 93  | 92  | 95  | 93  | 92  | 91  | 91  | 91  |
| 10  | 100 | 96  | 93  | 91  | 100 | 96  | 93  | 91  | 95  | 93  | 91  | 94  | 92  | 91  | 94  | 92  | 91  | 90  | 90  | 90  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 1024535 |
| 5°  | 427222  |
| 10° | 68763   |
| 15° | 19702   |
| 20° | 6635    |
| 25° | 2926    |
| 30° | 1631    |
| 35° | 1135    |
| 40° | 1012    |
| 45° | 658     |
| 50° | 482     |
| 55° | 270     |
| 60° | 310     |
| 65° | 367     |
| 70° | 0       |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 658 cd/sqm

TEST NUMBER: P1313812

CATALOG NUMBER: P3SQAS02R089735DE010 E3SQPH1MMS

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 177.4  | 77.1      |
| 10°-20°   | 37.1   | 16.1      |
| 20°-30°   | 8.1    | 3.5       |
| 30°-40°   | 3.5    | 1.5       |
| 40°-50°   | 2.1    | 0.9       |
| 50°-60°   | 0.9    | 0.4       |
| 60°-70°   | 0.8    | 0.3       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 222.6  | 96.8      |
| 0°-40°    | 226.1  | 98.3      |
| 0°-60°    | 229.2  | 99.7      |
| 0°-90°    | 230.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 230.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 5949 |      |
| 5°  | 2471 | 177  |
| 15° | 110  | 37   |
| 25° | 15   | 8    |
| 35° | 5    | 3    |
| 45° | 3    | 2    |
| 55° | 1    | 1    |
| 65° | 1    | 1    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |

TEST NUMBER: P1313812

CATALOG NUMBER: P3SQAS02R089735DE010 E3SQPH1MMS

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 5948.9 |
| 2.5°  | 4972.4 |
| 5°    | 2471.2 |
| 7.5°  | 921.3  |
| 10°   | 393.2  |
| 12.5° | 202.9  |
| 15°   | 110.5  |
| 17.5° | 62.5   |
| 20°   | 36.2   |
| 22.5° | 23.6   |
| 25°   | 15.4   |
| 27.5° | 11.8   |
| 30°   | 8.2    |
| 32.5° | 6.3    |
| 35°   | 5.4    |
| 37.5° | 4.5    |
| 40°   | 4.5    |
| 42.5° | 3.6    |
| 45°   | 2.7    |
| 47.5° | 1.8    |
| 50°   | 1.8    |
| 52.5° | 0.9    |
| 55°   | 0.9    |
| 57.5° | 0.9    |
| 60°   | 0.9    |
| 62.5° | 0.9    |
| 65°   | 0.9    |
| 67.5° | 0.9    |
| 70°   | 0.0    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |

(END OF REPORT)