

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1316682

Luminaire Tested: P3SQAS02R309830DE010 E3SQCD1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1316682
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-36)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3SQAS02R309830DE010 E3SQCD1MW
Description: 3in Adjustable LED luminaire with, R30 optic, 3000K CCT AND, 98CRI , E3SQCD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 232.1 lumens
Efficiency: N/A
Efficacy: 64.5 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.46
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1316682
CATALOG NUMBER: P3SQAS02R309830DE010 E3SQCD1MW

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270°



TEST NUMBER: P1316682

CATALOG NUMBER: P3SQAS02R309830DE010 E3SQCD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	98	97	97	97
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	95	94	94	94
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	93	91	91	91
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	93	88	88	88
5	102	96	92	89	100	95	91	89	93	90	88	92	89	87	91	88	86	91	85	85	85
6	99	93	89	86	98	92	88	85	91	87	85	90	87	84	88	86	84	88	83	83	83
7	96	90	86	83	95	89	85	83	88	85	82	87	84	82	86	84	82	86	81	81	81
8	94	87	83	80	93	87	83	80	86	82	80	85	82	80	84	81	79	84	78	78	78
9	91	85	81	78	90	84	80	78	83	80	78	83	80	77	82	79	77	82	76	76	76
10	89	82	78	76	88	82	78	76	81	78	76	81	78	75	80	77	75	80	74	74	74

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	153623	153623	153623
5°	149421	150078	150994
10°	128484	127382	127522
15°	78950	78308	78380
20°	30039	30112	29562
25°	9558	10071	9596
30°	3838	4773	3957
35°	1240	2102	1240
40°	562	922	562
45°	219	390	219
50°	107	188	107
55°	120	120	120
60°	138	138	138
65°	82	82	82
70°	101	101	101
75°	133	133	133
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 390 cd/sqm



TEST NUMBER: P1316682

CATALOG NUMBER: P3SQAS02R309830DE010 E3SQCD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.7	33.9
10°-20°	116.7	50.3
20°-30°	29.0	12.5
30°-40°	5.8	2.5
40°-50°	1.1	0.5
50°-60°	0.4	0.2
60°-70°	0.3	0.1
70°-80°	0.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	224.4	96.7
0°-40°	230.2	99.2
0°-60°	231.6	99.8
0°-90°	232.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	232.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	892	892	892	892	892	
5°	864	867	868	869	873	79
15°	443	444	439	441	440	117
25°	50	51	53	52	50	28
35°	6	8	10	8	6	5
45°	1	1	2	1	1	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1316682

CATALOG NUMBER: P3SQAS02R309830DE010 E3SQCD1MW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	892.0	892.0	892.0	892.0	892.0
1°	890.1	891.1	891.9	891.9	891.9
2°	887.6	888.3	889.4	889.5	891.0
3°	881.7	883.3	885.1	886.1	886.8
4°	874.5	876.6	877.7	880.4	882.7
5°	864.3	867.2	868.1	869.3	873.4
6°	850.5	852.7	854.5	855.0	857.5
7°	832.3	833.3	833.0	833.9	838.3
8°	804.5	804.9	807.9	805.9	809.0
9°	771.6	770.2	769.4	770.9	771.0
10°	734.7	729.9	728.4	727.2	729.2
11°	686.9	680.7	681.2	680.8	678.0
12°	627.5	626.8	622.1	623.0	627.3
13°	566.8	568.1	567.2	568.3	563.4
14°	509.9	503.8	505.4	499.4	501.7
15°	442.8	443.7	439.2	440.6	439.6
17.5°	283.5	285.5	284.0	282.8	284.8
20°	163.9	163.8	164.3	162.7	161.3
22.5°	86.3	87.5	89.1	89.3	90.4
25°	50.3	51.4	53.0	52.3	50.5
27.5°	30.8	32.8	35.3	33.5	31.3
30°	19.3	20.9	24.0	21.1	19.9
32.5°	10.9	13.2	15.8	13.2	10.9
35°	5.9	7.7	10.0	7.5	5.9
37.5°	3.9	4.5	6.6	4.5	3.9
40°	2.5	3.0	4.1	3.0	2.5
42.5°	1.4	2.0	2.3	2.0	1.4
45°	0.9	1.1	1.6	1.3	0.9
47.5°	0.4	0.5	1.1	0.5	0.5
50°	0.4	0.4	0.7	0.4	0.4
52.5°	0.4	0.4	0.4	0.4	0.4
55°	0.4	0.4	0.4	0.4	0.4
57.5°	0.4	0.4	0.4	0.4	0.4
60°	0.4	0.4	0.4	0.4	0.4
62.5°	0.4	0.4	0.4	0.4	0.4
65°	0.2	0.2	0.2	0.2	0.2
67.5°	0.2	0.2	0.2	0.2	0.2
70°	0.2	0.2	0.2	0.2	0.2
72.5°	0.2	0.2	0.2	0.2	0.2
75°	0.2	0.2	0.2	0.2	0.2
77.5°	0.2	0.2	0.2	0.2	0.2
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1316682
CATALOG NUMBER: P3SQAS02R309830DE010 E3SQCD1MW

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)