

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1316684

Luminaire Tested: P3SQAS02R309830DE010 E3SQPH1MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1316684
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-4)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3SQAS02R309830DE010 E3SQPH1MMS
Description: 3in Adjustable LED luminaire with, R30 optic, 3000K CCT AND, 98CRI , E3SQPH1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 207.0 lumens
Efficiency: N/A
Efficacy: 57.5 lumens/watt
Spacing Criteria (0/90/45): 0.5 / 0.49 / 0.46
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1316684

CATALOG NUMBER: P3SQAS02R309830DE010 E3SQPH1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1316684

CATALOG NUMBER: P3SQAS02R309830DE010 E3SQPH1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	110	113	111	109	108	107	106	105		103	103	102		100
2	112	108	105	103	110	107	104	102	104	101	100		101	99	98		98
3	108	104	101	98	107	103	100	97	100	98	96		98	96	94		96
4	105	100	97	94	104	99	96	93	97	94	92		95	93	91		94
5	102	97	93	90	101	96	93	90	95	91	89		93	90	88		92
6	100	94	90	87	99	93	90	87	92	89	86		91	88	86		90
7	97	91	87	84	96	91	87	84	90	86	84		88	86	83		88
8	95	89	85	82	94	88	84	82	87	84	82		86	83	81		86
9	92	86	82	80	92	86	82	80	85	82	79		84	81	79		84
10	90	84	80	78	90	84	80	78	83	80	77		82	79	77		82

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	147130	147130	147130
5°	143335	142350	141174
10°	120964	117257	115350
15°	72906	70856	72175
20°	24724	28554	32935
25°	4542	7126	8418
30°	1571	1730	1949
35°	442	568	610
40°	112	202	157
45°	49	49	49
50°	54	0	54
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 52.5°
Luminance: 57 cd/sqm

TEST NUMBER: P1316684

CATALOG NUMBER: P3SQAS02R309830DE010 E3SQPH1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.9	35.7
10°-20°	108.0	52.2
20°-30°	22.8	11.0
30°-40°	2.1	1.0
40°-50°	0.2	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	204.7	98.9
0°-40°	206.8	99.9
0°-60°	207.0	100.0
0°-90°	207.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	207.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	854	854	854	854	854	
5°	829	828	823	821	817	75
15°	409	407	397	407	405	108
25°	24	27	38	44	44	17
35°	2	3	3	3	3	2
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	

TEST NUMBER: P1316684

CATALOG NUMBER: P3SQAS02R309830DE010 E3SQPH1MMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	854.3	854.3	854.3	854.3	854.3
1°	854.5	853.6	852.3	854.1	852.9
2°	852.7	850.5	848.8	850.5	850.0
3°	847.3	845.6	844.3	845.2	845.2
4°	839.3	837.3	836.3	836.5	833.8
5°	829.1	827.5	823.4	820.9	816.6
6°	814.1	810.2	805.2	801.1	795.6
7°	793.8	787.7	780.6	773.5	766.5
8°	761.1	758.3	748.6	743.8	736.9
9°	730.4	723.5	713.1	705.3	701.5
10°	691.7	681.4	670.5	664.2	659.6
11°	645.9	635.3	626.6	617.5	610.3
12°	592.0	583.0	573.0	567.0	558.6
13°	528.1	526.8	515.6	513.6	512.5
14°	473.3	468.3	457.2	460.3	461.0
15°	408.9	407.4	397.4	406.7	404.8
17.5°	256.1	256.6	262.9	277.5	282.1
20°	134.9	139.0	155.8	173.5	179.7
22.5°	54.6	63.7	80.8	92.8	100.8
25°	23.9	26.8	37.5	44.1	44.3
27.5°	13.6	13.7	18.0	18.7	19.1
30°	7.9	8.0	8.7	9.3	9.8
32.5°	4.3	4.6	4.8	5.5	5.5
35°	2.1	2.7	2.7	3.2	2.9
37.5°	1.2	1.4	1.6	1.6	1.4
40°	0.5	0.7	0.9	0.9	0.7
42.5°	0.2	0.4	0.4	0.4	0.5
45°	0.2	0.2	0.2	0.2	0.2
47.5°	0.2	0.2	0.0	0.2	0.2
50°	0.2	0.0	0.0	0.0	0.2
52.5°	0.2	0.0	0.0	0.0	0.2
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1316684

CATALOG NUMBER: P3SQAS02R309830DE010 E3SQPH1MMS

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)