

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMARK

Report Number: P1001999

Luminaire Tested: **CYL-2D-30W-347V-PC_15W_Downlight_5000K**

Issue Date: 6/25/2025

Test Information

Test Method: LM-79-08
Report Number: P1001999
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2504-411-3dn)
Test Lab: INNOVATION CENTER
Issue Date: 6/25/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMARK
Catalog Number: CYL-2D-30W-347V-PC_15W_Downlight_5000K
Description: Lumark AP Wall Cylinder at 15W Downlight output with 5000K CCT settings
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1804.1 lumens
Efficiency: N/A
Efficacy: 114.2 lumens/watt
Luminous Opening: Circular (Dia: 0.38' x H: 0')
IES Classification: Type V - Short
BUG Rating: B2 - U0 - G0

Input Watts (W): 15.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9875
Total Harmonic Distortion (THDi): 10
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT




REPORT NUMBER: P1001999

CATALOG NUMBER: CYL-2D-30W-347V-PC_15W_Downlight_5000K

Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd

--- 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 21.4 fc

Type V - Short - N/A

REPORT NUMBER: P1001999
CATALOG NUMBER: CYL-2D-30W-347V-PC_15W_Downlight_5000K

Luminous Intensity Polar Plot



REPORT NUMBER: P1001999

CATALOG NUMBER: CYL-2D-30W-347V-PC_15W_Downlight_5000K


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	902.0	0.0	902.0
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	902.0	0.0	902.0
	% Fixture	50.0	0.0	50.0
Total	Lumens	1804.1	0.0	1804.1
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	194.4	10.8
10°-20°	472.2	26.2
20°-30°	519.4	28.8
30°-40°	357.2	19.8
40°-50°	174.8	9.7
50°-60°	60.6	3.4
60°-70°	13.9	0.8
70°-80°	7.8	0.4
80°-90°	3.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	1804.1	100.0
0°-180°	1804.1	100.0



REPORT NUMBER: P1001999


CATALOG NUMBER: CYL-2D-30W-347V-PC_15W_Downlight_5000K

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	593.0	32.9			
FM	(30°-60°)	296.3	16.4			
FH	(60°-80°)	10.9	0.6			G0/660
FVH	(80°-90°)	1.9	0.1			G0/10
BL	(0°-30°)	593.0	32.9	B2/1000		
BM	(30°-60°)	296.3	16.4	B1/1000		
BH	(60°-80°)	10.9	0.6	B0/110		G0/660
BVH	(80°-90°)	1.9	0.1			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G0

Type V Short





REPORT NUMBER: P1001999

CATALOG NUMBER: CYL-2D-30W-347V-PC_15W_Downlight_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2143.0
2.5°	2128.5
5°	2087.8
7.5°	2022.1
10°	1932.8
12.5°	1823.7
15°	1700.2
17.5°	1564.9
20°	1424.3
22.5°	1281.1
25°	1141.8
27.5°	1002.5
30°	837.0
32.5°	692.4
35°	565.0
37.5°	453.3
40°	364.0
42.5°	283.8
45°	219.4
47.5°	165.6
50°	130.1
52.5°	92.0
55°	61.8
57.5°	42.0
60°	26.3
62.5°	14.5
65°	11.8
67.5°	11.8
70°	10.5
72.5°	7.9
75°	6.6
77.5°	6.6
80°	6.6
82.5°	5.3
85°	3.9
87.5°	1.3
90°	0.0

(END OF REPORT)