

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1319410

Luminaire Tested: P3SQAS02R25B2750DE010 E3SQCA301MB\_3000K

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1319410  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-49)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3SQAS02R25B2750DE010 E3SQCA301MB\_3000K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R25 optic, 3000K CCT AND, 90CRI , E3SQCA301MB TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 208.0 lumens  
Efficiency: N/A  
Efficacy: 71.7 lumens/watt  
Spacing Criteria (0/90/45): 2.4 / 0.45 / 1.25  
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 2.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1319410

CATALOG NUMBER: P3SQAS02R25B2750DE010 E3SQCA301MB\_3000K

### Luminous Intensity Polar Plot



TEST NUMBER: P1319410

CATALOG NUMBER: P3SQA02R25B2750DE010 E3SQCA301MB\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |    | 10 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |
| 1   | 113 | 109 | 107 | 104 | 110 | 107 | 105 | 102 | 103 | 101 | 99  | 99  | 98  | 96  | 96  | 95  | 93  | 92  |    |    |
| 2   | 106 | 100 | 95  | 92  | 103 | 98  | 94  | 90  | 95  | 92  | 88  | 92  | 89  | 87  | 89  | 87  | 85  | 83  |    |    |
| 3   | 99  | 92  | 86  | 81  | 97  | 90  | 85  | 80  | 87  | 83  | 79  | 85  | 81  | 78  | 83  | 79  | 77  | 75  |    |    |
| 4   | 93  | 84  | 77  | 72  | 91  | 83  | 76  | 72  | 80  | 75  | 71  | 78  | 74  | 70  | 76  | 72  | 69  | 67  |    |    |
| 5   | 87  | 77  | 70  | 65  | 85  | 76  | 69  | 64  | 74  | 68  | 64  | 72  | 67  | 63  | 70  | 66  | 62  | 61  |    |    |
| 6   | 81  | 70  | 63  | 58  | 79  | 69  | 63  | 58  | 68  | 62  | 57  | 66  | 61  | 57  | 65  | 60  | 56  | 55  |    |    |
| 7   | 75  | 64  | 57  | 52  | 74  | 64  | 57  | 52  | 62  | 56  | 52  | 61  | 55  | 51  | 60  | 55  | 51  | 49  |    |    |
| 8   | 70  | 59  | 52  | 47  | 69  | 58  | 52  | 47  | 57  | 51  | 47  | 56  | 51  | 46  | 55  | 50  | 46  | 45  |    |    |
| 9   | 66  | 54  | 47  | 42  | 65  | 54  | 47  | 42  | 53  | 47  | 42  | 52  | 46  | 42  | 51  | 46  | 42  | 40  |    |    |
| 10  | 62  | 50  | 43  | 38  | 60  | 50  | 43  | 38  | 49  | 42  | 38  | 48  | 42  | 38  | 47  | 42  | 38  | 36  |    |    |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°     | 45°   | 90°  | 135° | 180° |
|-----|--------|-------|------|------|------|
| 0°  | 1137   | 1137  | 1137 | 1137 | 1137 |
| 5°  | 3544   | 2472  | 1037 | 553  | 415  |
| 10° | 11192  | 4494  | 769  | 70   | 0    |
| 15° | 69162  | 8558  | 464  | 0    | 0    |
| 20° | 151642 | 16678 | 147  | 0    | 0    |
| 25° | 190616 | 19193 | 0    | 0    | 0    |
| 30° | 211016 | 14855 | 0    | 0    | 0    |
| 35° | 207701 | 8410  | 0    | 0    | 0    |
| 40° | 157892 | 2203  | 0    | 0    | 0    |
| 45° | 63959  | 974   | 0    | 0    | 0    |
| 50° | 7100   | 107   | 0    | 0    | 0    |
| 55° | 540    | 0     | 60   | 0    | 0    |
| 60° | 0      | 0     | 69   | 0    | 0    |
| 65° | 0      | 0     | 163  | 0    | 0    |
| 70° | 0      | 101   | 201  | 0    | 0    |
| 75° | 0      | 133   | 399  | 0    | 0    |
| 80° | 0      | 198   | 595  | 0    | 0    |
| 85° | 0      | 395   | 1186 | 0    | 0    |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 63959 cd/sqm

TEST NUMBER: P1319410

CATALOG NUMBER: P3SQAS02R25B2750DE010 E3SQCA301MB\_3000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 1.0    | 0.5       |
| 10°-20°   | 21.5   | 10.3      |
| 20°-30°   | 75.1   | 36.1      |
| 30°-40°   | 83.8   | 40.3      |
| 40°-50°   | 25.3   | 12.2      |
| 50°-60°   | 0.8    | 0.4       |
| 60°-70°   | 0.1    | 0.1       |
| 70°-80°   | 0.2    | 0.1       |
| 80°-90°   | 0.2    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 97.6   | 46.9      |
| 0°-40°    | 181.4  | 87.2      |
| 0°-60°    | 207.5  | 99.8      |
| 0°-90°    | 208.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 208.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | 45° | 90° | 135° | 180° | Flux |
|-----|------|-----|-----|------|------|------|
| 0°  | 7    | 7   | 7   | 7    | 7    |      |
| 5°  | 20   | 14  | 6   | 3    | 2    | 3    |
| 15° | 388  | 48  | 3   | 0    | 0    | 129  |
| 25° | 1003 | 101 | 0   | 0    | 0    | 458  |
| 35° | 988  | 40  | 0   | 0    | 0    | 593  |
| 45° | 263  | 4   | 0   | 0    | 0    | 227  |
| 55° | 2    | 0   | 0   | 0    | 0    | 6    |
| 65° | 0    | 0   | 0   | 0    | 0    | 0    |
| 75° | 0    | 0   | 1   | 0    | 0    | 0    |
| 85° | 0    | 0   | 1   | 0    | 0    | 0    |
| 90° | 0    | 0   | 0   | 0    | 0    |      |

TEST NUMBER: P1319410

CATALOG NUMBER: P3SQAS02R25B2750DE010 E3SQCA301MB\_3000K

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 1°     | 2°     | 3°     | 4°     | 5°     | 6°     | 7°     | 8°     | 9°    | 10°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|-------|-------|
| 0°    | 6.6    | 6.6    | 6.6    | 6.6    | 6.6    | 6.6    | 6.6    | 6.6    | 6.6    | 6.6   | 6.6   |
| 2.5°  | 11.4   | 11.8   | 11.6   | 11.8   | 11.6   | 11.6   | 11.6   | 11.8   | 11.6   | 11.6  | 11.6  |
| 5°    | 20.5   | 20.7   | 20.7   | 20.5   | 20.5   | 20.9   | 20.5   | 20.7   | 20.1   | 20.5  | 20.3  |
| 7.5°  | 33.7   | 33.3   | 33.3   | 33.5   | 33.5   | 33.1   | 32.9   | 32.5   | 32.9   | 32.9  | 32.3  |
| 10°   | 64.0   | 63.6   | 62.6   | 62.2   | 62.6   | 62.6   | 60.6   | 61.0   | 61.2   | 59.4  | 58.8  |
| 12.5° | 187.9  | 186.5  | 189.3  | 184.9  | 182.3  | 178.1  | 180.5  | 172.3  | 170.5  | 169.3 | 166.6 |
| 15°   | 387.9  | 398.4  | 393.9  | 394.3  | 395.1  | 385.1  | 388.5  | 376.1  | 365.8  | 362.6 | 360.4 |
| 17.5° | 632.5  | 635.7  | 631.5  | 629.5  | 628.7  | 624.0  | 618.2  | 612.0  | 604.0  | 597.1 | 591.3 |
| 20°   | 827.4  | 825.0  | 817.8  | 818.6  | 810.0  | 805.7  | 800.7  | 794.5  | 788.3  | 778.2 | 768.4 |
| 21°   | 878.8  | 871.8  | 872.0  | 867.2  | 867.0  | 861.4  | 852.7  | 846.3  | 840.7  | 829.2 | 823.0 |
| 22°   | 921.0  | 919.4  | 915.8  | 912.2  | 908.5  | 905.7  | 895.9  | 892.7  | 881.4  | 871.8 | 863.0 |
| 23°   | 953.9  | 954.5  | 951.3  | 948.9  | 943.7  | 942.5  | 930.0  | 925.6  | 917.8  | 903.3 | 894.3 |
| 24°   | 981.2  | 980.2  | 976.6  | 972.4  | 969.4  | 966.6  | 957.1  | 949.9  | 941.3  | 929.4 | 920.6 |
| 25°   | 1003.1 | 1000.7 | 998.3  | 995.1  | 990.3  | 987.1  | 977.4  | 969.4  | 962.0  | 948.7 | 936.7 |
| 26°   | 1016.0 | 1016.6 | 1012.8 | 1010.5 | 1006.3 | 1003.1 | 992.9  | 983.6  | 974.4  | 960.1 | 949.3 |
| 27°   | 1029.2 | 1028.6 | 1025.2 | 1021.6 | 1017.2 | 1016.0 | 1004.3 | 994.5  | 985.2  | 970.0 | 957.3 |
| 28°   | 1041.3 | 1039.7 | 1037.0 | 1032.8 | 1028.0 | 1024.4 | 1013.0 | 1002.9 | 992.7  | 976.6 | 962.6 |
| 29°   | 1051.5 | 1049.9 | 1048.1 | 1042.7 | 1036.6 | 1034.2 | 1022.0 | 1009.7 | 999.5  | 983.0 | 968.2 |
| 30°   | 1061.1 | 1058.1 | 1053.9 | 1049.3 | 1043.3 | 1038.7 | 1026.0 | 1015.2 | 1003.3 | 985.0 | 970.8 |
| 31°   | 1061.5 | 1057.5 | 1054.5 | 1049.7 | 1042.9 | 1037.4 | 1024.0 | 1013.0 | 999.1  | 982.0 | 966.6 |
| 32°   | 1054.5 | 1052.5 | 1047.7 | 1042.5 | 1036.0 | 1030.4 | 1015.6 | 1004.1 | 990.9  | 972.6 | 957.3 |
| 33°   | 1038.7 | 1036.8 | 1034.0 | 1028.6 | 1020.0 | 1014.8 | 1001.7 | 988.9  | 976.0  | 959.5 | 941.9 |
| 34°   | 1017.0 | 1014.6 | 1011.1 | 1005.7 | 996.9  | 991.5  | 981.0  | 967.8  | 954.1  | 936.9 | 920.6 |
| 35°   | 987.9  | 983.4  | 982.4  | 974.4  | 966.2  | 964.8  | 952.3  | 938.5  | 924.6  | 905.7 | 891.5 |
| 36°   | 951.9  | 946.5  | 942.9  | 940.1  | 934.8  | 928.2  | 915.8  | 904.9  | 886.9  | 874.8 | 854.9 |
| 37°   | 902.7  | 896.1  | 899.5  | 891.9  | 883.6  | 880.8  | 865.0  | 855.1  | 839.9  | 823.4 | 806.5 |
| 38°   | 845.3  | 844.7  | 843.9  | 840.5  | 826.2  | 818.8  | 812.2  | 801.7  | 788.5  | 768.6 | 745.7 |
| 39°   | 772.8  | 774.0  | 769.8  | 770.2  | 763.0  | 755.7  | 746.5  | 734.5  | 718.6  | 700.5 | 681.9 |
| 40°   | 702.3  | 685.3  | 688.3  | 678.2  | 678.8  | 667.8  | 655.8  | 645.3  | 635.1  | 619.2 | 593.9 |
| 42.5° | 485.9  | 483.3  | 474.3  | 468.0  | 470.8  | 456.6  | 440.9  | 426.1  | 412.0  | 394.1 | 371.9 |
| 45°   | 262.6  | 256.6  | 258.4  | 248.0  | 248.0  | 241.7  | 237.3  | 224.9  | 211.8  | 203.6 | 190.9 |
| 47.5° | 97.6   | 98.8   | 101.0  | 96.8   | 92.0   | 94.8   | 90.6   | 90.6   | 88.5   | 85.9  | 82.3  |
| 50°   | 26.5   | 26.9   | 26.5   | 26.5   | 25.9   | 25.5   | 24.7   | 24.5   | 24.3   | 23.7  | 22.7  |
| 52.5° | 10.8   | 10.2   | 10.2   | 10.4   | 10.4   | 10.0   | 10.2   | 10.2   | 10.0   | 9.8   | 9.8   |
| 55°   | 1.8    | 2.0    | 2.0    | 2.0    | 2.0    | 1.8    | 1.8    | 2.0    | 2.2    | 2.0   | 2.0   |
| 57.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   |
| 60°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   |
| 62.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   |
| 65°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   |
| 67.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   |
| 70°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   |
| 72.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   |
| 75°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   |
| 77.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   |
| 80°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   |



TEST NUMBER: P1319410

CATALOG NUMBER: P3SQAS02R25B2750DE010 E3SQCA301MB\_3000K

**CANDELA DISTRIBUTION (continued):**

|       | 0°  | 1°  | 2°  | 3°  | 4°  | 5°  | 6°  | 7°  | 8°  | 9°  | 10° |
|-------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

TEST NUMBER: P1319410

CATALOG NUMBER: P3SQAS02R25B2750DE010 E3SQCA301MB\_3000K

**CANDELA DISTRIBUTION (continued):**

|       | 22.5° | 45°   | 67.5° | 90° | 112.5° | 135° | 157.5° | 180° |
|-------|-------|-------|-------|-----|--------|------|--------|------|
| 0°    | 6.6   | 6.6   | 6.6   | 6.6 | 6.6    | 6.6  | 6.6    | 6.6  |
| 2.5°  | 11.2  | 9.8   | 8.2   | 6.8 | 5.4    | 4.6  | 4.2    | 4.4  |
| 5°    | 18.9  | 14.3  | 9.4   | 6.0 | 4.2    | 3.2  | 2.6    | 2.4  |
| 7.5°  | 29.1  | 19.7  | 10.6  | 5.2 | 3.2    | 1.6  | 1.0    | 0.8  |
| 10°   | 44.6  | 25.7  | 11.4  | 4.4 | 2.0    | 0.4  | 0.0    | 0.0  |
| 12.5° | 114.6 | 31.5  | 11.6  | 3.6 | 0.8    | 0.0  | 0.0    | 0.0  |
| 15°   | 235.5 | 48.0  | 11.2  | 2.6 | 0.2    | 0.0  | 0.0    | 0.0  |
| 17.5° | 391.5 | 73.5  | 9.8   | 1.8 | 0.0    | 0.0  | 0.0    | 0.0  |
| 20°   | 543.1 | 91.0  | 7.8   | 0.8 | 0.0    | 0.0  | 0.0    | 0.0  |
| 21°   | 588.7 | 96.2  | 7.0   | 0.6 | 0.0    | 0.0  | 0.0    | 0.0  |
| 22°   | 626.0 | 100.0 | 6.2   | 0.4 | 0.0    | 0.0  | 0.0    | 0.0  |
| 23°   | 657.0 | 102.0 | 5.4   | 0.2 | 0.0    | 0.0  | 0.0    | 0.0  |
| 24°   | 678.8 | 102.4 | 5.0   | 0.2 | 0.0    | 0.0  | 0.0    | 0.0  |
| 25°   | 689.1 | 101.0 | 4.4   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  |
| 26°   | 693.1 | 98.2  | 4.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  |
| 27°   | 690.1 | 94.6  | 3.6   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  |
| 28°   | 684.7 | 89.3  | 3.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  |
| 29°   | 674.2 | 82.1  | 2.6   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  |
| 30°   | 664.0 | 74.7  | 2.2   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  |
| 31°   | 652.5 | 68.1  | 1.8   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  |
| 32°   | 638.3 | 60.6  | 1.4   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  |
| 33°   | 614.8 | 53.6  | 1.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  |
| 34°   | 581.9 | 47.0  | 0.8   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  |
| 35°   | 537.9 | 40.0  | 0.6   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  |
| 36°   | 489.7 | 32.7  | 0.4   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  |
| 37°   | 430.7 | 23.7  | 0.4   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  |
| 38°   | 369.2 | 14.9  | 0.2   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  |
| 39°   | 306.2 | 11.4  | 0.2   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  |
| 40°   | 248.6 | 9.8   | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  |
| 42.5° | 133.1 | 6.6   | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  |
| 45°   | 78.5  | 4.0   | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  |
| 47.5° | 43.8  | 1.6   | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  |
| 50°   | 15.7  | 0.4   | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  |
| 52.5° | 6.2   | 0.0   | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  |
| 55°   | 2.2   | 0.0   | 0.0   | 0.2 | 0.0    | 0.0  | 0.0    | 0.0  |
| 57.5° | 0.2   | 0.0   | 0.2   | 0.2 | 0.0    | 0.0  | 0.0    | 0.0  |
| 60°   | 0.0   | 0.0   | 0.2   | 0.2 | 0.0    | 0.0  | 0.0    | 0.0  |
| 62.5° | 0.0   | 0.0   | 0.2   | 0.4 | 0.0    | 0.0  | 0.0    | 0.0  |
| 65°   | 0.0   | 0.0   | 0.4   | 0.4 | 0.2    | 0.0  | 0.0    | 0.0  |
| 67.5° | 0.0   | 0.2   | 0.4   | 0.4 | 0.2    | 0.0  | 0.0    | 0.0  |
| 70°   | 0.0   | 0.2   | 0.4   | 0.4 | 0.2    | 0.0  | 0.0    | 0.0  |
| 72.5° | 0.0   | 0.2   | 0.4   | 0.6 | 0.2    | 0.0  | 0.0    | 0.0  |
| 75°   | 0.0   | 0.2   | 0.4   | 0.6 | 0.2    | 0.0  | 0.0    | 0.0  |
| 77.5° | 0.0   | 0.2   | 0.4   | 0.6 | 0.2    | 0.0  | 0.0    | 0.0  |
| 80°   | 0.0   | 0.2   | 0.4   | 0.6 | 0.2    | 0.0  | 0.0    | 0.0  |



TEST NUMBER: P1319410

CATALOG NUMBER: P3SQAS02R25B2750DE010 E3SQCA301MB\_3000K

**CANDELA DISTRIBUTION (continued):**

|       | 22.5° | 45° | 67.5° | 90° | 112.5° | 135° | 157.5° | 180° |
|-------|-------|-----|-------|-----|--------|------|--------|------|
| 82.5° | 0.0   | 0.2 | 0.4   | 0.6 | 0.2    | 0.0  | 0.0    | 0.0  |
| 85°   | 0.0   | 0.2 | 0.4   | 0.6 | 0.2    | 0.0  | 0.0    | 0.0  |
| 87.5° | 0.0   | 0.2 | 0.4   | 0.6 | 0.2    | 0.0  | 0.0    | 0.0  |
| 90°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  |

(END OF REPORT)