

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMARK

Report Number: P965154

Luminaire Tested: **NAV-SB3D-750-U-SLR**

Issue Date: 1/21/2025

**Test Information**

Test Method: LM-79-08  
Report Number: P965154  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/21/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMARK  
Catalog Number: NAV-SB3D-750-U-SLR  
Description: NAVION ROADWAY AND AREA HIGH DENSITY LED LUMINAIRE  
(3) 70 CRI, 5000K, 900mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT  
ELIMINATOR RIGHT OPTICS  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 32990.6 lumens  
Efficiency: N/A  
Efficacy: 151.3 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B3 - U0 - G5

Input Watts (W): 218.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




REPORT NUMBER: P965154  
CATALOG NUMBER: NAV-SB3D-750-U-SLR



REPORT NUMBER: P965154  
CATALOG NUMBER: NAV-SB3D-750-U-SLR

## Luminous Intensity Polar Plot



REPORT NUMBER: P965154

CATALOG NUMBER: NAV-SB3D-750-U-SLR

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 8384.6   | 0.0    | 8384.6  |
|                    | % Fixture | 25.4     | 0.0    | 25.4    |
| <b>Street Side</b> | Lumens    | 24606.1  | 0.0    | 24606.1 |
|                    | % Fixture | 74.6     | 0.0    | 74.6    |
| <b>Total</b>       | Lumens    | 32990.6  | 0.0    | 32990.6 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 450.0   | 1.4       |
| 10°-20°   | 1412.7  | 4.3       |
| 20°-30°   | 2182.1  | 6.6       |
| 30°-40°   | 2765.3  | 8.4       |
| 40°-50°   | 4170.8  | 12.6      |
| 50°-60°   | 6738.5  | 20.4      |
| 60°-70°   | 8400.6  | 25.5      |
| 70°-80°   | 5508.7  | 16.7      |
| 80°-90°   | 1361.9  | 4.1       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 32990.6 | 100.0     |
| 0°-180°   | 32990.6 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P965154


CATALOG NUMBER: NAV-SB3D-750-U-SLR

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens  | % Fixture | Zone Rating/Lumen Limit |      |          |
|------|-------------|---------|-----------|-------------------------|------|----------|
|      |             |         |           | B                       | U    | G        |
| FL   | (0°-30°)    | 2219.0  | 6.7       |                         |      |          |
| FM   | (30°-60°)   | 9622.7  | 29.2      |                         |      |          |
| FH   | (60°-80°)   | 11642.5 | 35.3      |                         |      | G4/12000 |
| FVH  | (80°-90°)   | 1121.9  | 3.4       |                         |      | G5       |
| BL   | (0°-30°)    | 1825.8  | 5.5       | B3/2500                 |      |          |
| BM   | (30°-60°)   | 4051.9  | 12.3      | B3/5000                 |      |          |
| BH   | (60°-80°)   | 2266.8  | 6.9       | B3/2500                 |      | G3/2500  |
| BVH  | (80°-90°)   | 240.0   | 0.7       |                         |      | G3/500   |
| UL   | (90°-100°)  | 0.0     | 0.0       |                         | U0/0 |          |
| UH   | (100°-180°) | 0.0     | 0.0       |                         | U0/0 |          |

**BUG Rating: B3-U0-G5**

Type IV Short



REPORT NUMBER: P965154

CATALOG NUMBER: NAV-SB3D-750-U-SLR

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      | 5°      | 10°     | 15°    | 20°    | 25°    | 30°    | 35°    | 40°    | 45°    | 50°    |
|-------|---------|---------|---------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 4536.5  | 4536.5  | 4536.5  | 4536.5 | 4536.5 | 4536.5 | 4536.5 | 4536.5 | 4536.5 | 4536.5 | 4536.5 |
| 2.5°  | 4878.6  | 4841.2  | 4803.7  | 4763.9 | 4724.1 | 4684.1 | 4644.1 | 4605.7 | 4567.5 | 4530.4 | 4489.2 |
| 5°    | 5245.8  | 5163.2  | 5080.5  | 4998.0 | 4915.6 | 4832.6 | 4749.7 | 4672.3 | 4594.8 | 4521.7 | 4449.4 |
| 7.5°  | 5615.0  | 5478.4  | 5342.1  | 5216.1 | 5090.0 | 4967.4 | 4844.7 | 4736.5 | 4628.4 | 4528.7 | 4435.2 |
| 10°   | 5897.7  | 5725.2  | 5552.7  | 5386.2 | 5219.7 | 5070.8 | 4921.5 | 4793.8 | 4665.7 | 4542.6 | 4442.1 |
| 12.5° | 6071.0  | 5881.4  | 5692.0  | 5503.3 | 5314.6 | 5138.8 | 4962.9 | 4818.3 | 4673.7 | 4544.3 | 4450.9 |
| 15°   | 6176.3  | 5978.7  | 5781.2  | 5576.4 | 5371.7 | 5169.3 | 4966.8 | 4799.4 | 4631.9 | 4488.6 | 4413.8 |
| 17.5° | 6235.5  | 6035.1  | 5834.8  | 5611.5 | 5388.1 | 5153.1 | 4918.1 | 4716.6 | 4515.2 | 4346.7 | 4300.6 |
| 20°   | 6300.8  | 6092.6  | 5884.2  | 5638.7 | 5393.3 | 5108.5 | 4823.8 | 4574.1 | 4324.5 | 4128.3 | 4116.1 |
| 22.5° | 6376.5  | 6163.8  | 5950.8  | 5675.6 | 5400.3 | 5053.9 | 4707.4 | 4406.8 | 4106.2 | 3882.8 | 3906.7 |
| 25°   | 6474.0  | 6265.4  | 6057.0  | 5742.6 | 5427.8 | 4999.8 | 4572.2 | 4220.0 | 3868.0 | 3639.2 | 3703.5 |
| 27.5° | 6606.3  | 6407.5  | 6208.5  | 5847.0 | 5485.2 | 4963.9 | 4442.5 | 4049.3 | 3656.0 | 3447.6 | 3526.0 |
| 30°   | 6784.7  | 6592.6  | 6400.5  | 5982.2 | 5563.9 | 4947.0 | 4329.7 | 3906.5 | 3483.4 | 3308.4 | 3369.8 |
| 32.5° | 6995.3  | 6805.1  | 6615.0  | 6123.5 | 5631.8 | 4926.0 | 4220.0 | 3783.5 | 3346.6 | 3205.7 | 3233.0 |
| 35°   | 7251.3  | 7069.2  | 6886.9  | 6284.3 | 5681.6 | 4886.8 | 4092.2 | 3662.4 | 3232.6 | 3115.2 | 3103.8 |
| 37.5° | 7682.1  | 7449.9  | 7217.6  | 6464.5 | 5711.2 | 4819.3 | 3927.6 | 3520.1 | 3112.5 | 3009.8 | 2968.4 |
| 40°   | 8333.1  | 7994.8  | 7656.3  | 6693.1 | 5729.9 | 4726.6 | 3723.5 | 3350.1 | 2976.7 | 2883.6 | 2820.1 |
| 42.5° | 9196.6  | 8708.1  | 8219.7  | 6992.4 | 5765.1 | 4630.8 | 3496.9 | 3162.6 | 2828.4 | 2742.6 | 2662.5 |
| 45°   | 10262.8 | 9603.9  | 8945.1  | 7386.2 | 5827.3 | 4541.9 | 3256.6 | 2963.5 | 2670.3 | 2583.3 | 2505.8 |
| 47.5° | 11596.2 | 10668.9 | 9741.5  | 7805.7 | 5870.0 | 4468.4 | 3066.9 | 2805.9 | 2545.1 | 2432.7 | 2366.1 |
| 50°   | 13344.1 | 11946.0 | 10547.8 | 8195.0 | 5842.1 | 4388.3 | 2934.6 | 2701.4 | 2468.1 | 2320.5 | 2243.0 |
| 52.5° | 15350.3 | 13287.5 | 11224.6 | 8447.7 | 5670.6 | 4253.1 | 2835.8 | 2632.4 | 2429.2 | 2259.5 | 2151.3 |
| 55°   | 17486.2 | 14476.8 | 11467.5 | 8392.0 | 5316.4 | 4028.9 | 2741.4 | 2582.5 | 2423.5 | 2265.7 | 2102.5 |
| 57.5° | 19429.0 | 15319.6 | 11210.3 | 8000.0 | 4789.8 | 3712.8 | 2635.6 | 2523.2 | 2411.0 | 2271.7 | 2073.3 |
| 60°   | 20603.1 | 15530.3 | 10457.3 | 7270.4 | 4083.5 | 3302.2 | 2521.0 | 2432.7 | 2344.5 | 2252.5 | 2045.8 |
| 62.5° | 20006.9 | 14643.4 | 9279.8  | 6283.9 | 3288.0 | 2811.1 | 2334.0 | 2275.4 | 2216.9 | 2205.6 | 2013.7 |
| 65°   | 18813.6 | 13388.4 | 7963.2  | 5277.4 | 2591.7 | 2369.1 | 2146.4 | 2118.7 | 2091.0 | 2092.4 | 1946.2 |
| 67.5° | 17214.7 | 11895.0 | 6575.3  | 4291.4 | 2007.5 | 1944.3 | 1880.9 | 1896.5 | 1911.7 | 1907.9 | 1825.7 |
| 70°   | 15293.7 | 10265.5 | 5237.1  | 3378.9 | 1520.6 | 1538.7 | 1556.6 | 1628.3 | 1699.9 | 1699.9 | 1672.9 |
| 72.5° | 13004.6 | 8498.9  | 3993.4  | 2583.2 | 1172.9 | 1227.4 | 1282.1 | 1383.7 | 1485.2 | 1502.3 | 1502.6 |
| 75°   | 10108.8 | 6473.8  | 2838.8  | 1874.8 | 910.8  | 960.2  | 1009.6 | 1123.5 | 1237.4 | 1316.0 | 1309.4 |
| 77.5° | 7222.6  | 4531.1  | 1839.7  | 1270.4 | 701.2  | 734.8  | 768.5  | 879.1  | 989.6  | 1119.3 | 1115.8 |
| 80°   | 4727.1  | 2919.3  | 1111.5  | 818.6  | 525.7  | 539.7  | 553.6  | 647.2  | 740.7  | 895.6  | 895.1  |
| 82.5° | 2747.8  | 1689.6  | 631.6   | 503.5  | 375.7  | 378.1  | 380.9  | 449.8  | 518.8  | 651.1  | 658.4  |
| 85°   | 1209.0  | 760.0   | 311.3   | 269.2  | 227.1  | 225.9  | 224.6  | 275.0  | 325.5  | 423.8  | 433.5  |
| 87.5° | 374.2   | 249.0   | 123.6   | 111.6  | 99.5   | 98.4   | 97.2   | 117.7  | 138.4  | 179.3  | 191.5  |
| 90°   | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P965154

CATALOG NUMBER: NAV-SB3D-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

|       | 55°    | 60°    | 65°    | 70°    | 75°    | 80°    | 85°    | 90°    | 95°    | 100°   | 105°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 4536.5 | 4536.5 | 4536.5 | 4536.5 | 4536.5 | 4536.5 | 4536.5 | 4536.5 | 4536.5 | 4536.5 | 4536.5 |
| 2.5°  | 4455.7 | 4422.5 | 4392.3 | 4362.4 | 4336.2 | 4309.8 | 4283.4 | 4257.1 | 4236.7 | 4216.2 | 4199.6 |
| 5°    | 4386.5 | 4323.2 | 4270.4 | 4217.6 | 4170.9 | 4124.3 | 4082.0 | 4039.5 | 4006.9 | 3974.2 | 3951.4 |
| 7.5°  | 4351.2 | 4267.6 | 4197.9 | 4128.3 | 4069.7 | 4010.8 | 3958.9 | 3907.2 | 3868.3 | 3829.7 | 3802.5 |
| 10°   | 4353.7 | 4265.3 | 4195.6 | 4126.0 | 4062.8 | 3999.4 | 3941.1 | 3882.8 | 3836.6 | 3790.0 | 3759.8 |
| 12.5° | 4378.4 | 4306.3 | 4260.1 | 4214.1 | 4164.3 | 4114.9 | 4054.5 | 3994.2 | 3935.1 | 3875.8 | 3836.7 |
| 15°   | 4379.1 | 4344.7 | 4350.9 | 4357.2 | 4344.4 | 4331.4 | 4279.1 | 4226.6 | 4142.3 | 4058.2 | 3998.6 |
| 17.5° | 4313.3 | 4325.9 | 4401.8 | 4477.6 | 4518.0 | 4558.3 | 4515.9 | 4473.8 | 4362.2 | 4250.7 | 4162.9 |
| 20°   | 4175.2 | 4234.5 | 4366.3 | 4498.2 | 4582.7 | 4667.0 | 4647.6 | 4627.9 | 4500.3 | 4372.9 | 4265.3 |
| 22.5° | 3994.2 | 4081.8 | 4232.2 | 4383.0 | 4492.8 | 4602.7 | 4614.4 | 4626.1 | 4504.3 | 4382.4 | 4271.7 |
| 25°   | 3804.5 | 3905.5 | 4040.8 | 4176.2 | 4284.3 | 4392.3 | 4432.7 | 4473.0 | 4373.1 | 4273.3 | 4174.7 |
| 27.5° | 3623.5 | 3721.0 | 3832.2 | 3943.3 | 4029.9 | 4116.6 | 4161.5 | 4206.6 | 4135.5 | 4064.4 | 3988.0 |
| 30°   | 3447.1 | 3524.8 | 3617.0 | 3709.3 | 3781.1 | 3853.3 | 3889.8 | 3926.4 | 3872.2 | 3817.9 | 3763.3 |
| 32.5° | 3278.8 | 3324.6 | 3398.2 | 3472.0 | 3541.0 | 3610.0 | 3650.6 | 3691.3 | 3641.5 | 3591.6 | 3547.9 |
| 35°   | 3116.4 | 3129.1 | 3185.3 | 3241.4 | 3309.6 | 3378.0 | 3426.8 | 3475.5 | 3440.0 | 3404.6 | 3364.3 |
| 37.5° | 2954.5 | 2940.5 | 2980.9 | 3021.2 | 3089.2 | 3157.4 | 3217.7 | 3278.0 | 3261.5 | 3245.1 | 3208.1 |
| 40°   | 2788.6 | 2757.0 | 2786.2 | 2815.2 | 2881.0 | 2946.8 | 3016.1 | 3085.6 | 3089.6 | 3093.3 | 3061.9 |
| 42.5° | 2620.7 | 2579.0 | 2602.7 | 2626.5 | 2688.8 | 2751.3 | 2826.1 | 2901.1 | 2921.0 | 2941.0 | 2914.4 |
| 45°   | 2465.1 | 2424.5 | 2444.4 | 2464.6 | 2523.8 | 2583.0 | 2660.6 | 2738.3 | 2767.0 | 2795.7 | 2771.7 |
| 47.5° | 2332.0 | 2297.8 | 2316.6 | 2335.3 | 2393.3 | 2451.1 | 2527.6 | 2604.2 | 2637.3 | 2670.3 | 2653.6 |
| 50°   | 2212.7 | 2182.6 | 2211.8 | 2241.3 | 2295.9 | 2350.4 | 2419.0 | 2487.6 | 2530.1 | 2572.5 | 2571.5 |
| 52.5° | 2121.3 | 2091.5 | 2135.6 | 2179.5 | 2229.6 | 2279.6 | 2343.5 | 2407.5 | 2457.8 | 2508.2 | 2517.2 |
| 55°   | 2055.2 | 2008.0 | 2070.5 | 2132.8 | 2186.7 | 2240.8 | 2296.8 | 2352.7 | 2406.0 | 2459.4 | 2471.9 |
| 57.5° | 2004.4 | 1935.4 | 2002.6 | 2069.8 | 2133.1 | 2196.6 | 2251.9 | 2307.4 | 2361.2 | 2414.8 | 2427.5 |
| 60°   | 1956.5 | 1867.0 | 1926.0 | 1984.8 | 2057.6 | 2130.4 | 2186.6 | 2243.0 | 2296.9 | 2350.9 | 2364.9 |
| 62.5° | 1902.0 | 1790.4 | 1827.8 | 1865.3 | 1950.1 | 2034.9 | 2095.0 | 2155.1 | 2204.6 | 2254.0 | 2267.4 |
| 65°   | 1827.5 | 1708.6 | 1723.0 | 1737.3 | 1828.2 | 1919.2 | 1976.7 | 2034.1 | 2077.7 | 2121.1 | 2134.9 |
| 67.5° | 1726.8 | 1628.0 | 1623.5 | 1618.9 | 1702.8 | 1786.9 | 1841.4 | 1895.7 | 1933.4 | 1971.0 | 1984.3 |
| 70°   | 1602.6 | 1532.3 | 1516.6 | 1500.9 | 1574.7 | 1648.5 | 1695.6 | 1742.5 | 1776.4 | 1810.5 | 1823.3 |
| 72.5° | 1454.5 | 1406.2 | 1383.2 | 1360.4 | 1418.6 | 1476.5 | 1519.0 | 1561.5 | 1594.7 | 1628.0 | 1643.3 |
| 75°   | 1272.3 | 1235.1 | 1213.2 | 1191.0 | 1234.2 | 1277.4 | 1315.9 | 1354.3 | 1384.7 | 1414.9 | 1430.9 |
| 77.5° | 1086.1 | 1056.3 | 1034.0 | 1011.8 | 1046.9 | 1081.9 | 1115.0 | 1148.0 | 1179.9 | 1211.6 | 1226.5 |
| 80°   | 870.2  | 845.1  | 826.6  | 807.7  | 837.0  | 866.0  | 893.9  | 921.8  | 946.0  | 970.0  | 989.8  |
| 82.5° | 646.2  | 634.0  | 620.7  | 607.5  | 605.1  | 602.7  | 593.0  | 583.1  | 634.7  | 686.2  | 720.0  |
| 85°   | 420.4  | 407.3  | 392.6  | 377.7  | 365.2  | 352.5  | 325.5  | 298.6  | 346.8  | 395.1  | 437.0  |
| 87.5° | 186.2  | 181.0  | 178.2  | 175.5  | 175.0  | 174.5  | 153.9  | 133.1  | 153.3  | 173.7  | 190.6  |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P965154

CATALOG NUMBER: NAV-SB3D-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

|       | 110°   | 115°   | 120°   | 125°   | 130°   | 135°   | 140°   | 145°   | 150°   | 155°   | 160°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 4536.5 | 4536.5 | 4536.5 | 4536.5 | 4536.5 | 4536.5 | 4536.5 | 4536.5 | 4536.5 | 4536.5 | 4536.5 |
| 2.5°  | 4183.1 | 4170.2 | 4157.4 | 4145.5 | 4133.5 | 4118.8 | 4133.5 | 4145.5 | 4157.4 | 4170.2 | 4183.1 |
| 5°    | 3928.6 | 3912.4 | 3896.2 | 3883.8 | 3871.5 | 3859.3 | 3871.5 | 3883.8 | 3896.2 | 3912.4 | 3928.6 |
| 7.5°  | 3775.4 | 3756.8 | 3738.4 | 3727.2 | 3716.2 | 3707.8 | 3716.2 | 3727.2 | 3738.4 | 3756.8 | 3775.4 |
| 10°   | 3729.2 | 3711.5 | 3694.0 | 3684.6 | 3675.1 | 3671.3 | 3675.1 | 3684.6 | 3694.0 | 3711.5 | 3729.2 |
| 12.5° | 3797.5 | 3777.8 | 3758.4 | 3750.4 | 3742.4 | 3740.9 | 3742.4 | 3750.4 | 3758.4 | 3777.8 | 3797.5 |
| 15°   | 3939.1 | 3911.7 | 3884.5 | 3874.1 | 3863.6 | 3862.8 | 3863.6 | 3874.1 | 3884.5 | 3911.7 | 3939.1 |
| 17.5° | 4075.2 | 4034.8 | 3994.2 | 3981.0 | 3967.6 | 3965.5 | 3967.6 | 3981.0 | 3994.2 | 4034.8 | 4075.2 |
| 20°   | 4157.9 | 4106.2 | 4054.3 | 4037.8 | 4021.2 | 4016.1 | 4021.2 | 4037.8 | 4054.3 | 4106.2 | 4157.9 |
| 22.5° | 4160.9 | 4106.4 | 4051.7 | 4033.4 | 4015.1 | 4007.3 | 4015.1 | 4033.4 | 4051.7 | 4106.4 | 4160.9 |
| 25°   | 4076.6 | 4029.3 | 3982.0 | 3964.8 | 3947.8 | 3937.6 | 3947.8 | 3964.8 | 3982.0 | 4029.3 | 4076.6 |
| 27.5° | 3911.6 | 3879.8 | 3848.1 | 3840.2 | 3832.4 | 3829.7 | 3832.4 | 3840.2 | 3848.1 | 3879.8 | 3911.6 |
| 30°   | 3708.2 | 3692.0 | 3675.6 | 3675.6 | 3675.6 | 3678.3 | 3675.6 | 3675.6 | 3675.6 | 3692.0 | 3708.2 |
| 32.5° | 3504.2 | 3493.6 | 3483.0 | 3484.4 | 3485.9 | 3488.6 | 3485.9 | 3484.4 | 3483.0 | 3493.6 | 3504.2 |
| 35°   | 3324.1 | 3307.9 | 3291.8 | 3288.3 | 3284.9 | 3283.2 | 3284.9 | 3288.3 | 3291.8 | 3307.9 | 3324.1 |
| 37.5° | 3170.8 | 3141.4 | 3112.2 | 3096.7 | 3081.1 | 3072.5 | 3081.1 | 3096.7 | 3112.2 | 3141.4 | 3170.8 |
| 40°   | 3030.4 | 2987.6 | 2945.0 | 2916.1 | 2887.6 | 2870.5 | 2887.6 | 2916.1 | 2945.0 | 2987.6 | 3030.4 |
| 42.5° | 2887.9 | 2834.8 | 2781.7 | 2739.8 | 2697.9 | 2670.3 | 2697.9 | 2739.8 | 2781.7 | 2834.8 | 2887.9 |
| 45°   | 2747.8 | 2687.0 | 2626.5 | 2577.3 | 2528.0 | 2496.3 | 2528.0 | 2577.3 | 2626.5 | 2687.0 | 2747.8 |
| 47.5° | 2636.9 | 2583.0 | 2529.0 | 2483.4 | 2438.0 | 2407.5 | 2438.0 | 2483.4 | 2529.0 | 2583.0 | 2636.9 |
| 50°   | 2570.8 | 2527.6 | 2484.5 | 2442.4 | 2400.2 | 2370.9 | 2400.2 | 2442.4 | 2484.5 | 2527.6 | 2570.8 |
| 52.5° | 2526.2 | 2491.1 | 2455.9 | 2418.2 | 2380.6 | 2353.5 | 2380.6 | 2418.2 | 2455.9 | 2491.1 | 2526.2 |
| 55°   | 2484.5 | 2453.8 | 2423.2 | 2390.1 | 2357.0 | 2332.7 | 2357.0 | 2390.1 | 2423.2 | 2453.8 | 2484.5 |
| 57.5° | 2440.2 | 2409.3 | 2378.3 | 2345.5 | 2312.6 | 2287.4 | 2312.6 | 2345.5 | 2378.3 | 2409.3 | 2440.2 |
| 60°   | 2378.8 | 2348.5 | 2318.3 | 2284.6 | 2250.8 | 2224.8 | 2250.8 | 2284.6 | 2318.3 | 2348.5 | 2378.8 |
| 62.5° | 2280.8 | 2253.5 | 2226.1 | 2190.6 | 2155.1 | 2123.8 | 2155.1 | 2190.6 | 2226.1 | 2253.5 | 2280.8 |
| 65°   | 2148.5 | 2122.2 | 2095.9 | 2061.5 | 2027.1 | 2000.2 | 2027.1 | 2061.5 | 2095.9 | 2122.2 | 2148.5 |
| 67.5° | 1997.5 | 1973.3 | 1949.3 | 1917.3 | 1885.3 | 1860.9 | 1885.3 | 1917.3 | 1949.3 | 1973.3 | 1997.5 |
| 70°   | 1836.2 | 1816.5 | 1796.8 | 1766.2 | 1735.5 | 1707.8 | 1735.5 | 1766.2 | 1796.8 | 1816.5 | 1836.2 |
| 72.5° | 1658.7 | 1642.3 | 1625.9 | 1596.6 | 1567.5 | 1540.6 | 1567.5 | 1596.6 | 1625.9 | 1642.3 | 1658.7 |
| 75°   | 1447.0 | 1438.9 | 1430.9 | 1406.4 | 1381.8 | 1356.1 | 1381.8 | 1406.4 | 1430.9 | 1438.9 | 1447.0 |
| 77.5° | 1241.6 | 1230.4 | 1218.9 | 1194.2 | 1169.4 | 1148.9 | 1169.4 | 1194.2 | 1218.9 | 1230.4 | 1241.6 |
| 80°   | 1009.6 | 1004.8 | 1000.1 | 966.9  | 933.4  | 894.7  | 933.4  | 966.9  | 1000.1 | 1004.8 | 1009.6 |
| 82.5° | 753.8  | 751.6  | 749.4  | 721.4  | 693.2  | 668.5  | 693.2  | 721.4  | 749.4  | 751.6  | 753.8  |
| 85°   | 478.7  | 475.2  | 471.7  | 449.8  | 427.8  | 405.6  | 427.8  | 449.8  | 471.7  | 475.2  | 478.7  |
| 87.5° | 207.5  | 203.4  | 198.7  | 187.7  | 176.2  | 165.3  | 176.2  | 187.7  | 198.7  | 203.4  | 207.5  |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P965154

CATALOG NUMBER: NAV-SB3D-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

|       | 165°   | 170°   | 175°   | 180°   | 185°   | 190°   | 195°   | 200°   | 205°   | 210°   | 215°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 4536.5 | 4536.5 | 4536.5 | 4536.5 | 4536.5 | 4536.5 | 4536.5 | 4536.5 | 4536.5 | 4536.5 | 4536.5 |
| 2.5°  | 4199.6 | 4216.2 | 4236.7 | 4257.1 | 4283.4 | 4309.8 | 4336.2 | 4362.4 | 4392.3 | 4422.5 | 4455.7 |
| 5°    | 3951.4 | 3974.2 | 4006.9 | 4039.5 | 4082.0 | 4124.3 | 4170.9 | 4217.6 | 4270.4 | 4323.2 | 4386.5 |
| 7.5°  | 3802.5 | 3829.7 | 3868.3 | 3907.2 | 3958.9 | 4010.8 | 4069.7 | 4128.3 | 4197.9 | 4267.6 | 4351.2 |
| 10°   | 3759.8 | 3790.0 | 3836.6 | 3882.8 | 3941.1 | 3999.4 | 4062.8 | 4126.0 | 4195.6 | 4265.3 | 4353.7 |
| 12.5° | 3836.7 | 3875.8 | 3935.1 | 3994.2 | 4054.5 | 4114.9 | 4164.3 | 4214.1 | 4260.1 | 4306.3 | 4378.4 |
| 15°   | 3998.6 | 4058.2 | 4142.3 | 4226.6 | 4279.1 | 4331.4 | 4344.4 | 4357.2 | 4350.9 | 4344.7 | 4379.1 |
| 17.5° | 4162.9 | 4250.7 | 4362.2 | 4473.8 | 4515.9 | 4558.3 | 4518.0 | 4477.6 | 4401.8 | 4325.9 | 4313.3 |
| 20°   | 4265.3 | 4372.9 | 4500.3 | 4627.9 | 4647.6 | 4667.0 | 4582.7 | 4498.2 | 4366.3 | 4234.5 | 4175.2 |
| 22.5° | 4271.7 | 4382.4 | 4504.3 | 4626.1 | 4614.4 | 4602.7 | 4492.8 | 4383.0 | 4232.2 | 4081.8 | 3994.2 |
| 25°   | 4174.7 | 4273.3 | 4373.1 | 4473.0 | 4432.7 | 4392.3 | 4284.3 | 4176.2 | 4040.8 | 3905.5 | 3804.5 |
| 27.5° | 3988.0 | 4064.4 | 4135.5 | 4206.6 | 4161.5 | 4116.6 | 4029.9 | 3943.3 | 3832.2 | 3721.0 | 3623.5 |
| 30°   | 3763.3 | 3817.9 | 3872.2 | 3926.4 | 3889.8 | 3853.3 | 3781.1 | 3709.3 | 3617.0 | 3524.8 | 3447.1 |
| 32.5° | 3547.9 | 3591.6 | 3641.5 | 3691.3 | 3650.6 | 3610.0 | 3541.0 | 3472.0 | 3398.2 | 3324.6 | 3278.8 |
| 35°   | 3364.3 | 3404.6 | 3440.0 | 3475.5 | 3426.8 | 3378.0 | 3309.6 | 3241.4 | 3185.3 | 3129.1 | 3116.4 |
| 37.5° | 3208.1 | 3245.1 | 3261.5 | 3278.0 | 3217.7 | 3157.4 | 3089.2 | 3021.2 | 2980.9 | 2940.5 | 2954.5 |
| 40°   | 3061.9 | 3093.3 | 3089.6 | 3085.6 | 3016.1 | 2946.8 | 2881.0 | 2815.2 | 2786.2 | 2757.0 | 2788.6 |
| 42.5° | 2914.4 | 2941.0 | 2921.0 | 2901.1 | 2826.1 | 2751.3 | 2688.8 | 2626.5 | 2602.7 | 2579.0 | 2620.7 |
| 45°   | 2771.7 | 2795.7 | 2767.0 | 2738.3 | 2660.6 | 2583.0 | 2523.8 | 2464.6 | 2444.4 | 2424.5 | 2465.1 |
| 47.5° | 2653.6 | 2670.3 | 2637.3 | 2604.2 | 2527.6 | 2451.1 | 2393.3 | 2335.3 | 2316.6 | 2297.8 | 2332.0 |
| 50°   | 2571.5 | 2572.5 | 2530.1 | 2487.6 | 2419.0 | 2350.4 | 2295.9 | 2241.3 | 2211.8 | 2182.6 | 2212.7 |
| 52.5° | 2517.2 | 2508.2 | 2457.8 | 2407.5 | 2343.5 | 2279.6 | 2229.6 | 2179.5 | 2135.6 | 2091.5 | 2121.3 |
| 55°   | 2471.9 | 2459.4 | 2406.0 | 2352.7 | 2296.8 | 2240.8 | 2186.7 | 2132.8 | 2070.5 | 2008.0 | 2055.2 |
| 57.5° | 2427.5 | 2414.8 | 2361.2 | 2307.4 | 2251.9 | 2196.6 | 2133.1 | 2069.8 | 2002.6 | 1935.4 | 2004.4 |
| 60°   | 2364.9 | 2350.9 | 2296.9 | 2243.0 | 2186.6 | 2130.4 | 2057.6 | 1984.8 | 1926.0 | 1867.0 | 1956.5 |
| 62.5° | 2267.4 | 2254.0 | 2204.6 | 2155.1 | 2095.0 | 2034.9 | 1950.1 | 1865.3 | 1827.8 | 1790.4 | 1902.0 |
| 65°   | 2134.9 | 2121.1 | 2077.7 | 2034.1 | 1976.7 | 1919.2 | 1828.2 | 1737.3 | 1723.0 | 1708.6 | 1827.5 |
| 67.5° | 1984.3 | 1971.0 | 1933.4 | 1895.7 | 1841.4 | 1786.9 | 1702.8 | 1618.9 | 1623.5 | 1628.0 | 1726.8 |
| 70°   | 1823.3 | 1810.5 | 1776.4 | 1742.5 | 1695.6 | 1648.5 | 1574.7 | 1500.9 | 1516.6 | 1532.3 | 1602.6 |
| 72.5° | 1643.3 | 1628.0 | 1594.7 | 1561.5 | 1519.0 | 1476.5 | 1418.6 | 1360.4 | 1383.2 | 1406.2 | 1454.5 |
| 75°   | 1430.9 | 1414.9 | 1384.7 | 1354.3 | 1315.9 | 1277.4 | 1234.2 | 1191.0 | 1213.2 | 1235.1 | 1272.3 |
| 77.5° | 1226.5 | 1211.6 | 1179.9 | 1148.0 | 1115.0 | 1081.9 | 1046.9 | 1011.8 | 1034.0 | 1056.3 | 1086.1 |
| 80°   | 989.8  | 970.0  | 946.0  | 921.8  | 893.9  | 866.0  | 837.0  | 807.7  | 826.6  | 845.1  | 870.2  |
| 82.5° | 720.0  | 686.2  | 634.7  | 583.1  | 593.0  | 602.7  | 605.1  | 607.5  | 620.7  | 634.0  | 646.2  |
| 85°   | 437.0  | 395.1  | 346.8  | 298.6  | 325.5  | 352.5  | 365.2  | 377.7  | 392.6  | 407.3  | 420.4  |
| 87.5° | 190.6  | 173.7  | 153.3  | 133.1  | 153.9  | 174.5  | 175.0  | 175.5  | 178.2  | 181.0  | 186.2  |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P965154

CATALOG NUMBER: NAV-SB3D-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

|       | 220°   | 225°   | 230°   | 235°   | 240°   | 245°   | 250°   | 255°   | 260°    | 265°    | 270°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|---------|---------|---------|
| 0°    | 4536.5 | 4536.5 | 4536.5 | 4536.5 | 4536.5 | 4536.5 | 4536.5 | 4536.5 | 4536.5  | 4536.5  | 4536.5  |
| 2.5°  | 4489.2 | 4530.4 | 4567.5 | 4605.7 | 4644.1 | 4684.1 | 4724.1 | 4763.9 | 4803.7  | 4841.2  | 4878.6  |
| 5°    | 4449.4 | 4521.7 | 4594.8 | 4672.3 | 4749.7 | 4832.6 | 4915.6 | 4998.0 | 5080.5  | 5163.2  | 5245.8  |
| 7.5°  | 4435.2 | 4528.7 | 4628.4 | 4736.5 | 4844.7 | 4967.4 | 5090.0 | 5216.1 | 5342.1  | 5478.4  | 5615.0  |
| 10°   | 4442.1 | 4542.6 | 4665.7 | 4793.8 | 4921.5 | 5070.8 | 5219.7 | 5386.2 | 5552.7  | 5725.2  | 5897.7  |
| 12.5° | 4450.9 | 4544.3 | 4673.7 | 4818.3 | 4962.9 | 5138.8 | 5314.6 | 5503.3 | 5692.0  | 5881.4  | 6071.0  |
| 15°   | 4413.8 | 4488.6 | 4631.9 | 4799.4 | 4966.8 | 5169.3 | 5371.7 | 5576.4 | 5781.2  | 5978.7  | 6176.3  |
| 17.5° | 4300.6 | 4346.7 | 4515.2 | 4716.6 | 4918.1 | 5153.1 | 5388.1 | 5611.5 | 5834.8  | 6035.1  | 6235.5  |
| 20°   | 4116.1 | 4128.3 | 4324.5 | 4574.1 | 4823.8 | 5108.5 | 5393.3 | 5638.7 | 5884.2  | 6092.6  | 6300.8  |
| 22.5° | 3906.7 | 3882.8 | 4106.2 | 4406.8 | 4707.4 | 5053.9 | 5400.3 | 5675.6 | 5950.8  | 6163.8  | 6376.5  |
| 25°   | 3703.5 | 3639.2 | 3868.0 | 4220.0 | 4572.2 | 4999.8 | 5427.8 | 5742.6 | 6057.0  | 6265.4  | 6474.0  |
| 27.5° | 3526.0 | 3447.6 | 3656.0 | 4049.3 | 4442.5 | 4963.9 | 5485.2 | 5847.0 | 6208.5  | 6407.5  | 6606.3  |
| 30°   | 3369.8 | 3308.4 | 3483.4 | 3906.5 | 4329.7 | 4947.0 | 5563.9 | 5982.2 | 6400.5  | 6592.6  | 6784.7  |
| 32.5° | 3233.0 | 3205.7 | 3346.6 | 3783.5 | 4220.0 | 4926.0 | 5631.8 | 6123.5 | 6615.0  | 6805.1  | 6995.3  |
| 35°   | 3103.8 | 3115.2 | 3232.6 | 3662.4 | 4092.2 | 4886.8 | 5681.6 | 6284.3 | 6886.9  | 7069.2  | 7251.3  |
| 37.5° | 2968.4 | 3009.8 | 3112.5 | 3520.1 | 3927.6 | 4819.3 | 5711.2 | 6464.5 | 7217.6  | 7449.9  | 7682.1  |
| 40°   | 2820.1 | 2883.6 | 2976.7 | 3350.1 | 3723.5 | 4726.6 | 5729.9 | 6693.1 | 7656.3  | 7994.8  | 8333.1  |
| 42.5° | 2662.5 | 2742.6 | 2828.4 | 3162.6 | 3496.9 | 4630.8 | 5765.1 | 6992.4 | 8219.7  | 8708.1  | 9196.6  |
| 45°   | 2505.8 | 2583.3 | 2670.3 | 2963.5 | 3256.6 | 4541.9 | 5827.3 | 7386.2 | 8945.1  | 9603.9  | 10262.8 |
| 47.5° | 2366.1 | 2432.7 | 2545.1 | 2805.9 | 3066.9 | 4468.4 | 5870.0 | 7805.7 | 9741.5  | 10668.9 | 11596.2 |
| 50°   | 2243.0 | 2320.5 | 2468.1 | 2701.4 | 2934.6 | 4388.3 | 5842.1 | 8195.0 | 10547.8 | 11946.0 | 13344.1 |
| 52.5° | 2151.3 | 2259.5 | 2429.2 | 2632.4 | 2835.8 | 4253.1 | 5670.6 | 8447.7 | 11224.6 | 13287.5 | 15350.3 |
| 55°   | 2102.5 | 2265.7 | 2423.5 | 2582.5 | 2741.4 | 4028.9 | 5316.4 | 8392.0 | 11467.5 | 14476.8 | 17486.2 |
| 57.5° | 2073.3 | 2271.7 | 2411.0 | 2523.2 | 2635.6 | 3712.8 | 4789.8 | 8000.0 | 11210.3 | 15319.6 | 19429.0 |
| 60°   | 2045.8 | 2252.5 | 2344.5 | 2432.7 | 2521.0 | 3302.2 | 4083.5 | 7270.4 | 10457.3 | 15530.3 | 20603.1 |
| 62.5° | 2013.7 | 2205.6 | 2216.9 | 2275.4 | 2334.0 | 2811.1 | 3288.0 | 6283.9 | 9279.8  | 14643.4 | 20006.9 |
| 65°   | 1946.2 | 2092.4 | 2091.0 | 2118.7 | 2146.4 | 2369.1 | 2591.7 | 5277.4 | 7963.2  | 13388.4 | 18813.6 |
| 67.5° | 1825.7 | 1907.9 | 1911.7 | 1896.5 | 1880.9 | 1944.3 | 2007.5 | 4291.4 | 6575.3  | 11895.0 | 17214.7 |
| 70°   | 1672.9 | 1699.9 | 1699.9 | 1628.3 | 1556.6 | 1538.7 | 1520.6 | 3378.9 | 5237.1  | 10265.5 | 15293.7 |
| 72.5° | 1502.6 | 1502.3 | 1485.2 | 1383.7 | 1282.1 | 1227.4 | 1172.9 | 2583.2 | 3993.4  | 8498.9  | 13004.6 |
| 75°   | 1309.4 | 1316.0 | 1237.4 | 1123.5 | 1009.6 | 960.2  | 910.8  | 1874.8 | 2838.8  | 6473.8  | 10108.8 |
| 77.5° | 1115.8 | 1119.3 | 989.6  | 879.1  | 768.5  | 734.8  | 701.2  | 1270.4 | 1839.7  | 4531.1  | 7222.6  |
| 80°   | 895.1  | 895.6  | 740.7  | 647.2  | 553.6  | 539.7  | 525.7  | 818.6  | 1111.5  | 2919.3  | 4727.1  |
| 82.5° | 658.4  | 651.1  | 518.8  | 449.8  | 380.9  | 378.1  | 375.7  | 503.5  | 631.6   | 1689.6  | 2747.8  |
| 85°   | 433.5  | 423.8  | 325.5  | 275.0  | 224.6  | 225.9  | 227.1  | 269.2  | 311.3   | 760.0   | 1209.0  |
| 87.5° | 191.5  | 179.3  | 138.4  | 117.7  | 97.2   | 98.4   | 99.5   | 111.6  | 123.6   | 249.0   | 374.2   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     |

REPORT NUMBER: P965154

CATALOG NUMBER: NAV-SB3D-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

|       | 275°    | 280°    | 285°    | 290°    | 295°    | 300°    | 305°    | 310°    | 315°    | 320°    | 325°    |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°    | 4536.5  | 4536.5  | 4536.5  | 4536.5  | 4536.5  | 4536.5  | 4536.5  | 4536.5  | 4536.5  | 4536.5  | 4536.5  |
| 2.5°  | 4897.0  | 4915.6  | 4941.9  | 4968.2  | 4983.9  | 4999.5  | 5007.4  | 5015.2  | 5011.7  | 5015.2  | 5007.4  |
| 5°    | 5310.4  | 5375.2  | 5439.3  | 5503.5  | 5538.3  | 5573.1  | 5594.2  | 5615.5  | 5631.5  | 5615.5  | 5594.2  |
| 7.5°  | 5720.0  | 5825.1  | 5919.6  | 6014.1  | 6071.0  | 6128.0  | 6158.7  | 6189.4  | 6204.2  | 6189.4  | 6158.7  |
| 10°   | 6022.1  | 6146.4  | 6257.3  | 6368.1  | 6435.4  | 6502.2  | 6532.1  | 6561.9  | 6573.2  | 6561.9  | 6532.1  |
| 12.5° | 6205.8  | 6340.3  | 6440.6  | 6540.5  | 6589.2  | 6638.0  | 6654.3  | 6670.7  | 6672.4  | 6670.7  | 6654.3  |
| 15°   | 6292.6  | 6408.7  | 6471.5  | 6534.6  | 6536.3  | 6538.1  | 6520.6  | 6503.2  | 6482.7  | 6503.2  | 6520.6  |
| 17.5° | 6314.0  | 6392.5  | 6393.7  | 6394.8  | 6324.2  | 6253.8  | 6189.2  | 6124.5  | 6078.9  | 6124.5  | 6189.2  |
| 20°   | 6328.1  | 6355.6  | 6272.9  | 6190.3  | 6034.6  | 5879.0  | 5765.6  | 5652.4  | 5582.7  | 5652.4  | 5765.6  |
| 22.5° | 6340.6  | 6304.8  | 6133.5  | 5962.2  | 5733.3  | 5504.4  | 5362.7  | 5220.9  | 5144.1  | 5220.9  | 5362.7  |
| 25°   | 6360.8  | 6247.7  | 5987.6  | 5727.6  | 5449.5  | 5171.5  | 5022.5  | 4873.9  | 4801.1  | 4873.9  | 5022.5  |
| 27.5° | 6404.0  | 6201.6  | 5857.1  | 5512.8  | 5204.6  | 4896.5  | 4750.0  | 4603.5  | 4534.8  | 4603.5  | 4750.0  |
| 30°   | 6483.0  | 6181.6  | 5757.5  | 5333.4  | 5012.5  | 4691.4  | 4555.5  | 4419.5  | 4355.4  | 4419.5  | 4555.5  |
| 32.5° | 6582.2  | 6169.4  | 5689.6  | 5209.9  | 4908.1  | 4606.5  | 4499.8  | 4392.8  | 4346.7  | 4392.8  | 4499.8  |
| 35°   | 6745.7  | 6240.4  | 5740.4  | 5240.6  | 5031.0  | 4821.6  | 4796.8  | 4771.9  | 4768.0  | 4771.9  | 4796.8  |
| 37.5° | 7087.5  | 6492.8  | 6038.5  | 5584.1  | 5570.6  | 5556.9  | 5670.8  | 5784.7  | 5843.8  | 5784.7  | 5670.8  |
| 40°   | 7686.5  | 7039.8  | 6701.9  | 6364.0  | 6602.4  | 6841.0  | 7117.7  | 7394.6  | 7532.4  | 7394.6  | 7117.7  |
| 42.5° | 8555.0  | 7913.3  | 7718.7  | 7524.0  | 8044.2  | 8564.4  | 9067.8  | 9571.2  | 9866.8  | 9571.2  | 9067.8  |
| 45°   | 9686.5  | 9109.9  | 9024.1  | 8938.1  | 9771.4  | 10604.9 | 11432.1 | 12259.5 | 12761.8 | 12259.5 | 11432.1 |
| 47.5° | 11035.6 | 10474.7 | 10457.3 | 10439.8 | 11642.1 | 12843.9 | 14055.0 | 15265.8 | 15977.0 | 15265.8 | 14055.0 |
| 50°   | 12651.4 | 11958.9 | 11961.9 | 11964.8 | 13514.1 | 15063.4 | 16662.0 | 18260.6 | 19227.1 | 18260.6 | 16662.0 |
| 52.5° | 14511.5 | 13673.0 | 13588.2 | 13503.4 | 15354.0 | 17204.6 | 19182.5 | 21160.2 | 22318.7 | 21160.2 | 19182.5 |
| 55°   | 16657.6 | 15829.0 | 15498.4 | 15167.8 | 17227.6 | 19287.1 | 21645.0 | 24002.8 | 25380.7 | 24002.8 | 21645.0 |
| 57.5° | 18977.8 | 18526.4 | 17863.3 | 17200.4 | 19280.1 | 21359.9 | 24030.5 | 26701.1 | 28409.7 | 26701.1 | 24030.5 |
| 60°   | 21304.0 | 22005.0 | 21181.6 | 20358.1 | 22326.3 | 24294.4 | 27153.9 | 30013.3 | 31860.0 | 30013.3 | 27153.9 |
| 62.5° | 21922.0 | 23837.0 | 23744.2 | 23651.3 | 25454.1 | 27257.3 | 29977.8 | 32698.1 | 34404.9 | 32698.1 | 29977.8 |
| 65°   | 20610.9 | 22408.3 | 22763.9 | 23119.4 | 25410.7 | 27702.1 | 30340.1 | 32977.8 | 34431.1 | 32977.8 | 30340.1 |
| 67.5° | 18924.2 | 20633.6 | 20800.3 | 20967.0 | 23354.2 | 25741.4 | 28390.8 | 31040.1 | 32178.5 | 31040.1 | 28390.8 |
| 70°   | 17153.1 | 19012.5 | 19087.0 | 19161.8 | 21296.6 | 23431.4 | 25711.3 | 27991.0 | 28623.8 | 27991.0 | 25711.3 |
| 72.5° | 15138.2 | 17272.1 | 17325.8 | 17379.2 | 19049.4 | 20719.8 | 22427.3 | 24134.6 | 24198.7 | 24134.6 | 22427.3 |
| 75°   | 12317.1 | 14525.5 | 14723.8 | 14922.1 | 16221.5 | 17521.0 | 18723.1 | 19925.1 | 19603.0 | 19925.1 | 18723.1 |
| 77.5° | 9283.9  | 11345.6 | 11629.3 | 11913.1 | 12901.0 | 13888.9 | 14741.3 | 15594.0 | 15040.4 | 15594.0 | 14741.3 |
| 80°   | 6461.5  | 8195.6  | 8548.3  | 8901.0  | 9647.1  | 10392.9 | 10840.6 | 11288.1 | 10397.7 | 11288.1 | 10840.6 |
| 82.5° | 3933.5  | 5119.4  | 5513.3  | 5907.4  | 6420.9  | 6934.4  | 7121.2  | 7307.8  | 6608.1  | 7307.8  | 7121.2  |
| 85°   | 1838.2  | 2467.6  | 2802.7  | 3137.7  | 3559.7  | 3981.5  | 4087.6  | 4193.6  | 3633.0  | 4193.6  | 4087.6  |
| 87.5° | 585.8   | 797.2   | 984.2   | 1171.2  | 1382.2  | 1593.2  | 1602.2  | 1611.1  | 1352.6  | 1611.1  | 1602.2  |
| 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |

REPORT NUMBER: P965154

CATALOG NUMBER: NAV-SB3D-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

|       | 330°    | 335°    | 340°    | 345°    | 350°    | 355°    | 360°    |
|-------|---------|---------|---------|---------|---------|---------|---------|
| 0°    | 4536.5  | 4536.5  | 4536.5  | 4536.5  | 4536.5  | 4536.5  | 4536.5  |
| 2.5°  | 4999.5  | 4983.9  | 4968.2  | 4941.9  | 4915.6  | 4897.0  | 4878.6  |
| 5°    | 5573.1  | 5538.3  | 5503.5  | 5439.3  | 5375.2  | 5310.4  | 5245.8  |
| 7.5°  | 6128.0  | 6071.0  | 6014.1  | 5919.6  | 5825.1  | 5720.0  | 5615.0  |
| 10°   | 6502.2  | 6435.4  | 6368.1  | 6257.3  | 6146.4  | 6022.1  | 5897.7  |
| 12.5° | 6638.0  | 6589.2  | 6540.5  | 6440.6  | 6340.3  | 6205.8  | 6071.0  |
| 15°   | 6538.1  | 6536.3  | 6534.6  | 6471.5  | 6408.7  | 6292.6  | 6176.3  |
| 17.5° | 6253.8  | 6324.2  | 6394.8  | 6393.7  | 6392.5  | 6314.0  | 6235.5  |
| 20°   | 5879.0  | 6034.6  | 6190.3  | 6272.9  | 6355.6  | 6328.1  | 6300.8  |
| 22.5° | 5504.4  | 5733.3  | 5962.2  | 6133.5  | 6304.8  | 6340.6  | 6376.5  |
| 25°   | 5171.5  | 5449.5  | 5727.6  | 5987.6  | 6247.7  | 6360.8  | 6474.0  |
| 27.5° | 4896.5  | 5204.6  | 5512.8  | 5857.1  | 6201.6  | 6404.0  | 6606.3  |
| 30°   | 4691.4  | 5012.5  | 5333.4  | 5757.5  | 6181.6  | 6483.0  | 6784.7  |
| 32.5° | 4606.5  | 4908.1  | 5209.9  | 5689.6  | 6169.4  | 6582.2  | 6995.3  |
| 35°   | 4821.6  | 5031.0  | 5240.6  | 5740.4  | 6240.4  | 6745.7  | 7251.3  |
| 37.5° | 5556.9  | 5570.6  | 5584.1  | 6038.5  | 6492.8  | 7087.5  | 7682.1  |
| 40°   | 6841.0  | 6602.4  | 6364.0  | 6701.9  | 7039.8  | 7686.5  | 8333.1  |
| 42.5° | 8564.4  | 8044.2  | 7524.0  | 7718.7  | 7913.3  | 8555.0  | 9196.6  |
| 45°   | 10604.9 | 9771.4  | 8938.1  | 9024.1  | 9109.9  | 9686.5  | 10262.8 |
| 47.5° | 12843.9 | 11642.1 | 10439.8 | 10457.3 | 10474.7 | 11035.6 | 11596.2 |
| 50°   | 15063.4 | 13514.1 | 11964.8 | 11961.9 | 11958.9 | 12651.4 | 13344.1 |
| 52.5° | 17204.6 | 15354.0 | 13503.4 | 13588.2 | 13673.0 | 14511.5 | 15350.3 |
| 55°   | 19287.1 | 17227.6 | 15167.8 | 15498.4 | 15829.0 | 16657.6 | 17486.2 |
| 57.5° | 21359.9 | 19280.1 | 17200.4 | 17863.3 | 18526.4 | 18977.8 | 19429.0 |
| 60°   | 24294.4 | 22326.3 | 20358.1 | 21181.6 | 22005.0 | 21304.0 | 20603.1 |
| 62.5° | 27257.3 | 25454.1 | 23651.3 | 23744.2 | 23837.0 | 21922.0 | 20006.9 |
| 65°   | 27702.1 | 25410.7 | 23119.4 | 22763.9 | 22408.3 | 20610.9 | 18813.6 |
| 67.5° | 25741.4 | 23354.2 | 20967.0 | 20800.3 | 20633.6 | 18924.2 | 17214.7 |
| 70°   | 23431.4 | 21296.6 | 19161.8 | 19087.0 | 19012.5 | 17153.1 | 15293.7 |
| 72.5° | 20719.8 | 19049.4 | 17379.2 | 17325.8 | 17272.1 | 15138.2 | 13004.6 |
| 75°   | 17521.0 | 16221.5 | 14922.1 | 14723.8 | 14525.5 | 12317.1 | 10108.8 |
| 77.5° | 13888.9 | 12901.0 | 11913.1 | 11629.3 | 11345.6 | 9283.9  | 7222.6  |
| 80°   | 10392.9 | 9647.1  | 8901.0  | 8548.3  | 8195.6  | 6461.5  | 4727.1  |
| 82.5° | 6934.4  | 6420.9  | 5907.4  | 5513.3  | 5119.4  | 3933.5  | 2747.8  |
| 85°   | 3981.5  | 3559.7  | 3137.7  | 2802.7  | 2467.6  | 1838.2  | 1209.0  |
| 87.5° | 1593.2  | 1382.2  | 1171.2  | 984.2   | 797.2   | 585.8   | 374.2   |
| 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |

(END OF REPORT)