

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220536

Luminaire Tested: **1003-[A1, S1, SU1]-[RW, RI]-LED3090-F-BK-L1-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220536
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29474)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 1003-[A1, S1, SU1]-[RW, RI]-LED3090-F-BK-L1-UNV
Description: LUMIERE LANTERRA 1003 LED ACCENT/SIGN LUMINAIRE, RECESSED LENS, FLOOD OPTIC, BLACK HOUSING.
Light Source: (1) 3000K CCT, 90 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 704.9 lumens
Efficiency: N/A
Efficacy: 71.9 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.56
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct


Input Watts (W): 9.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220536

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3090-F-BK-L1-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220536

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3090-F-BK-L1-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	112	110	109	107	107	105	104	103	102	101	99	99	98	96
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	93
3	107	102	98	95	105	101	97	95	98	96	93	96	94	92	94	92	90	89
4	103	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86
5	100	94	90	86	99	93	89	86	91	88	85	90	87	85	89	86	84	83
6	97	90	86	83	96	90	86	83	88	85	82	87	84	82	86	83	81	80
7	94	87	83	80	93	87	82	79	85	82	79	84	81	79	83	80	78	77
8	91	84	80	77	90	84	79	77	83	79	76	82	78	76	81	78	76	75
9	88	81	77	74	87	81	77	74	80	76	74	79	76	73	79	76	73	72
10	86	79	74	72	85	78	74	71	78	74	71	77	74	71	76	73	71	70

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	450775
5°	441051
10°	388726
15°	300342
20°	186520
25°	69101
30°	14458
35°	5434
40°	1975
45°	1333
50°	1194
55°	994
60°	746
65°	467
70°	256
75°	0
80°	0
85°	0



TEST NUMBER: P220536

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3090-F-BK-L1-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.0	26.0
10°-20°	355.0	50.4
20°-30°	144.6	20.5
30°-40°	15.3	2.2
40°-50°	3.6	0.5
50°-60°	2.3	0.3
60°-70°	1.0	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	682.6	96.8
0°-40°	697.9	99.0
0°-60°	703.8	99.8
0°-90°	704.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	704.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2056	
5°	2004	183
15°	1323	355
25°	286	145
35°	20	15
45°	4	4
55°	3	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P220536

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3090-F-BK-L1-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	2055.7
1°	2050.5
2°	2044.4
3°	2038.8
4°	2027.5
5°	2003.7
6°	1971.3
7°	1928.9
8°	1874.8
9°	1813.3
10°	1745.8
11°	1671.8
12°	1593.0
13°	1510.8
14°	1420.8
15°	1323.0
16°	1223.4
17°	1113.1
18°	1010.1
19°	902.8
20°	799.3
21°	698.5
22°	591.6
23°	482.5
24°	379.1
25°	285.6
26°	204.7
27°	139.4
28°	92.2
29°	68.4
30°	57.1
32.5°	37.7
35°	20.3
37.5°	11.3
40°	6.9
42.5°	5.2
45°	4.3
47.5°	3.9
50°	3.5
52.5°	3.0
55°	2.6
57.5°	2.2
60°	1.7
62.5°	1.3
65°	0.9



TEST NUMBER: P220536

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3090-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.9
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)