

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220553

Luminaire Tested: **1003-[A1, S1, SU1]-[RW, RI]-LED3090-W-BK-L1-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220553
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29475)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 1003-[A1, S1, SU1]-[RW, RI]-LED3090-W-BK-L1-UNV
Description: LUMIERE LANTERRA 1003 LED ACCENT/SIGN LUMINAIRE, RECESSED LENS, WIDE FLOOD OPTIC, BLACK HOUSING.
Light Source: (1) 3000K CCT, 90 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 592.1 lumens
Efficiency: N/A
Efficacy: 60.4 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.67
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct


Input Watts (W): 9.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220553

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3090-W-BK-L1-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220553

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3090-W-BK-L1-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	109	107	112	110	108	106	105	104	102		102	101	99		98	97	97	95
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94	93	91	90
3	105	99	95	91	103	98	94	90	95	92	89		93	90	88		91	88	86	85
4	100	94	89	85	99	93	88	85	90	87	84		89	85	83		87	84	82	80
5	96	89	84	80	95	88	83	80	86	82	79		85	81	78		83	80	78	76
6	92	84	79	75	91	84	79	75	82	78	75		81	77	74		80	76	74	72
7	88	80	75	71	87	80	75	71	78	74	71		77	73	70		76	73	70	69
8	85	77	71	68	84	76	71	68	75	71	67		74	70	67		73	69	67	66
9	82	73	68	64	81	73	68	64	72	67	64		71	67	64		70	66	64	63
10	78	70	65	62	78	70	65	61	69	64	61		68	64	61		67	64	61	60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	231736
5°	232731
10°	217676
15°	185972
20°	158050
25°	93925
30°	42741
35°	27117
40°	15372
45°	5644
50°	1774
55°	1338
60°	1140
65°	675
70°	256
75°	339
80°	0
85°	0



TEST NUMBER: P220553

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3090-W-BK-L1-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.5	16.6
10°-20°	229.0	38.7
20°-30°	177.8	30.0
30°-40°	64.8	10.9
40°-50°	17.1	2.9
50°-60°	3.2	0.5
60°-70°	1.4	0.2
70°-80°	0.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	505.2	85.3
0°-40°	570.0	96.3
0°-60°	590.3	99.7
0°-90°	592.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	592.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1057	
5°	1057	98
15°	819	229
25°	388	178
35°	101	65
45°	18	17
55°	4	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P220553

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3090-W-BK-L1-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	1056.8
1°	1053.8
2°	1053.8
3°	1056.8
4°	1058.6
5°	1057.3
6°	1052.1
7°	1041.2
8°	1024.4
9°	1002.3
10°	977.6
11°	949.1
12°	917.5
13°	884.2
14°	850.0
15°	819.2
16°	791.5
17°	762.1
18°	734.0
19°	705.4
20°	677.3
21°	646.1
22°	596.8
23°	531.9
24°	461.3
25°	388.2
26°	319.4
27°	257.9
28°	211.6
29°	185.2
30°	168.8
32.5°	132.9
35°	101.3
37.5°	76.2
40°	53.7
42.5°	35.5
45°	18.2
47.5°	8.2
50°	5.2
52.5°	3.9
55°	3.5
57.5°	3.0
60°	2.6
62.5°	1.7
65°	1.3



TEST NUMBER: P220553

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3090-W-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1.3
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)