

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220538

Luminaire Tested: **1003-[A1, S1, SU1]-[RW, RI]-LED4080-F-BK-L1-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220538
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29474)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 1003-[A1, S1, SU1]-[RW, RI]-LED4080-F-BK-L1-UNV
Description: LUMIERE LANTERRA 1003 LED ACCENT/SIGN LUMINAIRE, RECESSED LENS, FLOOD OPTIC, BLACK HOUSING.
Light Source: (1) 4000K CCT, 80 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 883.3 lumens
Efficiency: N/A
Efficacy: 90.1 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.56
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct


Input Watts (W): 9.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220538

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4080-F-BK-L1-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220538

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4080-F-BK-L1-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	112	110	109	107	107	105	104	103	102	101	99	99	98	96
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	93
3	107	102	98	95	105	101	97	95	98	96	93	96	94	92	94	92	90	89
4	103	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86
5	100	94	90	86	99	93	89	86	91	88	85	90	87	85	89	86	84	83
6	97	90	86	83	96	90	86	83	88	85	82	87	84	82	86	83	81	80
7	94	87	83	80	93	87	82	79	85	82	79	84	81	79	83	80	78	77
8	91	84	80	77	90	84	79	77	83	79	76	82	78	76	81	78	76	75
9	88	81	77	74	87	81	77	74	80	76	74	79	76	73	79	76	73	72
10	86	79	74	72	85	78	74	71	78	74	71	77	74	71	76	73	71	70

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	564823
5°	552651
10°	487076
15°	376325
20°	233727
25°	86594
30°	18129
35°	6826
40°	2490
45°	1675
50°	1467
55°	1262
60°	965
65°	571
70°	321
75°	0
80°	0
85°	0



TEST NUMBER: P220538

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4080-F-BK-L1-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	229.3	26.0
10°-20°	444.8	50.4
20°-30°	181.2	20.5
30°-40°	19.1	2.2
40°-50°	4.5	0.5
50°-60°	2.9	0.3
60°-70°	1.3	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	855.3	96.8
0°-40°	874.5	99.0
0°-60°	881.8	99.8
0°-90°	883.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	883.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2576	
5°	2511	229
15°	1658	445
25°	358	181
35°	26	19
45°	5	4
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P220538

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4080-F-BK-L1-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	2575.8
1°	2569.3
2°	2561.7
3°	2554.7
4°	2540.6
5°	2510.7
6°	2470.1
7°	2416.9
8°	2349.1
9°	2272.1
10°	2187.5
11°	2094.8
12°	1996.1
13°	1893.1
14°	1780.3
15°	1657.7
16°	1533.0
17°	1394.7
18°	1265.7
19°	1131.2
20°	1001.6
21°	875.2
22°	741.3
23°	604.6
24°	475.0
25°	357.9
26°	256.5
27°	174.6
28°	115.5
29°	85.7
30°	71.6
32.5°	47.2
35°	25.5
37.5°	14.1
40°	8.7
42.5°	6.5
45°	5.4
47.5°	4.9
50°	4.3
52.5°	3.8
55°	3.3
57.5°	2.7
60°	2.2
62.5°	1.6
65°	1.1



TEST NUMBER: P220538

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4080-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1.1
70°	0.5
72.5°	0.5
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)