

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P220658

Luminaire Tested: **1003-[A1, S1, SU1]-FL-LED2790-M-BK-L1-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P220658  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29477)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 1003-[A1, S1, SU1]-FL-LED2790-M-BK-L1-UNV  
Description: LUMIERE LANTERRA 1003 LED ACCENT/SIGN LUMINAIRE, FLUSH LENS, MEDIUM FLOOD OPTIC, BLACK HOUSING.  
Light Source: (1) 2700K CCT, 90 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 664.0 lumens  
Efficiency: N/A  
Efficacy: 67.8 lumens/watt  
Spacing Criteria (0/90/45): 0.41 / 0.41 / 0.41  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct


Input Watts (W): 9.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P220658

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED2790-M-BK-L1-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P220658

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED2790-M-BK-L1-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	112	111	109	107	107	105	104	103	102	101	99	99	98	96
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	93
3	107	102	99	96	105	101	98	95	98	96	93	96	94	92	94	92	91	89
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86
5	100	94	90	87	99	93	89	86	92	88	86	90	87	85	89	86	84	83
6	97	91	86	83	96	90	86	83	89	85	82	87	84	82	86	84	81	80
7	94	88	83	80	93	87	83	80	86	82	80	85	82	79	84	81	79	78
8	92	85	80	77	91	84	80	77	83	80	77	82	79	77	82	79	76	75
9	89	82	78	75	88	82	78	75	81	77	75	80	77	74	79	76	74	73
10	86	79	75	73	86	79	75	72	78	75	72	78	74	72	77	74	72	71

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	616047
5°	559761
10°	395628
15°	213804
20°	113713
25°	83642
30°	33777
35°	6451
40°	3406
45°	1520
50°	1262
55°	1109
60°	877
65°	830
70°	769
75°	678
80°	505
85°	1006



TEST NUMBER: P220658

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED2790-M-BK-L1-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	217.9	32.8
10°-20°	265.8	40.0
20°-30°	146.3	22.0
30°-40°	24.3	3.7
40°-50°	4.4	0.7
50°-60°	2.6	0.4
60°-70°	1.6	0.2
70°-80°	0.8	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	630.0	94.9
0°-40°	654.3	98.5
0°-60°	661.3	99.6
0°-90°	664.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	664.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2809	
5°	2543	218
15°	942	266
25°	346	146
35°	24	24
45°	5	4
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P220658

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED2790-M-BK-L1-UNV

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2809.4
1°	2792.2
2°	2763.1
3°	2717.3
4°	2639.6
5°	2543.0
6°	2426.4
7°	2287.8
8°	2129.8
9°	1956.8
10°	1776.8
11°	1595.1
12°	1416.8
13°	1246.2
14°	1088.6
15°	941.8
16°	815.0
17°	700.8
18°	611.6
19°	540.4
20°	487.3
21°	446.8
22°	417.3
23°	396.4
24°	375.6
25°	345.7
26°	308.5
27°	266.7
28°	221.3
29°	176.7
30°	133.4
32.5°	48.3
35°	24.1
37.5°	17.2
40°	11.9
42.5°	6.1
45°	4.9
47.5°	4.5
50°	3.7
52.5°	3.3
55°	2.9
57.5°	2.5
60°	2.0
62.5°	2.0
65°	1.6



TEST NUMBER: P220658

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED2790-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	1.2
70°	1.2
72.5°	0.8
75°	0.8
77.5°	0.8
80°	0.4
82.5°	0.4
85°	0.4
87.5°	0.0
90°	0.0

(END OF REPORT)