

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P220610

Luminaire Tested: **1003-[A1, S1, SU1]-FL-LED2797-F-WT-L1-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P220610  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29478)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 1003-[A1, S1, SU1]-FL-LED2797-F-WT-L1-UNV  
Description: LUMIERE LANTERRA 1003 LED ACCENT/SIGN LUMINAIRE, FLUSH LENS, FLOOD OPTIC, WHITE HOUSING.  
Light Source: (1) 2700K CCT, 97 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 677.7 lumens  
Efficiency: N/A  
Efficacy: 69.2 lumens/watt  
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.56  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct


Input Watts (W): 9.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P220610

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED2797-F-WT-L1-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P220610

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED2797-F-WT-L1-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	112	110	108	112	110	108	107	106	105	104	103	101	100	99	98	98	96
2	110	107	103	101	108	105	102	100	102	99	97	99	97	95	96	95	93	92
3	106	101	98	94	105	100	97	94	98	95	92	95	93	91	93	91	89	88
4	103	97	93	89	101	96	92	89	94	90	88	92	89	87	90	88	86	85
5	99	93	88	85	98	92	88	85	90	87	84	89	86	83	87	85	82	81
6	96	89	84	81	95	88	84	81	87	83	80	86	82	80	84	82	79	78
7	93	85	81	78	91	85	81	77	84	80	77	83	79	77	82	79	76	75
8	90	82	78	75	89	82	77	74	81	77	74	80	76	74	79	76	74	72
9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70
10	84	77	72	69	83	76	72	69	75	72	69	75	71	69	74	71	69	68

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	399200
5°	387364
10°	342456
15°	262975
20°	163698
25°	92304
30°	35043
35°	7522
40°	2920
45°	930
50°	785
55°	573
60°	482
65°	571
70°	513
75°	678
80°	505
85°	0



TEST NUMBER: P220610

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED2797-F-WT-L1-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	161.1	23.8
10°-20°	310.9	45.9
20°-30°	173.3	25.6
30°-40°	26.2	3.9
40°-50°	2.9	0.4
50°-60°	1.5	0.2
60°-70°	1.0	0.1
70°-80°	0.7	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	645.3	95.2
0°-40°	671.5	99.1
0°-60°	675.9	99.7
0°-90°	677.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	677.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1820	
5°	1760	161
15°	1158	311
25°	382	173
35°	28	26
45°	3	3
55°	2	1
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P220610

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED2797-F-WT-L1-UNV

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1820.5
1°	1814.0
2°	1803.4
3°	1792.4
4°	1778.4
5°	1759.8
6°	1734.8
7°	1698.7
8°	1652.5
9°	1597.9
10°	1538.0
11°	1470.9
12°	1398.1
13°	1322.6
14°	1241.8
15°	1158.4
16°	1068.2
17°	974.9
18°	880.1
19°	789.5
20°	701.5
21°	620.0
22°	547.9
23°	487.3
24°	434.5
25°	381.5
26°	329.5
27°	279.1
28°	230.2
29°	183.1
30°	138.4
32.5°	55.4
35°	28.1
37.5°	17.4
40°	10.2
42.5°	3.8
45°	3.0
47.5°	2.3
50°	2.3
52.5°	1.9
55°	1.5
57.5°	1.5
60°	1.1
62.5°	1.1
65°	1.1



TEST NUMBER: P220610

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED2797-F-WT-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.8
70°	0.8
72.5°	0.8
75°	0.8
77.5°	0.4
80°	0.4
82.5°	0.4
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)