

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220593

Luminaire Tested: **1003-[A1, S1, SU1]-FL-LED3097-M-WT-L1-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220593
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29477)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 1003-[A1, S1, SU1]-FL-LED3097-M-WT-L1-UNV
Description: LUMIERE LANTERRA 1003 LED ACCENT/SIGN LUMINAIRE, FLUSH LENS, MEDIUM FLOOD OPTIC, WHITE HOUSING.
Light Source: (1) 3000K CCT, 97 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 621.3 lumens
Efficiency: N/A
Efficacy: 63.4 lumens/watt
Spacing Criteria (0/90/45): 0.41 / 0.41 / 0.41
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct


Input Watts (W): 9.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220593

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3097-M-WT-L1-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220593

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3097-M-WT-L1-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	112	111	109	107	107	105	104	103	102	101	99	99	98	96
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	93
3	107	102	99	96	105	101	98	95	98	96	93	96	94	92	94	92	91	89
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86
5	100	94	90	87	99	93	89	86	92	88	86	90	87	85	89	86	84	83
6	97	91	86	83	96	90	86	83	89	85	82	87	84	82	86	84	81	80
7	94	88	83	80	93	87	83	80	86	82	80	85	82	79	84	81	79	78
8	92	85	80	77	91	84	80	77	83	80	77	82	79	77	82	79	76	75
9	89	82	78	75	88	82	78	75	81	77	75	80	77	74	79	76	74	73
10	86	79	75	73	86	79	75	72	78	75	72	78	74	72	77	74	72	71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	576357
5°	523705
10°	370133
15°	200024
20°	106386
25°	78246
30°	31600
35°	6050
40°	3177
45°	1427
50°	1160
55°	1032
60°	833
65°	778
70°	705
75°	678
80°	505
85°	1006



TEST NUMBER: P220593

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3097-M-WT-L1-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	203.9	32.8
10°-20°	248.7	40.0
20°-30°	136.9	22.0
30°-40°	22.7	3.7
40°-50°	4.1	0.7
50°-60°	2.4	0.4
60°-70°	1.5	0.2
70°-80°	0.8	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	589.4	94.9
0°-40°	612.2	98.5
0°-60°	618.7	99.6
0°-90°	621.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	621.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2628	
5°	2379	204
15°	881	249
25°	323	137
35°	23	23
45°	5	4
55°	3	2
65°	2	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P220593

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3097-M-WT-L1-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	2628.4
1°	2612.3
2°	2585.1
3°	2542.3
4°	2469.6
5°	2379.2
6°	2270.1
7°	2140.4
8°	1992.6
9°	1830.7
10°	1662.3
11°	1492.4
12°	1325.5
13°	1165.9
14°	1018.5
15°	881.1
16°	762.5
17°	655.7
18°	572.2
19°	505.6
20°	455.9
21°	418.0
22°	390.4
23°	370.9
24°	351.4
25°	323.4
26°	288.6
27°	249.6
28°	207.1
29°	165.4
30°	124.8
32.5°	45.2
35°	22.6
37.5°	16.1
40°	11.1
42.5°	5.7
45°	4.6
47.5°	4.2
50°	3.4
52.5°	3.1
55°	2.7
57.5°	2.3
60°	1.9
62.5°	1.9
65°	1.5



TEST NUMBER: P220593

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3097-M-WT-L1-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1.1
70°	1.1
72.5°	0.8
75°	0.8
77.5°	0.8
80°	0.4
82.5°	0.4
85°	0.4
87.5°	0.0
90°	0.0

(END OF REPORT)