

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P220576

Luminaire Tested: **1003-[A1, S1, SU1]-FL-LED3597-S-WT-L1-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P220576  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29476)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 1003-[A1, S1, SU1]-FL-LED3597-S-WT-L1-UNV  
Description: LUMIERE LANTERRA 1003 LED ACCENT/SIGN LUMINAIRE, FLUSH LENS, SPOT OPTIC, WHITE HOUSING.  
Light Source: (1) 3500K CCT, 97 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 738.0 lumens  
Efficiency: N/A  
Efficacy: 75.3 lumens/watt  
Spacing Criteria (0/90/45): 0.27 / 0.27 / 0.27  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct


Input Watts (W): 9.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P220576

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3597-S-WT-L1-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P220576

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3597-S-WT-L1-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	110	113	111	109	108	107	106	105	103	102	101	100	99	99	97
2	111	108	105	103	109	106	104	101	103	101	99	100	99	97	98	96	95	94
3	108	104	100	97	106	102	99	97	100	97	95	98	95	94	95	94	92	91
4	105	100	96	93	103	99	95	92	97	94	91	95	92	90	93	91	89	88
5	102	96	92	89	101	95	92	89	94	91	88	92	90	88	91	89	87	86
6	99	93	89	86	98	93	89	86	91	88	86	90	87	85	89	86	85	83
7	97	90	86	84	96	90	86	83	89	85	83	88	85	83	87	84	82	81
8	94	88	84	81	93	87	84	81	87	83	81	86	83	81	85	82	80	79
9	92	86	82	79	91	85	82	79	84	81	79	84	81	79	83	80	78	77
10	90	83	80	77	89	83	79	77	82	79	77	82	79	77	81	78	77	76

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1227051
5°	952694
10°	406984
15°	172078
20°	114087
25°	85505
30°	32765
35°	5006
40°	2748
45°	1209
50°	887
55°	841
60°	965
65°	882
70°	833
75°	763
80°	505
85°	1006



TEST NUMBER: P220576

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3597-S-WT-L1-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	327.1	44.3
10°-20°	231.8	31.4
20°-30°	149.4	20.2
30°-40°	21.5	2.9
40°-50°	3.4	0.5
50°-60°	2.1	0.3
60°-70°	1.6	0.2
70°-80°	0.8	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	708.3	96.0
0°-40°	729.8	98.9
0°-60°	735.3	99.6
0°-90°	738.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	738.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5596	
5°	4328	327
15°	758	232
25°	353	149
35°	19	22
45°	4	3
55°	2	2
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P220576

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3597-S-WT-L1-UNV

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	5595.8
1°	5525.9
2°	5371.3
3°	5117.4
4°	4764.0
5°	4328.1
6°	3827.1
7°	3303.9
8°	2786.4
9°	2275.0
10°	1827.8
11°	1462.7
12°	1199.6
13°	1007.2
14°	864.4
15°	758.0
16°	670.3
17°	606.5
18°	560.9
19°	521.0
20°	488.9
21°	461.1
22°	436.8
23°	414.2
24°	388.1
25°	353.4
26°	312.6
27°	268.7
28°	221.0
29°	173.7
30°	129.4
32.5°	43.0
35°	18.7
37.5°	13.5
40°	9.6
42.5°	4.8
45°	3.9
47.5°	3.0
50°	2.6
52.5°	2.6
55°	2.2
57.5°	2.2
60°	2.2
62.5°	1.7
65°	1.7



TEST NUMBER: P220576

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3597-S-WT-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	1.3
70°	1.3
72.5°	0.9
75°	0.9
77.5°	0.4
80°	0.4
82.5°	0.4
85°	0.4
87.5°	0.0
90°	0.0

(END OF REPORT)