

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220447

Luminaire Tested: **1003-[A1, S1, SU1]-[RW, RI]-LED3097-S-WT-L2-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220447
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29468)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 1003-[A1, S1, SU1]-[RW, RI]-LED3097-S-WT-L2-UNV
Description: LUMIERE LANTERRA 1003 LED ACCENT/SIGN LUMINAIRE, RECESSED LENS, SPOT OPTIC, WHITE HOUSING.
Light Source: (1) 3000K CCT, 97 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1269.1 lumens
Efficiency: N/A
Efficacy: 63.1 lumens/watt
Spacing Criteria (0/90/45): 0.27 / 0.27 / 0.27
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct


Input Watts (W): 20.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220447

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3097-S-WT-L2-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220447

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3097-S-WT-L2-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	109	107	112	110	108	106	106	104	103		102	101	99		98	98	97	95
2	110	105	102	99	108	104	101	98	101	98	96		98	96	94		95	93	92	90
3	106	100	96	93	104	99	95	92	96	93	91		94	91	89		92	90	88	87
4	102	96	91	88	100	95	91	88	93	89	87		91	88	86		89	87	85	83
5	99	92	88	84	97	91	87	84	90	86	83		88	85	82		87	84	82	80
6	96	89	84	81	94	88	84	81	87	83	80		85	82	80		84	81	79	78
7	93	86	81	78	92	85	81	78	84	80	78		83	80	77		82	79	77	76
8	90	83	79	76	89	83	79	76	82	78	75		81	78	75		80	77	75	74
9	88	81	77	74	87	81	76	74	80	76	73		79	76	73		78	75	73	72
10	86	79	75	72	85	79	75	72	78	74	72		77	74	71		77	73	71	70

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2037337
5°	1565173
10°	663559
15°	284746
20°	189413
25°	90175
30°	22155
35°	16436
40°	15772
45°	15754
50°	16136
55°	18083
60°	18244
65°	16863
70°	14041
75°	12539
80°	14269
85°	14089



TEST NUMBER: P220447

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3097-S-WT-L2-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	536.0	42.2
10°-20°	383.6	30.2
20°-30°	173.4	13.7
30°-40°	41.0	3.2
40°-50°	39.3	3.1
50°-60°	41.4	3.3
60°-70°	31.9	2.5
70°-80°	16.5	1.3
80°-90°	5.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1093.0	86.1
0°-40°	1134.0	89.4
0°-60°	1214.8	95.7
0°-90°	1269.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1269.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9291	
5°	7111	536
15°	1254	384
25°	373	173
35°	61	41
45°	51	39
55°	47	41
65°	32	32
75°	15	16
85°	6	6
90°	0	



TEST NUMBER: P220447

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3097-S-WT-L2-UNV

CANDELA DISTRIBUTION (FULL):

	0°
0°	9291.0
1°	9169.6
2°	8887.2
3°	8439.7
4°	7837.6
5°	7110.6
6°	6277.7
7°	5405.3
8°	4523.7
9°	3700.0
10°	2980.1
11°	2406.9
12°	1987.6
13°	1679.9
14°	1439.2
15°	1254.3
16°	1105.3
17°	1005.1
18°	930.3
19°	865.4
20°	811.7
22.5°	645.1
25°	372.7
26°	271.7
27°	184.9
28°	122.8
29°	96.7
30°	87.5
32.5°	73.4
35°	61.4
37.5°	57.2
40°	55.1
42.5°	52.9
45°	50.8
47.5°	48.7
50°	47.3
52.5°	47.3
55°	47.3
57.5°	45.9
60°	41.6
62.5°	38.1
65°	32.5
67.5°	26.8
70°	21.9
72.5°	17.6



TEST NUMBER: P220447

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	0°
75°	14.8
77.5°	13.4
80°	11.3
82.5°	8.5
85°	5.6
87.5°	2.1
90°	0.0

(END OF REPORT)