

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P29473

Luminaire Tested: **1003-[A1, S1, SU1]-[RW, RI]-LED4080-M-BK-L2-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P29473
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 1003-[A1, S1, SU1]-[RW, RI]-LED4080-M-BK-L2-UNV
Description: LUMIERE LANTERRA 1003 LED ACCENT/SIGN LUMINAIRE, RECESSED LENS,
MEDIUM FLOOD OPTIC, BLACK HOUSING.
Light Source: (1) 4000K CCT, 80 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1442.5 lumens
Efficiency: N/A
Efficacy: 71.8 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.4
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct


Input Watts (W): 20.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P29473

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4080-M-BK-L2-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P29473

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4080-M-BK-L2-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104		103	102	101		100	99	98	97
2	111	108	105	102	109	106	103	101	103	101	99		100	98	97		98	96	95	94
3	108	103	100	97	106	102	99	96	100	97	95		97	95	93		95	93	92	91
4	105	99	95	93	103	98	95	92	96	93	91		95	92	90		93	91	89	88
5	102	96	92	89	100	95	91	88	93	90	88		92	89	87		91	88	86	85
6	99	93	89	86	98	92	88	85	91	87	85		89	87	84		88	86	84	83
7	96	90	86	83	95	89	85	83	88	85	82		87	84	82		86	83	81	80
8	94	87	83	80	93	87	83	80	86	82	80		85	82	80		84	81	79	78
9	91	85	81	78	90	84	80	78	83	80	78		83	80	77		82	79	77	76
10	89	82	78	76	88	82	78	76	81	78	76		81	78	75		80	77	75	74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1516545
5°	1359010
10°	954781
15°	512375
20°	269523
25°	120491
30°	23295
35°	8566
40°	4866
45°	4031
50°	3411
55°	2676
60°	2193
65°	1557
70°	641
75°	0
80°	0
85°	0



TEST NUMBER: P29473

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4080-M-BK-L2-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	528.2	36.6
10°-20°	636.6	44.1
20°-30°	232.3	16.1
30°-40°	25.7	1.8
40°-50°	10.1	0.7
50°-60°	6.4	0.4
60°-70°	3.0	0.2
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1397.0	96.8
0°-40°	1422.7	98.6
0°-60°	1439.1	99.8
0°-90°	1442.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1442.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6916	
5°	6174	528
15°	2257	637
25°	498	232
35°	32	26
45°	13	10
55°	7	6
65°	3	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P29473

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4080-M-BK-L2-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	6916
1°	6860
2°	6762
3°	6618
4°	6419
5°	6174
6°	5881
7°	5537
8°	5147
9°	4724
10°	4288
11°	3849
12°	3414
13°	3003
14°	2611
15°	2257
16°	1932
17°	1667
18°	1452
19°	1282
20°	1155
21°	1051
22°	932
23°	791
24°	644
25°	498
26°	359
27°	235
28°	148
29°	108
30°	92
32.5°	62
35°	32
37.5°	21
40°	17
42.5°	15
45°	13
47.5°	11
50°	10
52.5°	8
55°	7
57.5°	6
60°	5
62.5°	4
65°	3



TEST NUMBER: P29473

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4080-M-BK-L2-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	2
70°	1
72.5°	1
75°	0
77.5°	0
80°	0
82.5°	0
85°	0
87.5°	0
90°	0

(END OF REPORT)