

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220619

Luminaire Tested: **1003-[A1, S1, SU1]-FL-LED2797-F-WT-L2-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220619
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29478)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 1003-[A1, S1, SU1]-FL-LED2797-F-WT-L2-UNV
Description: LUMIERE LANTERRA 1003 LED ACCENT/SIGN LUMINAIRE, FLUSH LENS, FLOOD OPTIC, WHITE HOUSING.
Light Source: (1) 2700K CCT, 97 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1249.6 lumens
Efficiency: N/A
Efficacy: 62.2 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.56
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct


Input Watts (W): 20.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220619

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED2797-F-WT-L2-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220619

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED2797-F-WT-L2-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	112	110	108	112	110	108	107	106	105	104	103	101	100	99	98	98	96
2	110	107	103	101	108	105	102	100	102	99	97	99	97	95	96	95	93	92
3	107	101	98	94	105	100	97	94	98	95	92	95	93	91	93	91	89	88
4	103	97	93	89	101	96	92	89	94	90	88	92	89	87	90	88	86	85
5	99	93	88	85	98	92	88	85	90	87	84	89	86	83	87	85	82	81
6	96	89	84	81	95	88	84	81	87	83	80	86	82	80	84	82	79	78
7	93	85	81	78	91	85	81	77	84	80	77	83	79	77	82	79	76	75
8	90	82	78	75	89	82	77	74	81	77	74	80	76	74	79	76	74	72
9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70
10	84	77	72	69	83	76	72	69	75	72	69	75	71	69	74	71	69	68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	736147
5°	714328
10°	631518
15°	484952
20°	301866
25°	170187
30°	64618
35°	13840
40°	5410
45°	1737
50°	1433
55°	1070
60°	921
65°	1090
70°	898
75°	1186
80°	884
85°	0



TEST NUMBER: P220619

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED2797-F-WT-L2-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	297.1	23.8
10°-20°	573.2	45.9
20°-30°	319.6	25.6
30°-40°	48.3	3.9
40°-50°	5.4	0.4
50°-60°	2.7	0.2
60°-70°	1.8	0.1
70°-80°	1.2	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1189.9	95.2
0°-40°	1238.2	99.1
0°-60°	1246.3	99.7
0°-90°	1249.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1249.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3357	
5°	3245	297
15°	2136	573
25°	703	320
35°	52	48
45°	6	5
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P220619

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED2797-F-WT-L2-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	3357.1
1°	3345.2
2°	3325.6
3°	3305.3
4°	3279.5
5°	3245.2
6°	3199.1
7°	3132.6
8°	3047.3
9°	2946.6
10°	2836.2
11°	2712.4
12°	2578.1
13°	2439.0
14°	2290.0
15°	2136.2
16°	1969.8
17°	1797.8
18°	1623.0
19°	1455.8
20°	1293.6
21°	1143.3
22°	1010.4
23°	898.5
24°	801.3
25°	703.4
26°	607.6
27°	514.6
28°	424.4
29°	337.7
30°	255.2
32.5°	102.1
35°	51.7
37.5°	32.2
40°	18.9
42.5°	7.0
45°	5.6
47.5°	4.2
50°	4.2
52.5°	3.5
55°	2.8
57.5°	2.8
60°	2.1
62.5°	2.1
65°	2.1



TEST NUMBER: P220619

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED2797-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1.4
70°	1.4
72.5°	1.4
75°	1.4
77.5°	0.7
80°	0.7
82.5°	0.7
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)