

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220579

Luminaire Tested: **1003-[A1, S1, SU1]-FL-LED3090-S-WT-L2-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220579
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29476)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 1003-[A1, S1, SU1]-FL-LED3090-S-WT-L2-UNV
Description: LUMIERE LANTERRA 1003 LED ACCENT/SIGN LUMINAIRE, FLUSH LENS, SPOT OPTIC, WHITE HOUSING.
Light Source: (1) 3000K CCT, 90 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1356.5 lumens
Efficiency: N/A
Efficacy: 67.5 lumens/watt
Spacing Criteria (0/90/45): 0.27 / 0.27 / 0.27
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct


Input Watts (W): 20.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220579

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-S-WT-L2-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220579

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-S-WT-L2-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	110	113	111	109	108	107	106	105	103	102	101	100	99	99	97
2	111	108	105	103	109	106	104	101	103	101	99	100	99	97	98	96	95	94
3	108	104	100	97	106	102	99	97	100	97	95	98	95	94	95	94	92	91
4	105	100	96	93	103	99	95	92	97	94	91	95	92	90	93	91	89	88
5	102	96	92	89	101	95	92	89	94	91	88	92	90	88	91	89	87	86
6	99	93	89	86	98	93	89	86	91	88	86	90	87	85	89	86	85	83
7	97	90	86	84	96	90	86	83	89	85	83	88	85	83	87	84	82	81
8	94	88	84	81	93	87	84	81	87	83	81	86	83	81	85	82	80	79
9	92	86	82	79	91	85	82	79	84	81	79	84	81	79	83	80	78	77
10	90	83	80	77	89	83	79	77	82	79	77	82	79	77	81	78	76	76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	225565
5°	1751239
10°	748105
15°	316324
20°	209692
25°	157170
30°	60212
35°	9182
40°	5038
45°	2233
50°	1637
55°	1529
60°	1754
65°	1660
70°	1539
75°	1356
80°	1010
85°	2013



TEST NUMBER: P220579

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-S-WT-L2-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	601.3	44.3
10°-20°	426.0	31.4
20°-30°	274.6	20.2
30°-40°	39.6	2.9
40°-50°	6.2	0.5
50°-60°	3.8	0.3
60°-70°	3.0	0.2
70°-80°	1.5	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1301.9	96.0
0°-40°	1341.5	98.9
0°-60°	1351.6	99.6
0°-90°	1356.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1356.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10286	
5°	7956	601
15°	1393	426
25°	650	275
35°	34	40
45°	7	6
55°	4	4
65°	3	3
75°	2	1
85°	1	1
90°	0	



TEST NUMBER: P220579

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-S-WT-L2-UNV

CANDELA DISTRIBUTION (FULL):

	0°
0°	10286.2
1°	10157.7
2°	9873.6
3°	9406.8
4°	8757.1
5°	7955.9
6°	7034.9
7°	6073.3
8°	5122.0
9°	4181.8
10°	3359.8
11°	2688.7
12°	2205.0
13°	1851.5
14°	1588.9
15°	1393.4
16°	1232.2
17°	1114.9
18°	1031.1
19°	957.7
20°	898.6
21°	847.5
22°	802.9
23°	761.4
24°	713.5
25°	649.6
26°	574.6
27°	494.0
28°	406.2
29°	319.2
30°	237.8
32.5°	79.0
35°	34.3
37.5°	24.7
40°	17.6
42.5°	8.8
45°	7.2
47.5°	5.6
50°	4.8
52.5°	4.8
55°	4.0
57.5°	4.0
60°	4.0
62.5°	3.2
65°	3.2



TEST NUMBER: P220579

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	2.4
70°	2.4
72.5°	1.6
75°	1.6
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.8
87.5°	0.0
90°	0.0

(END OF REPORT)