

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P220672

Luminaire Tested: **1003-[A1, S1, SU1]-FL-LED3097-M-BK-L2-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P220672  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29477)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 1003-[A1, S1, SU1]-FL-LED3097-M-BK-L2-UNV  
Description: LUMIERE LANTERRA 1003 LED ACCENT/SIGN LUMINAIRE, FLUSH LENS, MEDIUM FLOOD OPTIC, BLACK HOUSING.  
Light Source: (1) 3000K CCT, 97 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1145.6 lumens  
Efficiency: N/A  
Efficacy: 57.0 lumens/watt  
Spacing Criteria (0/90/45): 0.41 / 0.41 / 0.41  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.1  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P220672

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3097-M-BK-L2-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P220672

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3097-M-BK-L2-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	113	111	109	112	111	109	107	107	105	104		103	102	101		99	99	98	96
2	111	107	104	101	109	105	103	100	102	100	98		99	98	96		97	95	94	93
3	107	102	99	96	105	101	98	95	98	96	93		96	94	92		94	92	91	89
4	104	98	94	91	102	97	93	90	95	92	89		93	90	88		91	89	87	86
5	100	94	90	87	99	93	89	86	92	88	86		90	87	85		89	86	84	83
6	97	91	86	83	96	90	86	83	89	85	82		87	84	82		86	84	81	80
7	94	88	83	80	93	87	83	80	86	82	80		85	82	79		84	81	79	78
8	92	85	80	77	91	84	80	77	83	80	77		82	79	77		82	79	76	75
9	89	82	78	75	88	82	78	75	81	77	75		80	77	74		79	76	74	73
10	86	79	75	73	86	79	75	72	78	75	72		78	74	72		77	74	72	71

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1062853
5°	965769
10°	682575
15°	368856
20°	196180
25°	144299
30°	58262
35°	11136
40°	5868
45°	2636
50°	2183
55°	1873
60°	1535
65°	1453
70°	1346
75°	1186
80°	884
85°	1761



TEST NUMBER: P220672

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3097-M-BK-L2-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	375.9	32.8
10°-20°	458.6	40.0
20°-30°	252.4	22.0
30°-40°	41.9	3.7
40°-50°	7.7	0.7
50°-60°	4.4	0.4
60°-70°	2.8	0.2
70°-80°	1.5	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1087.0	94.9
0°-40°	1128.8	98.5
0°-60°	1140.9	99.6
0°-90°	1145.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1145.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4847	
5°	4388	376
15°	1625	459
25°	596	252
35°	42	42
45°	8	8
55°	5	4
65°	3	3
75°	1	1
85°	1	0
90°	0	



TEST NUMBER: P220672

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3097-M-BK-L2-UNV

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4847.0
1°	4817.3
2°	4767.2
3°	4688.2
4°	4554.1
5°	4387.5
6°	4186.3
7°	3947.0
8°	3674.6
9°	3376.0
10°	3065.5
11°	2752.1
12°	2444.3
13°	2150.0
14°	1878.2
15°	1624.8
16°	1406.0
17°	1209.1
18°	1055.2
19°	932.4
20°	840.7
21°	770.8
22°	720.0
23°	684.0
24°	648.0
25°	596.4
26°	532.2
27°	460.2
28°	381.9
29°	304.9
30°	230.1
32.5°	83.3
35°	41.6
37.5°	29.6
40°	20.5
42.5°	10.6
45°	8.5
47.5°	7.8
50°	6.4
52.5°	5.6
55°	4.9
57.5°	4.2
60°	3.5
62.5°	3.5
65°	2.8



TEST NUMBER: P220672

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3097-M-BK-L2-UNV

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	2.1
70°	2.1
72.5°	1.4
75°	1.4
77.5°	1.4
80°	0.7
82.5°	0.7
85°	0.7
87.5°	0.0
90°	0.0

(END OF REPORT)