

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P220652

Luminaire Tested: **1003-[A1, S1, SU1]-FL-LED3590-S-BK-L2-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P220652  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29476)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 1003-[A1, S1, SU1]-FL-LED3590-S-BK-L2-UNV  
Description: LUMIERE LANTERRA 1003 LED ACCENT/SIGN LUMINAIRE, FLUSH LENS, SPOT OPTIC, BLACK HOUSING.  
Light Source: (1) 3500K CCT, 90 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1373.9 lumens  
Efficiency: N/A  
Efficacy: 68.4 lumens/watt  
Spacing Criteria (0/90/45): 0.27 / 0.27 / 0.27  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.1  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P220652

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-S-BK-L2-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P220652

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-S-BK-L2-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	110	113	111	109	108	107	106	105	103	102	101	100	99	99	97
2	111	108	105	103	109	106	104	101	103	101	99	100	99	97	98	96	95	94
3	108	104	100	97	106	102	99	97	100	97	95	98	95	94	95	94	92	91
4	105	100	96	93	103	99	95	92	97	94	91	95	92	90	93	91	89	88
5	102	96	92	89	101	95	92	89	94	91	88	92	90	88	91	89	87	86
6	99	93	89	86	98	93	89	86	91	88	86	90	87	85	89	86	85	83
7	97	90	86	84	96	90	86	83	89	85	83	88	85	83	87	84	82	81
8	94	88	84	81	93	87	84	81	87	83	81	86	83	81	85	82	80	79
9	92	86	82	79	91	85	82	79	84	81	79	84	81	79	83	80	78	77
10	90	83	80	77	89	83	79	77	82	79	77	82	79	77	81	78	77	76

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2284576
5°	1773757
10°	757724
15°	320388
20°	212398
25°	159203
30°	60997
35°	9316
40°	5095
45°	2264
50°	1637
55°	1529
60°	1754
65°	1660
70°	1539
75°	1356
80°	1010
85°	2013



TEST NUMBER: P220652

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-S-BK-L2-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	609.0	44.3
10°-20°	431.5	31.4
20°-30°	278.1	20.2
30°-40°	40.1	2.9
40°-50°	6.3	0.5
50°-60°	3.8	0.3
60°-70°	3.0	0.2
70°-80°	1.5	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1318.6	96.0
0°-40°	1358.7	98.9
0°-60°	1368.9	99.6
0°-90°	1373.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1373.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	10418	
5°	8058	609
15°	1411	432
25°	658	278
35°	35	40
45°	7	6
55°	4	4
65°	3	3
75°	2	1
85°	1	1
90°	0	



TEST NUMBER: P220652

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-S-BK-L2-UNV

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	10418.5
1°	10288.4
2°	10000.6
3°	9527.7
4°	8869.8
5°	8058.2
6°	7125.4
7°	6151.4
8°	5187.8
9°	4235.6
10°	3403.0
11°	2723.2
12°	2233.4
13°	1875.3
14°	1609.4
15°	1411.3
16°	1248.1
17°	1129.2
18°	1044.4
19°	970.0
20°	910.2
21°	858.4
22°	813.2
23°	771.1
24°	722.6
25°	658.0
26°	582.0
27°	500.4
28°	411.4
29°	323.3
30°	240.9
32.5°	80.0
35°	34.8
37.5°	25.1
40°	17.8
42.5°	8.9
45°	7.3
47.5°	5.7
50°	4.8
52.5°	4.8
55°	4.0
57.5°	4.0
60°	4.0
62.5°	3.2
65°	3.2



TEST NUMBER: P220652

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-S-BK-L2-UNV

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	2.4
70°	2.4
72.5°	1.6
75°	1.6
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.8
87.5°	0.0
90°	0.0

(END OF REPORT)