

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P221160

Luminaire Tested: **1003-[A1, S1, SU1]-[RW, RI]-LED CR-W-BK-LC2-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P221160
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29557)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 1003-[A1, S1, SU1]-[RW, RI]-LED CR-W-BK-LC2-UNV
Description: LUMIERE LANTERRA 1003 LED ACCENT/SIGN LUMINAIRE, RECESSED LENS, WIDE FLOOD OPTIC, BLACK HOUSING.
Light Source: (1) COLOR CHAGING MODULE, SET TO 3500K CCT, 90 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 541.8 lumens
Efficiency: N/A
Efficacy: 22.3 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct


Input Watts (W): 24.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P221160

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LEDCR-W-BK-LC2-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P221160

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED CR-W-BK-LC2-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 | | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | | 50 | 30 | 10 | | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | | 106 | 106 | 106 | | 102 | 102 | 102 | 100 |
| 1 | 114 | 112 | 110 | 108 | 112 | 110 | 108 | 106 | 106 | 104 | 103 | | 102 | 101 | 100 | | 99 | 98 | 97 | 95 |
| 2 | 110 | 106 | 102 | 99 | 108 | 104 | 101 | 98 | 101 | 98 | 96 | | 98 | 96 | 94 | | 95 | 94 | 92 | 91 |
| 3 | 106 | 100 | 96 | 93 | 104 | 99 | 95 | 92 | 96 | 93 | 90 | | 94 | 91 | 89 | | 92 | 90 | 88 | 86 |
| 4 | 101 | 95 | 90 | 87 | 100 | 94 | 90 | 86 | 92 | 88 | 85 | | 90 | 87 | 84 | | 88 | 86 | 84 | 82 |
| 5 | 97 | 91 | 86 | 82 | 96 | 90 | 85 | 82 | 88 | 84 | 81 | | 86 | 83 | 80 | | 85 | 82 | 80 | 78 |
| 6 | 94 | 86 | 81 | 78 | 92 | 86 | 81 | 78 | 84 | 80 | 77 | | 83 | 79 | 77 | | 82 | 79 | 76 | 75 |
| 7 | 90 | 82 | 78 | 74 | 89 | 82 | 77 | 74 | 81 | 77 | 73 | | 80 | 76 | 73 | | 79 | 75 | 73 | 72 |
| 8 | 87 | 79 | 74 | 71 | 86 | 78 | 74 | 70 | 77 | 73 | 70 | | 76 | 73 | 70 | | 76 | 72 | 70 | 68 |
| 9 | 84 | 76 | 71 | 67 | 83 | 75 | 71 | 67 | 74 | 70 | 67 | | 74 | 70 | 67 | | 73 | 69 | 67 | 66 |
| 10 | 81 | 73 | 68 | 65 | 80 | 72 | 68 | 64 | 71 | 67 | 64 | | 71 | 67 | 64 | | 70 | 67 | 64 | 63 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 219500 |
| 5° | 216376 |
| 10° | 208413 |
| 15° | 194553 |
| 20° | 161481 |
| 25° | 93634 |
| 30° | 37981 |
| 35° | 5889 |
| 40° | 2290 |
| 45° | 1861 |
| 50° | 1706 |
| 55° | 1529 |
| 60° | 877 |
| 65° | 519 |
| 70° | 641 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |



TEST NUMBER: P221160

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED CR-W-BK-LC2-UNV

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 92.4 | 17.1 |
| 10°-20° | 235.6 | 43.5 |
| 20°-30° | 178.7 | 33.0 |
| 30°-40° | 25.9 | 4.8 |
| 40°-50° | 4.7 | 0.9 |
| 50°-60° | 3.2 | 0.6 |
| 60°-70° | 1.1 | 0.2 |
| 70°-80° | 0.1 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 506.7 | 93.5 |
| 0°-40° | 532.6 | 98.3 |
| 0°-60° | 540.6 | 99.8 |
| 0°-90° | 541.8 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 541.8 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1001 | |
| 5° | 983 | 92 |
| 15° | 857 | 236 |
| 25° | 387 | 179 |
| 35° | 22 | 26 |
| 45° | 6 | 5 |
| 55° | 4 | 3 |
| 65° | 1 | 1 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P221160

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED CR-W-BK-LC2-UNV

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|------|
| 0° | 1001 |
| 1° | 998 |
| 2° | 994 |
| 3° | 990 |
| 4° | 988 |
| 5° | 983 |
| 6° | 979 |
| 7° | 972 |
| 8° | 961 |
| 9° | 948 |
| 10° | 936 |
| 11° | 923 |
| 12° | 909 |
| 13° | 894 |
| 14° | 876 |
| 15° | 857 |
| 16° | 834 |
| 17° | 809 |
| 18° | 778 |
| 19° | 741 |
| 20° | 692 |
| 21° | 634 |
| 22° | 569 |
| 23° | 506 |
| 24° | 445 |
| 25° | 387 |
| 26° | 334 |
| 27° | 289 |
| 28° | 247 |
| 29° | 196 |
| 30° | 150 |
| 32.5° | 65 |
| 35° | 22 |
| 37.5° | 9 |
| 40° | 8 |
| 42.5° | 7 |
| 45° | 6 |
| 47.5° | 5 |
| 50° | 5 |
| 52.5° | 4 |
| 55° | 4 |
| 57.5° | 3 |
| 60° | 2 |
| 62.5° | 1 |
| 65° | 1 |



TEST NUMBER: P221160

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED CR-W-BK-LC2-UNV

CANDELA DISTRIBUTION (continued):

| | 0° |
|-------|----|
| 67.5° | 1 |
| 70° | 1 |
| 72.5° | 0 |
| 75° | 0 |
| 77.5° | 0 |
| 80° | 0 |
| 82.5° | 0 |
| 85° | 0 |
| 87.5° | 0 |
| 90° | 0 |

(END OF REPORT)