

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: P247034

Luminaire Tested: **213-8LED2736-12-CS-LVR**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P247034
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-46)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 213-8LED2736-12-CS-LVR
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 2700K CCT, 36 DEGREE WIDE OPTIC,
REGRESSED HOOD SILVER, HEX CELL LOUVER
Light Source: (1) SORAA 2700K 90 CRI LED
SM16-07-36D-927-03
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4000.0 lumens
Efficiency: N/A
Efficacy: 526.3 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.48
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P247034
CATALOG NUMBER: 213-8LED2736-12-CS-LVR

Luminous Intensity Polar Plot





TEST NUMBER: P247034

CATALOG NUMBER: 213-8LED2736-12-CS-LVR

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	113	111	109	107	107	105	104	103	102	101	100	99	98	96
2	111	107	104	102	109	106	103	101	103	100	99	100	98	96	97	96	95	93
3	107	103	99	96	106	101	98	95	99	96	94	97	94	93	95	93	91	90
4	104	99	95	92	102	98	94	91	96	92	90	94	91	89	92	90	88	87
5	101	95	91	88	99	94	90	87	92	89	87	91	88	86	90	87	85	84
6	98	92	87	84	97	91	87	84	89	86	83	88	85	83	87	84	82	81
7	95	88	84	81	94	88	84	81	87	83	81	86	83	80	85	82	80	79
8	92	86	81	78	91	85	81	78	84	81	78	83	80	78	82	80	77	76
9	90	83	79	76	89	83	79	76	82	78	76	81	78	75	80	77	75	74
10	87	81	76	74	87	80	76	74	80	76	73	79	76	73	78	75	73	72

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	7579149
5°	6931618
10°	5531439
15°	3765092
20°	1884801
25°	648906
30°	199283
35°	95405
40°	51525
45°	32794
50°	12051
55°	13505
60°	15492
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P247034
 CATALOG NUMBER: 213-8LED2736-12-CS-LVR

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1242.5	31.1
10°-20°	1962.4	49.1
20°-30°	627.1	15.7
30°-40°	108.0	2.7
40°-50°	36.2	0.9
50°-60°	14.1	0.4
60°-70°	9.7	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3832.0	95.8
0°-40°	3940.0	98.5
0°-60°	3990.3	99.8
0°-90°	4000.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4000.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	15362	
5°	13996	###
15°	7371	1962
25°	1192	627
35°	158	108
45°	47	36
55°	16	14
65°	0	10
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P247034
CATALOG NUMBER: 213-8LED2736-12-CS-LVR

CANDELA DISTRIBUTION (FULL):

	0°
0°	15361.7
1°	15185.9
2°	14900.6
3°	14630.8
4°	14343.7
5°	13995.8
6°	13566.0
7°	13057.8
8°	12438.4
9°	11770.1
10°	11041.0
11°	10277.1
12°	9546.2
13°	8817.1
14°	8086.4
15°	7371.2
16°	6624.6
17°	5829.4
18°	5067.2
19°	4305.0
20°	3589.8
21°	2954.7
22°	2382.3
23°	1905.5
24°	1508.7
25°	1192.0
26°	904.9
27°	715.2
28°	556.8
29°	428.1
30°	349.8
32.5°	222.7
35°	158.4
37.5°	111.4
40°	80.0
42.5°	64.4
45°	47.0
47.5°	31.3
50°	15.7
52.5°	15.7
55°	15.7
57.5°	15.7
60°	15.7
62.5°	15.7
65°	0.0



TEST NUMBER: P247034
CATALOG NUMBER: 213-8LED2736-12-CS-LVR

CANDELA DISTRIBUTION (continued):

	0°
67.5°	15.7
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)