

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: P247031

Luminaire Tested: **213-8LED2736-12-CS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P247031
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-9)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 213-8LED2736-12-CS
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 2700K CCT, 36 DEGREE WIDE OPTIC,
REGRESSED HOOD SILVER
Light Source: (1) SORAA 2700K 90 CRI LED
SM16-07-36D-927-03
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4000.0 lumens
Efficiency: N/A
Efficacy: 526.3 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.54
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P247031
CATALOG NUMBER: 213-8LED2736-12-CS

Luminous Intensity Polar Plot





TEST NUMBER: P247031
 CATALOG NUMBER: 213-8LED2736-12-CS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	112	110	109	112	110	109	107	106	105	104	103	102	101	99	98	98	96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	96	95	94	92
3	107	102	98	95	105	100	97	94	98	95	93	96	93	91	93	91	90	88
4	103	97	93	90	101	96	92	89	94	91	88	92	90	87	91	88	86	85
5	100	93	89	86	98	92	88	85	91	87	85	89	86	84	88	85	83	82
6	96	90	85	82	95	89	85	82	88	84	81	86	83	81	85	82	80	79
7	93	86	82	79	92	86	82	79	85	81	78	84	80	78	83	80	77	76
8	90	83	79	76	89	83	79	76	82	78	75	81	78	75	80	77	75	74
9	88	81	76	73	87	80	76	73	79	75	73	78	75	73	78	75	72	71
10	85	78	74	71	84	78	73	71	77	73	70	76	73	70	76	72	70	69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	5734797
5°	5623576
10°	4982152
15°	3809479
20°	2152941
25°	843959
30°	227028
35°	97272
40°	55454
45°	37818
50°	33466
55°	37504
60°	20919
65°	12375
70°	15291
75°	20206
80°	0
85°	0



TEST NUMBER: P247031
 CATALOG NUMBER: 213-8LED2736-12-CS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1041.1	26.0
10°-20°	1976.9	49.4
20°-30°	763.9	19.1
30°-40°	117.2	2.9
40°-50°	45.7	1.1
50°-60°	33.8	0.8
60°-70°	14.4	0.4
70°-80°	7.0	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3781.9	94.5
0°-40°	3899.2	97.5
0°-60°	3978.7	99.5
0°-90°	4000.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4000.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11624	
5°	11355	###
15°	7458	1977
25°	1550	764
35°	162	117
45°	54	46
55°	44	34
65°	11	14
75°	11	7
85°	0	0
90°	0	



TEST NUMBER: P247031
CATALOG NUMBER: 213-8LED2736-12-CS

CANDELA DISTRIBUTION (FULL):

	0°
0°	11623.5
1°	11581.0
2°	11516.2
3°	11483.2
4°	11440.7
5°	11354.7
6°	11225.0
7°	11021.0
8°	10719.2
9°	10364.4
10°	9944.6
11°	9493.0
12°	9029.7
13°	8523.9
14°	7996.9
15°	7458.1
16°	6866.3
17°	6209.6
18°	5499.9
19°	4789.0
20°	4100.5
21°	3443.8
22°	2862.5
23°	2346.1
24°	1926.4
25°	1550.3
26°	1173.1
27°	893.6
28°	677.9
29°	516.4
30°	398.5
32.5°	247.6
35°	161.5
37.5°	117.9
40°	86.1
42.5°	64.8
45°	54.2
47.5°	54.2
50°	43.6
52.5°	43.6
55°	43.6
57.5°	31.8
60°	21.2
62.5°	21.2
65°	10.6



TEST NUMBER: P247031
CATALOG NUMBER: 213-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	0°
67.5°	10.6
70°	10.6
72.5°	10.6
75°	10.6
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)