

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: P246965

Luminaire Tested: **213-8LED3010-12-BK-DIFF**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P246965
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-24)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 213-8LED3010-12-BK-DIFF
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 3000K CCT, 10 DEGREE SPOT OPTIC,
REGRESSED HOOD BLACK, DIFFUSED LENS
Light Source: (1) SORAA 3000K 95 CRI 10°NSP LED
SM16-07-10D-930-03
Ballast/Driver: CHROMA POWER SUPPLY IN0004

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4000.0 lumens
Efficiency: N/A
Efficacy: 500.0 lumens/watt
Spacing Criteria (0/90/45): 0.38 / 0.38 / 0.4
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246965
CATALOG NUMBER: 213-8LED3010-12-BK-DIFF

Luminous Intensity Polar Plot





TEST NUMBER: P246965
 CATALOG NUMBER: 213-8LED3010-12-BK-DIFF

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	94	93	92
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84
5	99	92	88	84	97	92	87	84	90	86	83	88	85	83	87	84	82	81
6	96	89	84	81	94	88	84	80	87	83	80	85	82	79	84	81	79	78
7	92	85	81	77	91	85	80	77	84	80	77	82	79	76	81	78	76	75
8	90	82	78	75	89	82	77	74	81	77	74	80	76	74	79	76	74	72
9	87	79	75	72	86	79	75	72	78	74	72	77	74	71	77	74	71	70
10	84	77	72	70	83	77	72	69	76	72	69	75	72	69	75	71	69	68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	8668531
5°	7470565
10°	5001741
15°	2790311
20°	1410477
25°	741233
30°	433945
35°	273808
40°	199144
45°	140037
50°	97404
55°	61675
60°	18156
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P246965
 CATALOG NUMBER: 213-8LED3010-12-BK-DIFF

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1271.0	31.8
10°-20°	1536.7	38.4
20°-30°	667.8	16.7
30°-40°	301.3	7.5
40°-50°	156.6	3.9
50°-60°	59.9	1.5
60°-70°	6.7	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3475.5	86.9
0°-40°	3776.8	94.4
0°-60°	3993.3	99.8
0°-90°	4000.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4000.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	17570	
5°	15084	###
15°	5463	1537
25°	1362	668
35°	455	301
45°	201	157
55°	72	60
65°	0	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P246965
CATALOG NUMBER: 213-8LED3010-12-BK-DIFF

CANDELA DISTRIBUTION (FULL):

	0°
0°	17569.7
1°	17424.4
2°	17062.0
3°	16535.7
4°	15882.6
5°	15084.0
6°	14177.0
7°	13177.8
8°	12106.9
9°	11054.6
10°	9983.7
12.5°	7532.9
15°	5462.8
17.5°	3847.3
20°	2686.4
22.5°	1906.2
25°	1361.6
27.5°	999.2
30°	761.7
32.5°	581.5
35°	454.6
37.5°	380.8
40°	309.2
42.5°	235.5
45°	200.7
47.5°	163.8
50°	126.9
52.5°	90.1
55°	71.7
57.5°	36.9
60°	18.4
62.5°	18.4
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)