

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: P246971

Luminaire Tested: **213-8LED3010-12-CS-LVR**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P246971
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-38)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 213-8LED3010-12-CS-LVR
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 3000K CCT, 10 DEGREE SPOT OPTIC,
REGRESSED HOOD SILVER, HEX CELL LOUVER
Light Source: (1) SORAA 3000K 95 CRI 10° NSP LED
SM16-07-10D-930-03
Ballast/Driver: CHROMA POWER SUPPLY IN0004

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4000.0 lumens
Efficiency: N/A
Efficacy: 533.3 lumens/watt
Spacing Criteria (0/90/45): 0.2 / 0.2 / 0.19
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246971
CATALOG NUMBER: 213-8LED3010-12-CS-LVR

Luminous Intensity Polar Plot





TEST NUMBER: P246971
 CATALOG NUMBER: 213-8LED3010-12-CS-LVR

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	116	114	113	111	114	112	111	110	108	107	106	105	104	103	101	101	100	99
2	113	111	108	106	111	109	107	105	106	104	103	103	102	101	101	100	99	97
3	111	108	105	103	109	106	104	102	104	102	100	102	100	99	100	98	97	96
4	109	105	102	100	108	104	101	99	102	100	98	100	99	97	99	97	96	95
5	107	103	100	98	106	102	99	97	101	98	97	99	97	96	98	96	95	94
6	105	101	98	96	104	100	98	96	99	97	95	98	96	95	97	95	94	93
7	104	99	97	95	103	99	96	94	98	96	94	97	95	94	96	94	93	92
8	103	98	95	93	102	98	95	93	97	95	93	96	94	93	95	94	92	92
9	101	97	94	92	101	97	94	92	96	94	92	95	93	92	95	93	92	91
10	100	96	93	91	100	96	93	91	95	93	91	94	92	91	94	92	91	90

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	40616485
5°	25529581
10°	2937259
15°	807805
20°	326262
25°	183294
30°	121062
35°	85708
40°	56806
45°	37748
50°	27709
55°	15483
60°	17762
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P246971
 CATALOG NUMBER: 213-8LED3010-12-CS-LVR

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	3138.8	78.5
10°-20°	539.8	13.5
20°-30°	164.3	4.1
30°-40°	89.0	2.2
40°-50°	39.5	1.0
50°-60°	22.0	0.6
60°-70°	6.5	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3842.9	96.1
0°-40°	3932.0	98.3
0°-60°	3993.5	99.8
0°-90°	4000.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4000.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	82323	
5°	51547	###
15°	1582	540
25°	337	164
35°	142	89
45°	54	39
55°	18	22
65°	0	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P246971
CATALOG NUMBER: 213-8LED3010-12-CS-LVR

CANDELA DISTRIBUTION (FULL):

	0°
0°	82323.0
1°	80635.3
2°	76602.5
3°	70418.8
4°	62066.5
5°	51547.4
6°	39180.2
7°	26919.2
8°	16578.4
9°	9649.2
10°	5862.9
12.5°	2647.8
15°	1581.5
17.5°	1048.3
20°	621.4
22.5°	445.0
25°	336.7
27.5°	266.6
30°	212.5
32.5°	178.4
35°	142.3
37.5°	106.2
40°	88.2
42.5°	54.1
45°	54.1
47.5°	36.1
50°	36.1
52.5°	36.1
55°	18.0
57.5°	18.0
60°	18.0
62.5°	18.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)