

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: G2-1802-569-7

Luminaire Tested: **213-8LED3010-12-CS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: G2-1802-569-7
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-7)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 213-8LED3010-12-CS
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 3000K CCT, 10 DEGREE SPOT OPTIC,
REGRESSED HOOD SILVER
Light Source: (1) SORAA 3000K 95 CRI 10°NSP LED
SM16-07-10D-930-03
Ballast/Driver: CHROMA POWER SUPPLY IN0004

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4000.0 lumens
Efficiency: N/A
Efficacy: 533.3 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.19
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: G2-1802-569-7
CATALOG NUMBER: 213-8LED3010-12-CS

Luminous Intensity Polar Plot





TEST NUMBER: G2-1802-569-7
 CATALOG NUMBER: 213-8LED3010-12-CS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	116	114	112	110	113	112	110	109	108	106	105	104	103	102	101	100	99	98
2	112	109	106	104	110	107	105	103	104	102	101	101	100	99	99	98	97	95
3	109	105	102	99	108	104	101	99	102	99	97	99	97	96	97	96	94	93
4	107	102	99	96	105	101	98	95	99	96	94	97	95	93	96	94	92	91
5	104	99	96	93	103	98	95	93	97	94	92	95	93	91	94	92	91	90
6	102	97	93	91	101	96	93	91	95	92	90	94	91	90	93	91	89	88
7	100	95	91	89	99	94	91	89	93	91	88	92	90	88	91	89	88	87
8	99	93	90	87	98	93	90	87	92	89	87	91	89	87	90	88	86	86
9	97	92	88	86	96	91	88	86	91	88	86	90	87	86	89	87	85	85
10	96	90	87	85	95	90	87	85	89	87	85	89	86	85	88	86	84	84

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	33574232
5°	23215360
10°	2658958
15°	839729
20°	374934
25°	242360
30°	192162
35°	170211
40°	147748
45°	131455
50°	103774
55°	81029
60°	40457
65°	15994
70°	19763
75°	0
80°	0
85°	0



TEST NUMBER: G2-1802-569-7
 CATALOG NUMBER: 213-8LED3010-12-CS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2812.4	70.3
10°-20°	539.4	13.5
20°-30°	215.3	5.4
30°-40°	178.6	4.5
40°-50°	146.4	3.7
50°-60°	82.3	2.1
60°-70°	20.2	0.5
70°-80°	5.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3567.1	89.2
0°-40°	3745.7	93.6
0°-60°	3974.5	99.4
0°-90°	4000.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4000.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	68050	
5°	46875	###
15°	1644	539
25°	445	215
35°	283	179
45°	188	146
55°	94	82
65°	14	20
75°	0	5
85°	0	0
90°	0	



TEST NUMBER: G2-1802-569-7
CATALOG NUMBER: 213-8LED3010-12-CS

CANDELA DISTRIBUTION (FULL):

	0°
0°	68049.5
1°	67146.9
2°	64977.2
3°	61098.2
4°	55091.8
5°	46874.7
6°	36718.8
7°	25175.6
8°	15045.5
9°	8607.6
10°	5307.4
12.5°	2613.4
15°	1644.0
17.5°	1145.7
20°	714.1
22.5°	539.4
25°	445.2
27.5°	390.5
30°	337.3
32.5°	310.0
35°	282.6
37.5°	268.9
40°	229.4
42.5°	215.8
45°	188.4
47.5°	174.7
50°	135.2
52.5°	121.6
55°	94.2
57.5°	66.9
60°	41.0
62.5°	27.3
65°	13.7
67.5°	13.7
70°	13.7
72.5°	13.7
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)